



SURFACE-MOUNT SCHOTTKY BARRIER DIODE

Product Summary (@TA = +25°C)

VRRM (V)	lo (mA)	VFmax (V)	I _{Rmax} (μΑ)
30	200	0.8	2

200mA surface-mount Schottky Barrier Diode in SOT23 (Standard)

package, offers low turn-on voltage and fast switching capability,

designed with PN Junction Guard Ring for Transient and ESD

Protection, totally lead-free finish and RoHS compliant, "Green" device.

Features and Benefits

- Low Turn-on Voltage ٠
- Fast Switching
- PN Junction Guard Ring for Transient and ESD Protection
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.

https://www.diodes.com/quality/product-definitions/

An automotive-compliant part is available under separate datasheet (BAT54Q /AQ /CQ /SQ)

Mechanical Data

- Package: SOT23
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed over Alloy 42 Leadframe (Lead-Free Plating). Solderable per MIL-STD-202, Method 208 (e3)
- Polarity: See Diagrams Below
- Weight: 0.008 grams (Approximate)

SOT23 (Standard)


Description







Top View

BAT54







BAT54S

Ordering Information (Note 4)

Part Number	Daakaga	Packing		
Part Number	Package	Qty.	Carrier	
BAT54-7-F	SOT23 (Standard)	3,000	Tape & Reel	
BAT54A-7-F	SOT23 (Standard)	3,000	Tape & Reel	
BAT54C-7-F	SOT23 (Standard)	3,000	Tape & Reel	
BAT54S-7-F	SOT23 (Standard)	3,000	Tape & Reel	
BAT54-13-F	SOT23 (Standard)	10,000	Tape & Reel	
BAT54A-13-F	SOT23 (Standard)	10,000	Tape & Reel	

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. Notes:


2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.




Marking Information



xxx = Product Type Marking Code KL1 = BAT54 KL2 = BAT54A KL3 = BAT54C KL4 = BAT54C YM & YM = Date Code Marking

Y or \overline{Y} = Year (ex: K = 2023) M = Month (ex: D = December)



Date Code Key

Year	2004	-	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	R	-	К	L	М	Ν	Р	R	S	Т	U	V
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		Vrrm Vrwm Vr	30	V
Average Rectified Output Current (Note 5)		lo	200	mA
Repetitive Peak Forward Current		IFRM	300	mA
Forward Surge Current	@ t < 1.0s	IFSM	600	mA

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	PD	200	mW
Typical Thermal Resistance Junction to Ambient Air (Note 5)	R _{0JA}	500	°C/W
Typical Thermal Resistance Junction to Case (Note 6)	Rejc	180	°C/W
Operating and Storage Temperature Range (Note 7)	TJ, T _{STG}	-65 to +150	°C

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 8)	V _{(BR)R}	30	—	_	V	I _{RS} = 100μA
Forward Voltage	VF	 	 	240 320 400 500 800	mV	IF = 0.1mA IF = 1mA IF = 10mA IF = 30mA IF = 100mA
Reverse Leakage Current (Note 8)	IR	_	_	2.0	μA	$V_R = 25V$
Total Capacitance	Ст	_		10	pF	V _R = 1.0V, f = 1.0MHz
Reverse Recovery Time	t _{RR}	—	_	5.0	ns	$I_F = 10mA$ through $I_R = 10mA$ to $I_R = 1.0mA$, $R_L = 100\Omega$


Notes: 5. Part mounted on FR-4 board with recommended pad layout, which can be found on our website at http://www.diodes.com/package-outlines.html. 6. Device mounted on Polymide substrate PC board. FR-4 2oz 1*MRP layout.

7. The heat generated must be less than the thermal conductivity from Junction-to-Ambient: $dP_D/dT_J < 1 / R_{0JA}$.

8. Short duration test pulse used to minimize self-heating effect.




BAT54 /A /C /S





Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



S	SOT23 (Standard)							
Dim	Min	Max	Тур					
Α	0.90	1.15	1.025					
A1	0.00	0.10	0.05					
A2	0.85	1.10	0.975					
b	0.30	0.51	0.40					
c	0.080	0.202	0.11					
D	2.80	3.00	2.90					
ш	2.25	2.55	2.40					
E1	1.20	1.40	1.30					
е	0.89	1.03	0.915					
e1	1.78	2.05	1.83					
F	0.40	0.60	0.535					
L1	0.45	0.61	0.55					
L	0.25	0.55	0.40					
а	0°	8°						
All	Dimens	ions in	mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT23 (Standard)

Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9

SOT23 (Standard)



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com