

NPN SMALL SIGNAL SURFACE MOUNT TRANSISTOR

Features

- BV_{CEO} > 45V
- I_C = 100mA High Collector Current
- P_D = 1000mW Power Dissipation
- 0.60mm² Package Footprint, 13 times smaller than SOT23
- 0.4mm Height Package Minimizing Off-Board Profile
- Complementary NPN Type: BC857BLP4
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at

https://www.diodes.com/products/automotive/automotiveproducts/.


 This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Case: X2-DFN1006-3
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu. Solderable per MIL-STD-202, Method 208@
- Weight: 0.0008 grams (Approximate)




Bottom View



C

Device Symbol



Top View Device Schematic

Ordering Information (Note 4)

Product	Status	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
BC847BLP4-7	Obsolete	F1	7	8mm	3,000
BC847BLP4-7B	Active	F1	7	8mm	10,000

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.


2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information





Absolute Maximum Ratings (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	50	V
Collector-Emitter Voltage	V _{CEO}	45	V
Emitter-Base Voltage	V _{EBO}	6.0	V
Collector Current	Ι _C	100	mA
Peak Pulse Collector Current	I _{CM}	200	mA

Thermal Characteristics (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Dower Dissinction	(Note 5)	D	400	mW	
Power Dissipation	(Note 6)	PD PD	1000		
Thermal Desistance, Junction to Ambient	(Note 5)		310	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	R _{0JA}	120		
Thermal Resistance, Junction to Lead (Note 7)		R _{θJL}	120	°C/W	
Operating and Storage and Temperature Range		T _J , T _{STG}	-55 to +150	°C	

ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	200	V	В

Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)

Characteristic		Min	Тур	Мах	Unit	Test Condition
Collector-Base Breakdown Voltage		50	—	_	V	I _C = 10μΑ, I _B = 0
Collector-Emitter Breakdown Voltage (Note 9)	BV _{CEO}	45	—	—	V	I _C = 10mA, I _B = 0
Emitter-Base Breakdown Voltage	BV_{EBO}	6	—	—	V	$I_{E} = 1 \mu A, I_{C} = 0$
DC Current Gain	h _{FE}	200	350	450	_	V _{CE} = 5V, I _C = 2mA
Collector-Emitter Saturation Voltage (Note 9)	V _{CE(sat)}	_	80 200	250 600	mV	I_{C} = 10mA, I_{B} = 0.5mA I_{C} = 100mA, I_{B} = 5mA
Base-Emitter Saturation Voltage (Note 9)	V _{BE(sat)}	_	700 900	_	mV	I_{C} = 10mA, I_{B} = 0.5mA I_{C} = 100mA, I_{B} = 5mA
Base-Emitter Voltage (Note 9)	V _{BE(on)}	580 —	640 725	700 770	mV	V_{CE} = 5V, I_C = 2mA V_{CE} = 5V, I_C = 10mA
Collector-Cutoff Current	I _{СВО}			15 5	nA μA	V _{CB} = 30V V _{CB} = 30V, T _A = +150°C
Gain Bandwidth Product	f⊤	100	_	_	MHz	V _{CE} = 5V, I _C = 10mA, f = 100MHz
Collector-Base Capacitance	Ссво	_	3		pF	V _{CB} = 10V, f = 1MHz

Notes: 5. For a device mounted on the minimum recommended pad layout of 1oz copper on a single-sided 1.6mm FR4 PCB; device is measured under still-air conditions whilst operating in steady-state condition. The entire exposed collector pad is attached to the heatsink.

Same as Note 5, except the exposed collector pad is mounted on 25mm x 25mm 2oz copper.


7. Thermal resistance from junction to solder-point (on the exposed collector pad).


8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.

9. Measured under pulsed conditions. Pulse width \leq 300µs. Duty cycle \leq 2%.



Typical Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)








Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



X2-DFN1006-3					
Dim	Min	Max	Тур		
Α		0.40			
A1	0.00	0.05	0.03		
b	0.10	0.20	0.15		
b2	0.45	0.55	0.50		
D	0.95	1.05	1.00		
Е	0.55	0.65	0.60		
е	-	I	0.35		
L1	0.20	0.30	0.25		
L2	0.20	0.30	0.25		
k	-	-	0.40		
z	0.02	0.08	0.05		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)		
С	0.350		
G1	0.150		
G2	0.075		
Х	0.450		
X1	0.600		
X2	1.200		
Y	0.200		
Y1	0.550		

X2-DFN1006-3



IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 products provided subject to Diodes' Standard Terms and Conditions of Sale Diodes are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com