


Description

The BCR430U is a monolithically integrated linear LED controller designed to function as a Constant Current Regulator (CCR) for linear LED driving. The device operates over a voltage range of 5V to 42V and regulates the output LED current up to 100mA, set by an external resistor. It is designed for driving LEDs in strings and will reduce current at increasing temperatures to self-protect. The low voltage drop during current regulation allows efficient driving of LED strings with a range of forward voltages and supply voltage tolerances.

Applications

- LED strips
- LED panel displays
- Architectural and landscape lighting
- Mood and decorative lighting
- Retail lighting



Typical Configuration

Features

- LED Current Tolerance of ±5% at 95mA Output Current
- Thermal Protection Reduces LED Current at Elevated
 Temperature
- Low Typical Saturation Voltage of 115mV at 50mA
- 5mA to 100mA Adjustable LED Current with an External Resistor
- 5V to 42V Supply Voltage
- High Power 1W Dissipation in SOT26
- No External Capacitors Required for Stable Operation
- LED Dimming Using PWM
- Parallel Devices to Increase Regulated Current
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>
- An Automotive-Compliant Part is Available Under Separate Datasheet (<u>BCR430UW6Q</u>)

Mechanical Data

- Package: SOT26
- Package Material: Molded Plastic. "Green" Molding Compound. UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads.
 Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.018 grams (Approximate)



SOT26

Ordering Information (Note 4)

Product	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
BCR430UW6-7	430	7	8	3,000

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.


2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/




Marking Information



430 = Part Marking (See Ordering Information) YM = Date Code Marking Y = Year (ex: I = 2021) M = Month (ex: 9 = September)


Date Code Key												
Year	2019	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030
Code	G	Н		J	K	L	М	N	0	Р	R	S
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D

Pinout Diagram



Pin Descriptio	on		
Pin Number	Pin Name	Function	
1	NC	Not Connected	
2	GND	Power Ground	
3	REXT	External Resistor for Adjusting Output Current	
4	VS	Supply Voltage	
5	NC	Not Connected	
6	OUT	I _{OUT} - Regulated Output Current	

Functional Block Diagram





Absolute Maximum Ratings (Voltage relative to GND, @ T_A = +25°C, unless otherwise specified.)

Parameter	Symbol	Min	Мах	Unit
Supply Voltage	Vs	-0.5	45	V
Output Current	I _{OUT}	0	100	mA
Output Voltage	V _{OUT}	-0.5	42	V
R _{EXT} Current	I _{REXT}	0	0.3	mA
R _{EXT} Voltage	V _{REXT}	-0.5	5	V

Recommended Operating Conditions

Parameter	Symbol	Min	Мах	Unit
Supply Voltage	Vs	5	42	V
OUT Pin Voltage Range	Vout	0.5	40	V
Output Current (Note 5)	lout	5	100	mA
Ambient Temperature Range (Notes 5 & 6)	T _A	-40	+125	°C
Normal Operation Junction Temperature Range (Note 6)	TJ	-40	+125	°C

Thermal Characteristics (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Dower Dissinction	(Note 7)	D D	735		
Power Dissipation	(Note 8)	P _D	793	mW	
The model Desistance, humation to Ambient	(Note 7)	R	136		
Thermal Resistance, Junction to Ambient	(Note 8)	R _{0JA}	126	°C/W	
Thermal Resistance, Junction to Lead	(Note 9)	R _{θJL}	88.5		
Operating Junction Temperature	TJ	-40 to +125	°C		
Recommended Storage Temperature	Ts	-55 to +165	°C		

ESD Ratings (Note 10)

Characteristics	Symbols	Value	Unit	JEDEC Class
Electrostatic Discharge – Human Body Model	HBM	2000	V	2
Charge Device Model	CDM	1000	V	C5

Notes:

5. Subject to the device junction temperature not exceeding the onset point of Over Temperature Protection (OTP) operation. The OTP operation typically starts at +125°C, but can start as low as +100°C or as high as +140°C.

6. A typical device will operate at its defined output current (set by Rext) up to a junction temperature of +125°C. However, if the combination of power dissipation and ambient temperature drives T_J above +125°, the output current will be reduced linearly with temperature, reaching zero output current at +150°C.

7. For a device mounted on MRP FR4-PCB; device is measured under still air conditions whilst operating in a steady-state.

8. Same as Note 7, except the device is mounted on 25mm \times 25mm 2oz copper.

9. R_{BJL} = Thermal resistance from junction to solder-point (at the end of the OUT leads).

10. Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test	t Condition	
Supply Voltage	Vs	5	_	42	V	—		
Sussely Current (Nate 11)		180	261	400	μA	$I_{OUT} = 50 \text{mA}, \text{V}_{S}$	= 5V	
Supply Current (Note 11)	Is	_	285	500	μA	$I_{OUT} = 50 \text{mA}, \text{V}_{S}$	= 42V	
Quiescent Current	Ι _Q	40	67	100	μA	V _S = 42V; R _{EXT} =	V _S = 42V; R _{EXT} = open	
Output Current range	IOUT	5	_	100	mA	_		
		18	20.8	22.7	mA	$R_{EXT} = 30k\Omega$		
Output Current, set by R _{EXT} (Note 11)	lout	45.7	49.1	52.3	mA	R _{EXT} = 12.7kΩ	V _{OUT} > 1V; V _S ≥ 5V	
		90	95.3	100	mA	$R_{EXT} = 6.49 k\Omega$		
Driver Voltage Drop (Note 11)	V _{OUT-MIN}	50	115	200	mV	I _{OUT} = 50mA		
DEVI Din Valtage (Nate 11)	N	0.880	0.903	0.960	V	$R_{EXT} = 300 k\Omega$		
REXT Pin Voltage (Note 11)	V _{REXT}	0.875	0.892	0.955	V	$R_{EXT} = 6.49 k\Omega$		
Thermal Knee Junction Temperature (Note 12)	Τĸ	_	+125	_	°C	_		
Output Current Change vs. Temperature	(ΔΙ _{ΟUT} /Ι _{ΟUT}) / ΔΤ _J	_	0.0032	_	%/°C	T _J > -40°C; T _J = +120°C; I _{OUT} = 50mA		
Output Current Change vs. Supply Voltage or Output Voltage	(ΔI _{OUT} /I _{OUT}) / ΔV		0.0055	_	%/V	$I_{OUT} = 50 \text{mA};$ 5V < V _S < 42V or 1V < V _{OUT} < 40V		

Notes: 11. Measured under pulsed conditions. Pulse width \leq 300µs. Duty cycle \leq 2%.

Thermal Knee Junction Temperature is defined as the asymptotic intersection of the +25°C temperature I_{OUT} current and the I_{OUT} current in overtemperature protection mode.




Typical Thermal Characteristics (@ T_A = +25°C, unless otherwise specified.)






Typical Electrical Characteristics (continued) (@ T_A = +25°C, unless otherwise specified.)




The LED current is set according to the resistor value which is connected to the REXT pin.






Application Information

Typical Application Circuit




No external capacitors required for stable operation. Suitable for diming with VS or REXT pin modulation.

Switching / Timing Information (@ V_S = 10V, V_{OUT} = 1V, 1kHz, 50% Mark-Space ratio, R_{EXT} modulation.)



For $R_{EXT} = 6.49 k\Omega$, $t_R = 14 \mu s$ at -40°C, $9 \mu s$ at +25°C and $7 \mu s$ at +110°C. Rise time does not change significantly with LED loads (delay increases by less than $2 \mu s$).




Fall time is independent of temperature. Fall time does not change significantly with LED loads.



Package Outline Dimensions

Please see https://www.diodes.com/package-outlines.html for the latest version.






		DT26	
Dim	Min	Max	Тур
A1	0.013	0.10	0.05
A2	1.00	1.30	1.10
A3	0.70	0.80	0.75
b	0.35	0.50	0.38
Ċ	0.10	0.20	0.15
D	2.90	3.10	3.00
е	-	-	0.95
e1	-	-	1.90
Е	2.70	3.00	2.80
E1	1.50	1.70	1.60
L	0.35	0.55	0.40
а	-	-	8°
a1	-	-	7°
All	Dimen	sions	in mm

Suggested Pad Layout

Please see https://www.diodes.com/package-outlines.html for the latest version.

SOT26



Dimensions	Value (in mm)
С	2.40
C1	0.95
G	1.60
Х	0.55
Y	0.80
Y1	3.20



IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 products provided subiect to Diodes' Standard Terms and Conditions of Sale Diodes are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com