



D15V0S1U2LP1610Q

ONE CHANNEL HIGH SURGE TVS DIODE

Product Summary

VBR (Min)	PP (Max)	Ст (Тур)
17.0V	44A	270pF

Description

This new generation TVS is designed to protect sensitive electronics from the damage due to ESD. The combination of small size and high ESD surge capability makes it ideal for protecting one line against high surge current and other transients.

Applications


- Power line protections
- Mobile device applications
- Touch panels
- Small panel modules
- Type-C "CC"
- V_{DD} protections


Features


- Provides ESD Protection per IEC 61000-4-2 Standard: Air ±30kV. Contact ±30kV
- One Channel of ESD Protection
- Low Channel Input Capacitance
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3) The DIODES™ D15V0S1U2LP1610Q is suitable for
- automotive applications requiring specific change control; this part is AEC-Q101 gualified, PPAP capable, and manufactured in IATF 16949 certified facilities. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: U-DFN1610-2
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: NiPdAu. Solderable per MIL-STD-202, Method 208 @4)
- Weight: 0.003 grams (Approximate)









Device Schematic

Ordering Information (Note 4)

Notes:

Part Number	Package	Marking Code	Reel Size	Tape Width	Packing		
Fait Nulliber	Fackage	Marking Code	(inches)	(mm)	Qty.	Carrier	
D15V0S1U2LP1610Q-7	U-DFN1610-2 (Type B)	15T	7	8	10,000	Tape & Reel	

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and

Lead-free. 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and

<1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information

Option A:



15T = Product Type Marking Code YM = Date Code Marking Y = Year (ex: J = 2022) M = Month (ex: 9 = September) Dot Denotes Cathode Side

Date Code Key

Year	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032	2033
Code	J	K	L	М	N	0	Р	R	S	Т	U	V
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
monun	oun	100	initial	, Abi	initialy	oun	Vui	Aug	000	001	1101	000

Option B:

	15T YWX	
•		

15T = Product Type Marking Code YWX = Date Code Marking Y = Year (ex: 0 to 9) W = Week (ex: a = Week 27; z Represents Week 52 and 53) X = Internal Code Dot Denotes Cathode Side

Year	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032	2033
Code	2	3	4	5	6	7	8	9	0	1	2	3
Week		1-	26			27-	-52			5	3	
Code	A-Z			a-z				Z				
Internal Code	Sun	1	Mon		Tue	We	d	Thu		Fri		Sat
Code	Т		U		V	W		Х		Y		Z



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	Conditions
ESD Protection – Contact Discharge	Vesd_contact	±30	kV	Standard IEC 61000-4-2
ESD Protection – Air Discharge	Vesd_air	±30	kV	Standard IEC 61000-4-2

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Power Dissipation (Note 5)		PD	300	mW
Thermal Resistance, Junction to Ambient	T _A = +25°C	R _{0JA}	417	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C


Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Part Number	Reverse Standoff Voltage	Breakdown Voltage Vвв. @ Іт		Test Current	Max. Reverse Leakage Current @ V _{RWM} (Note 6)	Max. Clamping Voltage @ IPP (Note 7)	Max. Peak Pulse Current	Channel Input Capacitance (Note 8) $V_R = 0V,$ f = 1MHz, Any I/O to GND	Marking Code
		VBR	@ I _T		(
	VRWM (V)	Min (V)	Max (V)	lτ (mA)	I _R (nA)	Vc (V)	IPP (A)	Ст (рF)	
D15V0S1U2LP1610Q-7	15	17	23	1	200	28	44	270	15T

5. Device mounted on FR-4 PCB pad layout (2oz copper) as shown on Diodes Incorporated's suggested pad layout, which can be found on our website Notes: at http://www.diodes.com/package-outlines.html.
Short duration pulse test used to minimize self-heating effect.
Clamping voltage value is based on an 8x20µs peak pulse current (IPP) waveform.
Measured from any I/O to GND.



D15V0S1U2LP1610Q








Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

U-DFN1610-2 (Type B)




U-DFN1610-2 (Type B)								
Dim	Min Max 1							
Α	0.45	0.55	0.50					
A1	0.00	0.05	0.015					
A3	-	-	0.127					
b	0.85	0.95	0.90					
D	1.55	1.65	1.60					
E	0.95	1.05	1.00					
е	-	-	1.10					
L	0.35	0.45	0.40					
z	0.050 REF							
z1	0.050 REF							
All C	Dimens	ions in	mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

U-DFN1610-2 (Type B)



Dimensions	Value (in mm)
Х	0.650
X1	0.600
X2	1.900
Y	1.300



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

provided 5 Diodes' products subject to Diodes' Standard Terms and Conditions of Sale are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com