



# D30V0S1UG3LP20

#### **1 CHANNEL HIGH SURGE TVS DIODE**

#### **Product Summary**

VBR (MIN)	IPP (MAX)	VCL TYP @ IPP MAX
30.5V	180A	31


#### Description

This new generation TVS is designed to protect sensitive electronics from the damage due to ESD and Surge. The combination of small size and high ESD surge capability makes it ideal for use in portable applications such as cellular phones, battery and notebook computers. It provides low clamping voltage, making it ideally suited for power rail protection in computing and mobile devices.

#### Applications

- Battery protections
- USB VBUS
- Cellular handsets
- Portable electronics
- Notebook computers

# U-DFN2020-3 (Type C)



.

°G G


YM

# Features

- Low Profile Package (0.60mm Typical) and Ultra-Small PCB Footprint Area (2.3mm × 1.7mm Max) Suitable for Compact Portable Electronics
- Provides ESD Protection per IEC 61000-4-2 Standard: Air ±30kV, Contact ±30kV
- Provides Surge and Lightning Protection per IEC 61000-4-5 Standard: IPP Max 180A
- One Channel of ESD and Surge Protection
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

#### **Mechanical Data**

- Package: U-DFN2020-3
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208 @4
- Weight: 0.004 grams (Approximate)



1 and 2 Must Be Electrically Connected At the PCB

#### Ordering Information (Note 4)

Part Number	Baakaga	ackage Marking Code Reel Size (inches)		Tape Width (mm)	Pac	king
Fart Nulliber	Package	Marking Code	Reel Size (Inches)	Tape width (min)	Qty.	Carrier
D30V0S1UG3LP20-7	U-DFN2020-3 (Type C)	8G	7	8	3,000	Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4 For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

#### Marking Information

8G = Product Type Marking Code
YM = Date Code Marking
Y = Year (ex: J = 2022)
M = Month (ex: 9 = September)

Date Code Key

Year	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032	2033
Code	J	К	L	М	Ν	0	Р	R	S	Т	U	V
	1											
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec



#### Maximum Ratings (@ T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	Conditions
Peak Pulse Power Dissipation	P <sub>PP</sub>	5580	W	8/20µs (Note 6)
Peak Pulse Current	IPP	180	А	8/20µs, per Figure 3
ESD Protection – Contact Discharge	Vesd_contact	±30	kV	Standard IEC 61000-4-2
ESD Protection – Air Discharge	$V_{\text{ESD}}$ air	±30	kV	Standard IEC 61000-4-2

#### **Thermal Characteristics**

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	PD	500	mW
Thermal Resistance, Junction to Ambient $T_A = +25^{\circ}C$	Reja	250	°C/W
Operating and Storage Temperature Range	TJ, TSTG	-55 to +150	°C

#### Electrical Characteristics (@ T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
Reverse Working Voltage	V <sub>RWM</sub>	_	_	30	V	—
Reverse Current	IR	_	_	1	μA	VR = VRWM
Reverse Breakdown Voltage	V <sub>BR</sub>	30.5	_	38.0	V	I <sub>R</sub> = 1mA
Reverse Clamping Voltage (Note 6)		_	25.0	_	v	IPP = 50A, tP = 8/20µs
Reverse Clamping voltage (Note 6)	V <sub>CL</sub>	_	31.0	—	V	IPP = 180A, tP = 8/20µs
			34.5	—		IPP = 16A, tP = 100ns
ESD Clamping Voltage (Note 7)	Vc	—	32.5	—	V	IPP = 32A, tP = 100ns
		—	30.5	—		IPP = 70A, tP = 100ns
Conseitance	0	—	500	_	~ <b>F</b>	$V_R = 0V$ , f = 1MHz
Capacitance	CT	_	135	_	рF	V <sub>R</sub> = 30V, f = 1MHz

Notes: 5. Device mounted on FR-4 PCB pad layout (2oz copper) as shown on Diodes Incorporated's suggested pad layout, which can be found on our website at http://www.diodes.com/package-outlines.html.

6. Clamping voltage value is based on an 8x20us peak pulse current (IPP) waveform, Measured from Pin1 and Pin2 to Pin3.

7. Transmission Line Pulse Test (TLP) settings:  $t_P$  = 100ns,  $t_R$  = 10ns,  $I_{TLP}$  and  $V_{TLP}$  averaging window is from 70ns to 90ns.



# D30V0S1UG3LP20






Figure 1 Typical 8×20µs Puls Waveform









Figure 4 Typical Capacitance, Pin1 or Pin2 to Pin3



### **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.



U-DFN2020-3							
(Type C)							
Dim	Min	Max	Тур				
Α	0.55	0.65	0.60				
A1	0.00	0.05	0.02				
A3			0.152				
b	0.25	0.35	0.30				
D	1.95	2.05	2.00				
D2	0.90	1.10	1.00				
E	1.95	2.05	2.00				
E2	1.40	1.60	1.50				
е		0.65BS	SC				
k			0.35				
L	0.35	0.45	0.40				
L1	0.20	0.30	0.25				
Z			0.20				
All D	imens	ions ir	n mm				

## **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value
Dimensions	(in mm)
С	0.650
Х	0.600
X1	1.100
X2	0.350
X3	2.300
Y	0.400
Y1	1.600
Y2	1.700

U-DFN2020-3 (Type C)

U-DFN2020-3 (Type C)



#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' provided to Diodes' Standard Terms and Conditions of Sale products are subject (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2022 Diodes Incorporated. All Rights Reserved.

#### www.diodes.com