



DGD0636M

Description

The DIODES[™] DGD0636M is a three-phase gate driver IC designed for high-voltage / high-speed applications, driving N-Channel MOSFETs and IGBTs in a half-bridge configuration. High-voltage processing techniques enable the DGD0636M's high side to switch to 100V in a bootstrap operation.


The DGD0636M logic inputs are compatible with standard TTL and CMOS levels (down to 3.3V) for easy interfacing with controlling devices and are enabled low to better function in high-noise environments. The driver outputs feature high-pulse current buffers designed for minimum driver cross conduction.

The DGD0636M offers numerous protection functions. A shootthrough protection logic prevents both outputs from being high when both inputs are high (fault state). An undervoltage lockout for VCC shuts down the respective high-side output. An overcurrent protection will terminate the six outputs. Both the VCC UVLO and the overcurrent protection trip an automatic fault clear with a timing that is adjustable with an external capacitor.

The DGD0636M is offered in SO-28 (Type TH) package and the operating temperature extends from -40°C to +125°C.

Applications

- 3-phase motor inverter drivers
- BLDC motor drivers
- Industrial motor inverters power tools, robotics
- General-purpose 3-phase inverters



Typical Configuration

Ordering Information (Note 4)

Part Number	Packago	Marking	Reel Size (inch)	Tape Width (mm)	Pa	cking
Fart Number	Package	Warking	Reel Size (IIICII)	Tape Width (min)	Qty.	Carrier
DGD0636MS28-13	SO-28 (Type TH)	DGD0636M	13	24	1,500	Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

January 2023 © 2023 Copyright Diodes Incorporated. All Rights Reserved.

3-PHASE HALF-BRIDGE GATE DRIVER IN SO28

Features

- Three Floating High-Side Drivers in Bootstrap Operation to 100V
- 200mA Source / 350mA Sink Output Current Capability
- Outputs Tolerant to Negative Transients, dV/dt Immune
- Logic Input 3.3V Capability
- Internal Deadtime of 290ns to Protect MOSFETs and IGBTs
- Matched Prop Delay for All Channels
- Outputs Out of Phase with Inputs
- Schmitt Triggered Logic Inputs
- Cross Conduction Prevention Logic
- Undervoltage Lockout for All Channels
- Overcurrent Protection Shuts Down Drivers
- Extended Temperature Range: -40°C to +125°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative.

https://www.diodes.com/guality/product-definitions/

Mechanical Data

- Package: SO-28
- Package Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish—Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.250 grams (Approximate)



SO-28 (Type TH) Top View




DGD0636M

Marking Information



)'! = Manufacturer's Marking DGD0636M = Product Type Marking Code YY = Year (ex: 23 = 2023) WW = Week (01 to 53)

Pin Diagrams




SO-28 (Type TH)



Pin Descriptions

Pin Number	Pin Name	Function	
1	Vcc	Low-Side and Logic Fixed Supply	
2, 3, 4	HIN1*, HIN2*, HIN3*	Logic Input for High-Side Gate Driver Output, Out of Phase with HO	
5, 6, 7	LIN1*, LIN2*, LIN3*	Logic Input for Low-Side Gate Driver Output, Out of Phase with LO	
8	FO*	Fault Output with Open Drain (Fault with Overcurrent and Vcc UVLO)	
9	ITRIP	Analog Input for Overcurrent Shutdown	
10	EN	Logic Input for Functionality, I/O Logic Functions when EN is High	
11	RCIN	An External RC Network Input Used to Define FAULT CLEAR Delay	
12	Vss	Logic Ground	
13	COM	Low-Side Driver Return	
14, 15, 16	LO3, LO2, LO1	Low-Side Gate Driver Output	
17, 21, 25	NC	No Connection (No Internal Connection)	
18, 22, 26	Vs3, Vs2, Vs1	High-Side Floating Supply Return	
19, 23, 27	HO3, HO2, HO1	High-Side Gate Driver Output	
20, 24, 28	Vb3, Vb2, Vb1	High-Side Floating Supply	

Functional Block Diagram





Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
High-Side Floating Supply Voltage	VB	-0.3 to +124	V
High-Side Floating Supply Offset Voltage	Vs	V _B – 24 to V _B + 0.3	V
High-Side Floating Output Voltage	Vно	Vs – 0.3 to V _B + 0.3	V
Low-Side Output Voltage	Vlo	-0.3 to V _{CC} + 0.3	V
Offset Supply Voltage Transient	dVs/dt	50	V/ns
Low-Side Fixed Supply Voltage	Vcc	-0.3 to +24	V
Logic Input Voltage (HIN*, LIN*, ITRIP, EN and FO*)	VIN	-0.3 to +5.5	V

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power-Dissipation Linear Derating Factor (Note 5)	PD	2.3	W
Thermal Resistance, Junction to Ambient (Note 5)	Reja	60	°C/W
Thermal Resistance, Junction to Case (Note 5)	Rejc	45	°C/W
Operating Temperature	TJ	+150	
Lead Temperature (Soldering, 10s)	TL	+300	°C
Storage Temperature Range	T _{STG}	-55 to +150	

Note: 5. When mounted on a standard JEDEC 2-layer FR-4 board.

Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit
High-Side Floating Supply Absolute Voltage	VB	Vs + 10	Vs + 20	V
High-Side Floating Supply Offset Voltage	Vs	(Note 6)	100	V
High-Side Floating Output Voltage	Vно	Vs	VB	V
Low-Side Fixed Supply Voltage	Vcc	10	20	V
Low-Side Output Voltage	VLO	COM	Vcc	V
Logic Input Voltage (HIN*, LIN*, ITRIP & EN)	VIN	Vss	5	V
Fault Output Voltage	V _{FO}	V _{SS}	Vcc	V
Logic Ground	Vss	-5	5	V
Ambient Temperature	TA	-40	+125	°C

Note: 6. Logic operation for V_S of -5V to +100V.



DC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}) = 15V, @T_A = +25°C, unless otherwise specified.) (Note 7)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Logic "0" Input Voltage	VIH	2.4	—	—	V	—
Logic "1" Input Voltage	VIL	_		0.8	V	—
High-Level Output Voltage, V _{BIAS} – V _O	Voh	_	_	0.1	V	$I_O = 0 m A$
Low-Level Output Voltage, Vo	Vol	—	_	0.1	V	Io = 0mA
Offset Supply Leakage Current	ILK	—	—	10	μA	$V_{B} = V_{S} = 100V$
Quiescent V _{BS} Supply Current	IBSQ	10	85	130	μA	$V_{IN} = 0V \text{ or } 5V, EN = 0V$
Quiescent Vcc Supply Current	lccq	—	1.1	1.6	mA	$V_{IN} = 0V \text{ or } 5V, EN = 0V$
Logic-Input Bias Current (HO = LO = HIGH)	lin+	—	130	200	μA	$V_{IN} = 0V$
Logic-Input Bias Current (HO = LO = LOW)	l _{IN-}	—	3.0	20	μA	$V_{IN} = 5V$
Logic Enable "1" Input Bias Current	I _{EN+}	—	33	80	μA	$V_{EN} = 5V$
Logic Enable "0" Input Bias Current	I _{EN-}	—	_	2.0	μA	$V_{EN} = 0V$
V _{BS} Supply Undervoltage Positive Going Threshold	VBSUV+	7.6	8.9	9.9	V	—
V _{BS} Supply Undervoltage Negative Going Threshold	VBSUV-	7.1	8.3	9.4	V	—
V _{CC} Supply Undervoltage Positive Going Threshold	V _{CCUV+}	7.6	8.9	9.9	V	—
Vcc Supply Undervoltage Negative Going Threshold	Vccuv-	7.1	8.3	9.4	V	—
Output High Short-Circuit Pulsed Current	I _{O+}	120	200	_	mA	$V_0 = 0V$, PW $\leq 10\mu s$
Output Low Short-Circuit Pulsed Current	lo-	250	350	_	mA	Vo = 15V, PW ≤ 10µs
Overcurrent Detect Positive Threshold	VITH+	400	500	600	mV	—
Overcurrent Detect Negative Threshold	VITH-	340	420	500	mV	—
Short-Circuit Input Current	Icsin	6.0	11	16	μA	Vcsin = 1V
RCIN Positive Going Threshold Voltage	V _{RCINTH+}	7.0	8.4	9.8	V	—
RCIN Negative Going Threshold Voltage	VRCINTH-	—	5.0	_	V	-
Fault Output Low-Level Voltage	VFOL	_	0.2	0.5	V	Vcs = 1V, IFO = 1.5mA
RCIN on Resistance	Rdsrcin	40	75	110	Ω	I _{RCIN} = 1.5mA
Fault Output on Resistance	Rdsfo	80	130	180	Ω	IFO = 1.5mA

Note: 7. The V_{IN}, V_{TH}, and I_{IN} parameters are referenced to V_{SS} and are applicable to all six channels (HIN1*, 2*, 3* and LIN1*, 2*, 3*). The V_O and I_O parameters are applicable to the output pins (HO1, 2, 3 and LO1, 2, 3) and are referenced to COM.

AC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}) = 15V, C_L = 1000pF, @T_A = +25°C, unless otherwise specified.)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Turn-On Propagation Delay	ton	200	330	460	ns	$V_S = 0V$
Turn-Off Propagation Delay	toff	200	330	460	ns	$V_S = 0V$
Turn-On Rise Time	tr	—	90	150	ns	$V_S = 0V$
Turn-Off Fall Time	tf	_	35	60	ns	$V_S = 0V$
Delay Matching	tрм	_	_	50	ns	—
Enable Low to Output Shutdown Delay	t _{EN}	225	330	425	ns	—
ITRIP Pin Leading-Edge Blanking Time	t BLT	200	300	400	ns	—
Time from ITRIP Triggering to FO*	t FLT	360	550	760	ns	From VITRIP = 1V to FO* turn off
Time from ITRIP Triggering to All Gate Outputs Turn Off	t ITRIP	420	615	820	ns	From VITRIP = 1V to starting gate turn off
Input Filtering Time (HIN*, LIN*, EN)	t FLTIN	_	250	_	ns	—
Fault Clear Time	t FLTCLR	—	1.6	—	ms	Crcin = 1nF, Rrcin = 2MW
Deadtime	tрт	200	290	420	ns	—
Deadtime Matching	t _{DTM}	_		50	ns	—
Output Pulse Width Matching (Note 8)	tрм	_	50	75	ns	PWIN > 1µs

Note: 8. t_{PM} is defined as $PW_{IN} - PW_{OUT}$.



Timing Waveforms




Figure 1. Switching Time Waveform Definitions




Figure 2. Input/Output Timing Diagram





Figure 3. Overcurrent Timing Definitions





Typical Performance Characteristics (@T_A = +25°C, unless otherwise specified.)




Figure 5. Turn-on Propagation Delay vs. Supply Voltage




Figure 7. Turn-off Propagation Delay vs. Supply Voltage




Figure 9. Rise Time vs. Supply Voltage






Figure 6. Turn-on Propagation Delay vs. Temperature









Typical Performance Characteristics (continued)




Figure 11. Fall Time vs. Supply Voltage




Figure 13. Quiescent Current vs. Supply Voltage






Figure 15. Delay Matching vs. Supply Voltage










Figure 16. Delay Matching vs. Temperature



Typical Performance Characteristics (continued)




Figure 17. Output Source Current vs. Supply Voltage




Figure 19. Output Sink Current vs. Supply Voltage




Figure 21. Logic 1 Input Voltage vs. Supply Voltage





Figure 18. Output Source Current vs. Temperature






Figure 22. Logic 1 Input Voltage vs. Temperature



Typical Performance Characteristics (continued)




Figure 23. Logic 0 Input Voltage vs. Supply Voltage





Figure 25. VCC UVLO vs. Temperature







Figure 26. Offset Supply Leakage Current vs. Temperature



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.






SO-28 (Type TH)						
Dim	Min	Min Max Typ				
Α		2.65				
A1	0.10	0.30				
A2	2.25	2.35	2.30			
A3	0.97	0.97 1.07 1.02				
b	0.39 0.48					
С	0.25	0.25 0.31				
D	17.80 18.20 18.0					
E	10.10	10.10 10.50 10.30				
E1	7.30	7.30 7.70 7.50				
е		1.27 BS	С			
L	0.70	0.70 1.00				
L1	1.40 BSC					
θ	0°	8°				
All	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.





Dimensions	Value (in mm)
C	1.270
Х	0.680
X1	17.190
Y	2.200
Y1	11.300

Note: For high-voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' provided Diodes' Standard Terms and Conditions of Sale products are subject to (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com