



N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{SSS}	R _{SS(ON)} T _{py}	I _{S Max} T _A = +25°C
14.5V	4.8mΩ @ V _{GS} = 3.8V	16.5A

Description

This new generation MOSFET is designed to minimize the on-state resistance ($R_{SS(ON)}$) yet maintain superior switching performance, which makes it ideal for high-efficiency power management applications.

Applications

- Battery Management
- Load Switch
- Battery Protection

Features


- CSP with Footprint 2.70mm × 1.81mm
- Height = 0.21mm for Low Profile
- ESD Protection of Gate
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
 - For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.


 https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Case: X3-DSN2718-6
- Terminal Connections: See Diagram Below
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish—NiAu or NiPdAu.
 Solderable per MIL-STD-202, Method 208 @4
- Weight: 0.0026 grams (Approximate)







Equivalent Circuit


Ordering Information (Note 4)

-			
	Part Number	Case	Packaging
	DMN15M3UCA6-7	X3-DSN2718-6	3000/Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



J2 = Product Type Marking Code YM = Date Code Marking Y or \overline{Y} = Year (ex: H = 2020) M or \overline{M} = Month (ex: 9 = September)

Date Code Key

Year	2019	2020	20)21	2022	2023	3	20	24	2025	202	26	2027
Code	G	Н		I	J	K		L	_	М	N		0
Month	Jan	Feb	Mar	Apr	May	Jun	Ju	ıl	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7		8	9	0	N	D



Maximum Ratings ($@T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit				
Source-Source Voltage	Source-Source Voltage						
Gate-Source Voltage			V_{GSS}	±12	V		
Continuous Source Current (Note 5) V _{GS} = 4.5V	Steady State	$T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$	Is	16.5 13.5	А		
Continuous Source Current (Note 5) V _{GS} = 2.5V	Is	14.2 11.3	А				
Pulsed Source Current (Note 6)	I _{SM}	80	A				

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 7)	P_{D}	1.0	W
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 7)	$R_{\Theta JA}$	124.6	°C/W
Power Dissipation (Note 5)	P_{D}	2.4	W
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 5)	$R_{\Theta JA}$	51.5	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition		
OFF CHARACTERISTICS (Note 8)								
Source-Source Breakdown Voltage	BVsss	14.5	_	_	V	$V_{GS} = 0V$, $I_S = 1mA$		
Zero Gate Voltage Drain Current T _J = +25°C	I _{SSS}	_	_	1	μΑ	V _{SS} = 10V V _{GS} = 0V		
Gate-Source Leakage	I _{GSS}	_	_	±10	μA	$V_{GS} = \pm 8V, V_{SS} = 0V$		
ON CHARACTERISTICS (Note 8)								
Gate Threshold Voltage	$V_{GS(TH)}$	0.5	0.9	1.3	V	Vss = 6V, Is = 1mA		
		3.5	4.6	5.8		$V_{GS} = 4.5V, I_S = 3A$		
		3.6	4.7	5.9		$V_{GS} = 4.0V, I_S = 3A$		
Static Source-Source On-Resistance	Rss(ON)	3.8	4.8	6.2	mΩ	V _{GS} = 3.8V, I _S = 3A		
	25(21)	3.8	5.1	6.9		V _{GS} = 3.1V, I _S = 3A		
		3.9	5.8	8.0		V _{GS} = 2.5V, I _S = 3A		
Diode Forward Voltage	V _{SS}	_	0.7	1.2	V	V _{GS} = 0V, I _S = 3A		
DYNAMIC CHARACTERISTICS (Note 9)			•	•				
Input Capacitance	C _{iss}		2360	_		24 224		
Output Capacitance	Coss	_	666	_	pF	$V_{SS} = 6V, V_{GS} = 0V,$ f = 1.0MHz		
Reverse Transfer Capacitance	C _{rss}	_	325	_		1 - 1.01/11/12		
Total Gate Charge	Qg	_	35.2	_				
Gate-Source Charge	Q _{gs}	_	7.0	_		$V_{SS} = 6V, V_{GS} = 4.5V,$		
Gate-Drain Charge	Q _{gd}	_	8.3	_	nC	I _S = 18A		
Gate Charge at V _{TH}	Q _{g(TH)}	_	4.2	_				
Turn-On Delay Time	t _{D(ON)}	_	615	_				
Turn-On Rise Time	t _R	_	1447	_		$V_{SS} = 6V, V_{GS} = 4.5V,$		
Turn-Off Delay Time	t _{D(OFF)}	_	2736	_	ns	I _S = 3A		
Turn-Off Fall Time	t _F		3812	_				

Notes:

- Device mounted on FR-4 material with 1inch² (6.45cm²), 2oz. (0.071mm thick) Cu.
 Repetitive rating, pulse width limited by junction temperature.
 Device mounted on FR-4 PCB with minimum recommended pad layout, single sided.
- 8. Short duration pulse test used to minimize self-heating effect.
- 9. Guaranteed by design. Not subject to production testing.










Figure 3. Typical On-Resistance vs. Source Current and Gate Voltage




Figure 5. Typical On-Resistance vs. Source Current and Junction Temperature




Figure 2. Typical Transfer Characteristic




Figure 4. Typical Transfer Characteristic




Figure 6. On-Resistance Variation with Junction Temperature









Figure 7. On-Resistance Variation with Junction Temperature



V_{FSS}, SOURCE-SOURCE VOLTAGE (V)
Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

X3-DSN2718-6




X3-DSN2718-6							
Dim Min Max Typ							
Α	0.16	0.26	0.21				
b	0.27	0.33	0.30				
D	2.65	2.75	2.70				
Е	1.76	1.86	1.81				
e 0.62 0.68 0.65							
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

X3-DSN2718-6



Dimensions	Value (in mm)		
С	0.65		
D	0.30		



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com