

6600W SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSOR

Product Summary (@TA = +25°C)

P _{PK}	I _{FSM} (A)	V _{RWM} (V)	PM _(AV)
6600W	700	10 to 43	W8

Description and Applications

Suitable to protect sensitive circuits against surges defined in ISO7637-2 and against load dump surge according to ISO16750-2.

Compliance with following standards:

- ISO 16750-2, Pulse A and Pulse B
- ISO 7637-2 (Note 5)
 Pulse 1, Pulse 2a, Pulse 3a, Pulse 3b

Features and Benefits

- 6600W Peak Pulse Power Dissipation
- T_J = +175°C Capability Suitable for High Reliability
- Available in Unidirectional Polarity Only
- High Current Capability
- Excellent High-Temperature Stability
- Meets ISO7637-2 Surge Capability
- Meets ISO16750-2 Surge Specification
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part.
 A listing can be found at

https://www.diodes.com/products/automotive/automotive-products/.

- This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.
 - https://www.diodes.com/quality/product-definitions/
- An Automotive-Compliant Part is Available Under Separate Datasheet (DM8W10AQ-DM8W43AQ)


Mechanical Data

- Package: DO-218
- Package Material: Molded Plastic.
 - UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead-Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208 (23)
- Polarity Indicator: Heatsink is Anode
- Weight: 2.74 grams (Approximate)

DO-218 (Type E)



Top View



Pin Information

Ordering Information (Note 4)

Part Number	Qualification	Package	Packing		
Part Number	Qualification	Package	Qty. Carrie		
DM8WxxA-13	AEC-Q101	DO-218 (Type E)	750	Tape & Reel	

x = Device Voltage, e.g., DM8W10A-13

Notes:

1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
- 5. Not applicable to parts with stand-off voltage lower than the average battery voltage (13.5V).



Marking Information

Pin1



M8WxxA = Product Type Marking Code (i.e. M8W18A for DM8W18A-13)

☐☐ = Manufacturers' Code Marking

aa: Wafer source code

y: Year (M=2022)

m: Month (1 – C) d: Date (1 – V) cc: Lot serial number

Bar Denotes Cathode Pin, Circle Denotes Anode

Date Code Key

Year	2018	2019	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	I	J	K	L	М	N	0	Р	Q	R	S	Т
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	Α	В	С
Date	1	2	3		9	10	11	12		29	30	31
Code	1	2	3		9	Α	В	С		Т	U	V

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Peak Pulse Power Dissipation	10/1000µs Waveform	P _{PK}	6600 5200	
(Non Repetitive Current Pulse Derated above T _A = +25°C) (Note 6)	10/10000µs Waveform			W
Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Loa	I _{FSM}	700	А	
Steady State Power Dissipation @ T _C = +25°C	PM _(AV)	8.0	W	

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Typical Thermal Resistance, Junction to Case	Rejc	0.9	°C/W
Operating Temperature Range	TJ	-55 to +175	°C
Storage Temperature Range	Tstg	-55 to +175	°C

Notes:

^{6.} Valid provided that terminals are kept at ambient temperature.

^{7.} Measured on 8.3ms single half sine-wave or equivalent square wave. Duty cycle = 4 pulses per minute maximum.




Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Part Number	Reverse Standoff Voltage	Vol	kdown tage r (Note 8)	Test Current	Max. Reverse Leakage @ VRWM	Max. Clamping Voltage @ IPP	Max. Peak Pulse Current I _{PP} at 10/1000μs (Note 9)	Maximum Leakage at Vwm T _J = +175°C
	V _{RWM} (V)	Min (V)	Max (V)	I _T (mA)	I _R (μA)	V _C (V)	(A)	I _D (μ A)
DM8W10A	10	11.1	12.3	5	15	17.0	388	250
DM8W11A	11	12.2	13.5	5	10	18.2	363	150
DM8W12A	12	13.3	14.7	5	10	19.9	332	150
DM8W13A	13	14.4	15.9	5	10	21.5	307	150
DM8W14A	14	15.6	17.2	5	10	23.2	284	150
DM8W15A	15	16.7	18.5	5	10	24.4	270	150
DM8W16A	16	17.8	19.7	5	10	26.0	254	150
DM8W17A	17	18.9	20.9	5	10	27.6	239	150
DM8W18A	18	20.0	22.1	5	10	29.2	226	150
DM8W20A	20	22.2	24.5	5	10	32.4	204	150
DM8W22A	22	24.4	26.9	5	10	35.5	186	150
DM8W24A	24	26.7	29.5	5	10	38.9	170	150
DM8W26A	26	28.9	31.9	5	10	42.1	157	150
DM8W28A	28	31.1	34.4	5	10	45.4	145	150
DM8W30A	30	33.3	36.8	5	10	48.4	136	150
DM8W33A	33	36.7	40.6	5	10	53.3	124	150
DM8W36A	36	40.0	44.2	5	10	58.1	114	150
DM8W40A	40	44.4	49.1	5	10	64.5	102	150
DM8W43A	43	47.8	52.8	5	10	69.4	95.1	150

8. V_{BR} measured with I_{T} current pulse = 10ms to 15ms. 9. Refer to Figure 3 for the waveform. Notes:








Fig. 3 - Pulse Waveform




Fig. 5 Typical Transient Thermal Impedance






Fig. 2 Load Dump Power Characteristics (10ms Exponential Waveform)




WAVEFORM
Fig. 4 Reverse Power Capability







Package Outline Dimensions

DO-218 (Type E)






DO-218 (Type E)						
Dim	Min	Max	Тур			
Α	4.70	5.70				
A1	4.70	5.25	5.00			
A2	3.45	4.26	3.95			
А3	1.70	2.50	2.00			
A4	2.58	3.55	3.10			
b	2.30	3.00				
С	0.45	0.90				
D	13.20	13.80	13.50			
D1	8.70	9.30	9.00			
D2	9.70	10.30	10.00			
Е	8.20	8.80	8.50			
E1	9.50	10.50				
Н	15.00	16.00	15.50			
L	1.50	2.50	2.00			
All	Dimensi	ons in	mm			



Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

DO-218 (Type E)



Dimensions	value
Dillielisions	(in mm)
G	3.30
Х	3.50
X1	11.00
Υ	3.00
Y1	9.50
Y2	15.80



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Conditions of Diodes products are provided subject to Diodes' Standard Terms and Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com