

DMN3065LW

N-CHANNEL ENHANCEMENT MODE FIELD EFFECT TRANSISTOR

Product Summary

BV _{DSS}	R _{DS(ON)}	Package	I _{D max} T _A = +25°C
	$52m\Omega$ @ $V_{GS} = 10V$		
30V	65mΩ @ V _{GS} = 4.5V	SOT323	4A
	$85m\Omega @ V_{GS} = 2.5V$		

Features

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Applications

- DC-DC Converters
- Power Management Functions
- · Battery Operated Systems and Solid-State Relays


Mechanical Data

- Case: SOT323
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Alloy 42 Leadframe.
 Solderable per MIL-STD-202, Method 208 (3)
- Terminal Connections: See Diagram
- Weight: 0.006 grams (Approximate)


SOT323



Top View



Pin Configuration Top View



Equivalent Circuit


Ordering Information (Note 4)

Part Number	Case	Packaging
DMN3065LW-7	SOT323	3000/Tape & Reel
DMN3065LW-13	SOT323	10000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



N35 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: G = 2019) M = Month (ex: 9 = September)

Date Code Key

Year	2018	20	19	2020	2021	20	22	2023	2024	20	25	2026
Code	F		9	Н	- 1	,	J	K	L	N	Λ	N
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Drain Source Voltage	V _{DSS}	30	V
Gate-Source Voltage	V _{GSS}	±12	V
Drain Current (Note 5)	I _D	4	А
Body-Diode Continuous Current (Note 5)	I _S	1	А

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Total Power Dissipation (Note 5)	P_{D}	770	mW
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 5)	$R_{ heta JA}$	162	°C/W
Operating and Storage Temperature Range	$T_{J_i}T_{STG}$	-55 to +150	°C


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition		
OFF CHARACTERISTICS (Note 6)								
Drain-Source Breakdown Voltage	BV _{DSS}	30			V	$V_{GS} = 0V, I_D = 250\mu A$		
Zero Gate Voltage Drain Current	I _{DSS}	_		1	μA	$V_{DS} = 30V, V_{GS} = 0V$		
Gate-Body Leakage	I _{GSS}	_		±100	nA	$V_{GS} = \pm 12V$, $V_{DS} = 0V$		
ON CHARACTERISTICS (Note 6)	ON CHARACTERISTICS (Note 6)							
Gate Threshold Voltage	V _{GS(TH)}	0.5		1.5	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$		
				52		V _{GS} = 10V, I _D = 4A		
Static Drain-Source On-Resistance	R _{DS(ON)}	_	_	65	mΩ	$V_{GS} = 4.5V, I_D = 3A$		
			1	85		$V_{GS} = 2.5V, I_D = 2A$		
Source-Drain Diode Forward Voltage	V_{SD}	_		1.2	V	$V_{GS} = 0V, I_{S} = 2.0A$		
DYNAMIC CHARACTERISTICS (Note 7)								
Input Capacitance	C _{iss}	_	465	_	pF			
Output Capacitance	Coss	_	49.5	_	pF	$V_{DS} = 15V, V_{GS} = 0V, f = 1.0MHz$		
Reverse Transfer Capacitance	C _{rss}	_	43.8		pF			
Gate Resistance	Rg	_	2.3		Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$		
Total Gate Charge (V _{GS} = 10V)	Qg	_	11.7		nC	V _{DS} = 15V, I _D = 4A		
Total Gate Charge (V _{GS} = 4.5V)	Qg	_	5.5		nC			
Gate-Source Charge	Qgs	_	1.1		nC	V _{DS} = 15V, I _D = 4A		
Gate-Drain Charge	Q_{gd}	_	1.8		nC			
Turn-On Delay Time	t _{D(ON)}	_	1.9		ns			
Turn-On Rise Time	t _R	_	1.6	_	ns	V _{DD} = 15V, V _{GEN} = 10V,		
Turn-Off Delay Time	t _{D(OFF)}		10.3	_	ns	$R_{GEN} = 3\Omega$, $R_L = 3.75\Omega$		
Turn-Off Fall Time	t _F		2.0		ns			


5. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper pad layout.6. Short duration pulse test used to minimize self-heating effect.7. Guaranteed by design. Not subject to production testing.




















Figure 6 On-Resistance Variation with Temperature











Figure 7 Gate Threshold Variation vs. Junction Temperature











Figure 11. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT323




	SO	T323				
Dim	Min	Max	Тур			
A 1	0.00	0.10	0.05			
A2	0.90	1.00	0.95			
b	0.25	0.40	0.30			
С	0.10	0.18	0.11			
D	1.80	2.20	2.15			
Е	2.00	2.20	2.10			
E1	1.15	1.35	1.30			
е	0.650 BSC					
e1	1.20	1.40	1.30			
F	0.375	0.475	0.425			
L	0.25	0.40	0.30			
а	0°	8°				
All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT323



Dimensions	Value (in mm)
С	0.650
G	1.300
Х	0.470
Υ	0.600
Y1	2.500



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com