



April 2020

N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)} max	I _D max T _A = +25°C
001/	$60m\Omega$ @ $V_{GS} = 10V$	2.6A
30V	$100 \text{m}\Omega$ @ $V_{GS} = 4.5 \text{V}$	2.1A

Features and Benefits

- Low On-Resistance
- Low Input Capacitance
- Fast Switching Speed
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Description and Applications

This MOSFET has been designed to minimize the on-state resistance (RDS(ON)) yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- General Purpose Interfacing Switch
- **Power Management Functions**
- **DC-DC Converters**
- Analog Switch


Mechanical Data

- Case: SOT323
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Diagram
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.027 grams (Approximate)




Top View

SOT323



Equivalent Circuit



Top View


Ordering Information (Note 4)

Part Number	Case	Packaging
DMN3060LW-7	SOT323	3,000/Tape & Reel
DMN3060LW-13	SOT323	10,000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



BA3 = Product Type Marking Code YM or $\overline{Y}M$ = Date Code Marking Y or \overline{Y} = Year (ex: H = 2020) M = Month (ex: 9 = September)

Date Code Kev

Year	2019	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030
Code	G	Н	I	J	K	L	М	N	0	Р	R	S
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec



Maximum Ratings (@ $T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	VDSS	30	V		
Gate-Source Voltage	V_{GSS}	±12	V		
Continuous Drain Current (Note 6) Vgs = 4.5V	П	2.6 2.1	А		
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	IDM	18	Α		
Maximum Body Diode Forward Current (Note 5)			Is	0.68	Α

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 5)		PD	0.5	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	RθJA	251	°C/W
Total Power Dissipation (Note 6)		PD	0.64	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	195	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Cumala al	Min	T	May	11	Toot Condition
Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)	ı	1	1		1	
Drain-Source Breakdown Voltage	BV _{DSS}	30	_	_	V	$V_{GS} = 0V, I_{D} = 250\mu A$
Zero Gate Voltage Drain Current @Tc = +25°C	IDSS	_	_	1.0	μΑ	$V_{DS} = 30V$, $V_{GS} = 0V$
Gate-Source Leakage	Igss	_	_	±100	nA	$V_{GS} = \pm 12V$, $V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	VGS(TH)	0.7	_	1.8	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$
Otatia Brain Oceana Oc Basistana	1	_	48	60	0	V _G S = 10V, I _D = 3.1A
Static Drain-Source On-Resistance	R _{DS(ON)}	_	51	100	mΩ	V _G S = 4.5V, I _D = 2A
Diode Forward Voltage	VsD	_	0.8	1.2	V	V _G S = 0V, I _S = 1A
DYNAMIC CHARACTERISTICS (Note 8)						•
Input Capacitance		_	395	_	pF	N 451/ N 01/
Output Capacitance	Coss	_	39	_	pF	V _{DS} = 15V, V _{GS} = 0V, -f = 1.2MHz
Reverse Transfer Capacitance	Crss	_	26	_	pF	1 = 1.21/11 12
Gate Resistance	R_g	_	3.1	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$
Total Gate Charge	Qg	_	5.6	_	nC	V 45V V 40V
Gate-Source Charge	Qgs	_	0.2	_	nC	$V_{GS} = 4.5V, V_{DS} = 10V,$ $I_{D} = 6A$
Gate-Drain Charge	Q_{gd}	_	1.8	_	nC	ID = 6A
Turn-On Delay Time	t _{D(ON)}		5.8	_	ns	
Turn-On Rise Time	t _R	_	30.8	_	ns	V _{DD} = 10V, V _{GS} = 15V,
Turn-Off Delay Time		_	18.3	_	ns	$R_L = 4.7\Omega$, $R_G = 3\Omega$
Turn-Off Fall Time	t _F	_	2.7	_	ns	

- 5. Device mounted on FR-4 substrate PC board, with minimum recommended pad layout.6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.7. Short duration pulse test used to minimize self-heating effect.
- 8. Guaranteed by design. Not subject to product testing.






Figure 5. Typical On-Resistance vs. Drain

Current and Junction Temperature

Figure 6. On-Resistance Variation with Junction

Temperature


100 125


f = 1MHz

150

30







2

 $V_{GS}(V)$

4

2

0

0

100







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT323




SOT323						
Dim	Min	Max	Тур			
A1	0.00	0.10	0.05			
A2	0.90	1.00	0.95			
b	0.25	0.40	0.30			
С	0.10	0.18	0.11			
D	1.80	2.20	2.15			
E	2.00	2.20	2.10			
E1	1.15	1.35	1.30			
е	C).650 B	SC			
e1	1.20	1.40	1.30			
F	0.375	0.475	0.425			
L	0.25	0.40	0.30			
а	0°	8°				
All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT323



Dimensions	Value (in mm)
С	0.650
G	1.300
Х	0.470
Y	0.600
Y1	2.500

April 2020

© Diodes Incorporated



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com