



N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)} max	I _D max T _A = +25°C
001/	2Ω @ $V_{GS} = 4.5V$	000 4
60V	2.5Ω @ V _{GS} = 2.5V	320mA

Description

This MOSFET is designed to minimize the on-state resistance (Rds(on)) and yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Applications

- Motor Control
- Power Management Functions

https://www.diodes.com/quality/product-definitions/

Mechanical Data

Case: SOT523

Features

Low On-Resistance: R_{DS(ON)} Low Gate Threshold Voltage Low Input Capacitance Fast Switching Speed Low Input/Output Leakage ESD Protected Up To 1kV

- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020

us or your local Diodes representative.

 Terminals: Finish — Matte Tin Annealed over Alloy 42 Leadframe. Solderable per MIL-STD-202, Method 208(63)

Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2) Halogen and Antimony Free. "Green" Device (Note 3)

For automotive applications requiring specific change control

manufactured in IATF 16949 certified facilities), please contact

(i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and


- Terminal Connections: See Diagram
- Weight: 0.002 grams (Approximate)






SOT523

Top View






Ordering Information (Note 4)

Part Number	Case	Packaging		
DMN62D0UT-7	SOT523	3,000/Tape & Reel		
DMN62D0UT-13	SOT523	10,000/Tape & Reel		

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



TK9 = Product Type Marking Code YM = Date Code Marking Y or \overline{Y} = Year (ex: H = 2020) M = Month (ex: 9 = September)

Date Code Key

Year	2015		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	С		Н	ı	J	K	L	М	N	0	Р	R
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Characteristic		Symbol	Value	Unit
Drain-Source Voltage	VDSS	60	V	
Gate-Source Voltage	V _{GSS}	±20	V	
Continuous Drain Current (Note 6) $V_{GS} = 4.5V$ Steady $T_A = +25^{\circ}C$ State $T_A = +70^{\circ}C$		lD	320 260	mA
Maximum Continuous Body Diode Forward Currer	nt (Note 6)	Is	320	mA
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1	%)	IDM	1.2	Α

Thermal Characteristics (@TA = +25°C unless otherwise specified.)


Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 5)		PD	230	mW
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	R _{0JA}	546	°C/W
Total Power Dissipation (Note 6)		PD	340	mW
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	Reja	377	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C


Electrical Characteristics (@T_A = +25°C unless otherwise specified.)

		,			,	
Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						
Drain-Source Breakdown Voltage	BVDSS	60	_	_	V	$V_{GS} = 0V, I_{D} = 10\mu A$
Zero Gate Voltage Drain Current	I _{DSS}	1	_	1.0	μΑ	$V_{DS} = 60V, V_{GS} = 0V$
Gate-Source Leakage	Igss	_	_	±10	μΑ	$V_{GS} = \pm 20V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	Vgs(TH)	0.5	_	1.0	V	V _{DS} = 10V, I _D = 250µA
			1.2	2.0		$V_{GS} = 4.5V, I_D = 0.1A$
Static Drain-Source On-Resistance	R _{DS} (ON)	_	1.4	2.5	Ω	$V_{GS} = 2.5V, I_{D} = 0.05A$
			1.8	3.0		$V_{GS} = 1.8V, I_{D} = 0.05A$
Forward Transconductance	Y _{fs}	_	1.8	_	S	$V_{DS} = 10V, I_D = 0.2A$
Diode Forward Voltage	VsD	_	0.8	1.3	V	V _{GS} = 0V, I _S = 115mA
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	C _{iss}	_	32	_	pF	
Output Capacitance	Coss	_	3.9	_	pF	V _{DS} = 30V, V _{GS} = 0V f = 1.0MHz
Reverse Transfer Capacitance	C _{rss}	_	2.4	_	pF	1 = 1.01/11 12
Gate Resistance	Rg	_	101	_	Ω	$f = 1MHz$, $V_{GS} = 0V$, $V_{DS} = 0V$
Total Gate Charge	Qg	_	0.5	_	nC	45)/)/ 40)/
Gate-Source Charge	Qgs	_	0.09	_	nC	$V_{GS} = 4.5V, V_{DS} = 10V,$
Gate-Drain Charge	Qgd	_	0.09	_	nC	ID = 250mA
Turn-On Delay Time	t _{D(ON)}	_	2.4	_	ns	
Turn-On Rise Time	tR	_	2.5	_	ns	V _{DD} = 30V, V _{GS} = 10V,
Turn-Off Delay Time	t _{D(OFF)}	_	22.6	_	ns	$R_G = 25\Omega$, $I_D = 200mA$
Turn-Off Fall Time	t _F	_	12.5	_	ns	

- 5. Device mounted on FR-4 PCB, with minimum recommended pad layout.
- 6. Device mounted on 1" \times 1" FR-4 PCB with high coverage 2oz. Copper, single sided.
- 7. Short duration pulse test used to minimize self-heating effect. 8. Guaranteed by design. Not subject to product testing.










Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 5. Typical On-Resistance vs. Drain Current and Temperature




Figure 2. Typical Transfer Characteristic




Figure 4. Typical Transfer Characteristic




Figure 6. On-Resistance Variation with Junction Temperature






Figure 7. On-Resistance Variation with Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT523




SOT523						
Dim	Min	Max	Тур			
A1	0.00	0.10	0.05			
A2	0.60	0.80	0.75			
A3	0.45	0.65	0.50			
b	0.15	0.30	0.22			
С	0.10	0.20	0.12			
D	1.50	1.70	1.60			
Е	1.45	1.75	1.60			
E1	0.75	0.85	0.80			
е	0.50 BSC					
e1	0.90	1.10	1.00			
L	0.20	0.40	0.33			
а	0°		8°			
All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT523



Dimensions	Value (in mm)
С	1.29
Х	0.40
X1	0.70
Υ	0.51
Y1	1.80



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

7 of 7

www.diodes.com

Copyright © 2020, Diodes Incorporated

www.diodes.com