



DMN3401LV

Product Summary

BV _{DSS}	Rds(on) Max	I _D Max T _A = +25°C
001/	0.4Ω @ V _{GS} = 10V	1.1A
30V	0.7Ω @ V _{GS} = 4.5V	0.8A

Description

This MOSFET is designed to minimize the on-state resistance (R_{DS(ON)}) yet maintain superior switching performance, making it ideal for high efficiency power management applications.

Applications

- Motor controls
- Power management functions
- **DC-DC** converters
- Backlighting

DUAL N-CHANNEL ENHANCEMENT MODE MOSFET

Features and Benefits

- Low On-Resistance
- Low Input Capacitance
- Fast Switching Speed
- ESD Protected Gate
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/guality/product-definitions/

Mechanical Data

Package: SOT563 •

D1

S1


- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 @3)
- Weight: 0.006 grams (Approximate)






SOT563

Top View





Top View Pin Out

Ordering Information (Note 4)

Part Number	Package	Marking	Reel Size (inches)	Tape Width (mm)	Pac	king
Fait Nullibei	гаскауе	Warking	Reel Size (Inches)		Qty.	Carrier
DMN3401LV-7	SOT563	BG3	7	8	3,000	Reel
DMN3401LV-13	SOT563	BG3	13	8	10,000	Reel

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free


3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

G1



Marking Information



 $\begin{array}{l} BG3 = Product Type Marking Code \\ \overline{Y}M = Date Code Marking \\ \overline{Y} = Year (ex: J = 2022) \\ M = Month (ex: 9 = September) \end{array}$

|--|

Year	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	I	J	К	L	М	Ν	0	Р	R	S	Т	U
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	Ν	D

Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Drain-Source Voltage	VDSS	30	V		
Gate-Source Voltage	Vgss	±20	V		
Continuous Drain Current (Note 5) $V_{GS} = 4.5V$ State $T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$			lD	0.8 0.7	A
Maximum Continuous Body Diode Forward Currer	ls	0.9	А		
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1	%)	Ідм	4.5	А	

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 6)	T _A = +25°C	PD	0.49	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	R _{0JA}	257	°C/W
Total Power Dissipation (Note 5)	T _A = +25°C	PD	0.81	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	Reja	155	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C

Notes: 5. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.

6. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Turn	Max	Unit	Test Condition
	Symbol	WIIN	Тур	Wax	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)				1		
Drain-Source Breakdown Voltage	BVDSS	30	—	—	V	$V_{GS} = 0V, I_D = 1mA$
Zero Gate Voltage Drain Current @T	c = +25°C IDSS	_	_	1	μA	$V_{DS} = 30V, V_{GS} = 0V$
Gate-Source Leakage	lgss	—	—	±10	μA	$V_{GS} = \pm 20V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	Vgs(th)	0.8	_	1.6	V	$V_{DS} = 3V, I_{D} = 100 \mu A$
Static Drain-Source On-Resistance	Proven	_	0.16	0.4	Ω	Vgs = 10V, ID = 0.59A
Static Drain-Source On-Resistance	R _{DS(ON)}		0.22	0.7	12	$V_{GS} = 4.5 V, I_D = 0.2 A$
Diode Forward Voltage	Vsd		0.7	1.2	V	$V_{GS} = 0V, I_{S} = 0.1A$
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance			50		pF	
Output Capacitance	Coss	_	12	_	pF	V _{DS} = 15V, V _{GS} = 0V f = 1.0MHz
Reverse Transfer Capacitance	Crss	_	10		pF	
Total Gate Charge (V _{GS} = 4.5V)		_	0.5	_	nC	
Total Gate Charge (V _{GS} = 10V)	Qg	_	1.2		nC	
Gate-Source Charge	Qgs		0.2		nC	$V_{DS} = 10V, I_D = 250mA$
Gate-Drain Charge	Qgd		0.1		nC	
Turn-On Delay Time	td(on)	_	3.5		ns	
Turn-On Rise Time	t _R	_	3.3		ns	Vgs = 10V, Vds = 30V
Turn-Off Delay Time	tD(OFF)		16.8		ns	I _D = 100mA, R _G = 25Ω
Turn-Off Fall Time	tF		13.8		ns	7

7. Short duration pulse test used to minimize self-heating effect.8. Guaranteed by design. Not subject to product testing. Notes:



DMN3401LV









Figure 11. Gate Charge








Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



	SOT563									
Dim	Min	Max	Тур							
Α	0.55	0.60								
b	0.15	0.30	0.20							
c	0.10	0.18	0.11							
D	1.50	1.70	1.60							
Е	1.55	1.70	1.60							
E1	1.10	1.25	1.20							
е			0.50							
e1	0.90	1.10	1.00							
L	0.10	0.30	0.20							
а	8°	9°	7°							
All	Dimens	sions in	mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	0.500
C1	1.270
G	0.600
Х	0.300
X1	1.300
Y	0.670
Y1	1.940

SOT563



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' provided to Diodes' Standard Terms and Conditions of Sale products are subject (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com