



N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _A = +25°C
60V	5Ω @ V _{GS} = 10V	0.21A
600	6Ω @ V _{GS} = 5V	0.20A

Description

This MOSFET is designed to minimize the on-state resistance (R_{DS(ON)}) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Applications

- Motor Control
- Power Management Functions

Features

- Low On-Resistance: R_{DS(ON)}
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- . ESD Protected up to 1kV
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/

Mechanical Data


- Case: SOT523
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Alloy 42 Leadframe. Solderable per MIL-STD-202, Method 208 (§3)
- Terminal Connections: See Diagram
- Weight: 0.002 grams (Approximate)






SOT523

Top View







Top View Pin Out Configuration

Ordering Information (Note 4)


Part Number	Case	Packaging
DMN65D8LT-7	SOT523	3000/Tape & Reel
DMN65D8LT-13	SOT523	10000/Tape & Reel

Notes: 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3).compliant. All applicable RoHS exemptions applied.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information



58D = Product Type Marking Code YM = Date Code Marking Y or \overline{Y} = Year (ex: H = 2020) M = Month (ex: 9 = September)

Date Code Key

Year	2014		2019	2020	20	021	2022	202	3	2024	2025	2026	2027	2028
Code	В		G	Н		I	J	K		L	М	N	0	Р
N	Month	Ja	n Feb	Mar	Apr	May	Jun	Jul	Aug	g Sep	Oct	N	ov	Dec

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit		
Drain-Source Voltage		V _{DSS}	60	V		
Gate-Source Voltage		V_{GSS}	±20	V		
Continuous Prais Current (Note 6) // F 0)/	Steady	T _A = +25°C	I _D	210	mA	
Continuous Drain Current (Note 6) V _{GS} = 5.0V	State	T _A = +70°C		170	IIIA	
Maximum Continuous Body Diode Forward Currer	nt (Note 6)		Is	210	mA	
Pulsed Drain Current (10µs Pulse, Duty Cycle = 19	%)	I _{DM}	0.7	Α		
Pulsed Source Current (10µs Pulse, Duty Cycle =	1%)	I _{SM}	0.7	А		

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)		P_{D}	300	mW
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	$R_{\theta JA}$	426	°C/W
Total Power Dissipation (Note 6)		P _D	360	mW
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	351	°C/W
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +150	°C




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)	-						
Drain-Source Breakdown Voltage	BV _{DSS}	60	_	_	V	$V_{GS} = 0V, I_D = 10\mu A$	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1.0	μΑ	$V_{DS} = 60V, V_{GS} = 0V$	
Gate-Source Leakage	I _{GSS}	_	_	±10	μΑ	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	V _{GS(TH)}	1.2	_	2.0	V	VDS = VGS, ID = 250μA	
Static Drain-Source On-Resistance	D		2.0	5.0	0	$V_{GS} = 10V, I_D = 0.115A$	
Static Drain-Source Off-Nesistance	R _{DS(ON)}		2.2	6.0	12	$V_{GS} = 5V, I_D = 0.115A$	
DYNAMIC CHARACTERISTICS (Note 8)							
Input Capacitance	C _{iss}	_	24	_		.,	
Output Capacitance	Coss	_	2.8	_	pF	$V_{DS} = 25V, V_{GS} = 0V$ f = 1.0MHz	
Reverse Transfer Capacitance	C _{rss}	_	1.8	_		1 = 1.000112	
Gate Resistance	R_g	_	50	_	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1.0MHz$	
Total Gate Charge	Qg	_	0.4	_			
Gate-Source Charge	Q_{gs}	_	0.12	_	nC	$V_{DD} = 30V, V_{GS} = 4.5V, I_{D} = 150mA$	
Gate-Drain Charge	Q _{gd}	_	0.14	_			
Turn-On Delay Time	t _{D(ON)}	_	2.0	_			
Turn-On Rise Time	t _R		1.9			$V_{GS} = 10V, V_{DD} = 30V, R_g = 25\Omega,$	
Turn-Off Delay Time	t _{D(OFF)}		9.5	_	ns	$I_D = 0.2A$	
Turn-Off Fall Time	t _F		4.3	_			

Notes:

- 5. Device mounted on FR-4 PCB, with minimum recommended pad layout
 6. Device mounted on 1" x 1" FR-4 PCB with high coverage 2oz. Copper, single sided.
 7. Short duration pulse test used to minimize self-heating effect.
- 8. Guaranteed by design. Not subject to product testing.








Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage






Figure 5. Typical On-Resistance vs. Drain Current and Junction Temperature








Figure 6. On-Resistance Variation with Junction Temperature






Figure 7. On-Resistance Variation with Junction Temperature




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT523




	SOT523						
Dim	Min	Max	Тур				
A1	0.00	0.10	0.05				
A2	0.60	0.80	0.75				
A3	0.45	0.65	0.50				
b	0.15	0.30	0.22				
С	0.10	0.20	0.12				
D	1.50	1.70	1.60				
Е	1.45	1.75	1.60				
E1	0.75	0.85	0.80				
е	0.50 BSC						
e1	0.90	1.10	1.00				
L	0.20	0.40	0.33				
а	0°		8°				
A	All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT523



Dimensions	Value (in mm)
С	1.29
Х	0.40
X1	0.70
Y	0.51
Y1	1.80



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com