



60V +175°C N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _C = +25°C
60//	7.3mΩ @ V _{GS} = 10V	95A
60V	15mΩ @ V _{GS} = 4.5V	67A

Description and Applications

This MOSFET is designed to minimize the on-state resistance (RDS(ON)) yet maintain superior switching performance, making it ideal for high-efficiency power-management applications.

- Power-management functions
- DC-DC converters
- Backlighting

Site 1:



Site 2:

PowerDI5060-8/SWP (Type UX)



Top View Bottom View

Features

- Rated to +175°C—Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switch (UIS) Test in Production
- Low R_{DS(ON)}—Minimizes Power Losses
- Low Q_q—Minimizes Switching Losses
- < 1.1mm Package Profile—Ideal for Thin Applications
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at


https://www.diodes.com/products/automotive/automotive-products/.

This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.

https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Package: PowerDI[®]5060-8
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram Below
- Terminals: Finish—Matte Tin Annealed over Copper Leadframe.
 Solderable per MIL-STD-202, Method 208 ©3
- Weight: 0.097 grams (Approximate)






S [] D
S [] D
Top View
Pin Configuration









Ordering Information (Note 4)

Part Number	Package	Packing		
Fait Number	Fackage	Qty.	Carrier	
DMNH6009SPS-13	PowerDI5060-8	2500	Tape & Reel	
DIMINH00093F3-13	PowerDI5060-8/SWP (Type UX)	2500	Tape & Reel	

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information





☐ ☐ Hanufacturer's Marking

NH6009SS = Product Type Marking Code

YYWW = Date Code Marking

YY or YY= Year (ex: 23 = 2023)

WW = Week Code (01 to 53)

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	VDSS	60	V	
Gate-Source Voltage	V_{GSS}	±20	V	
Continuous Drain Current (Note 5) V _{GS} = 10V	T _C = +25°C T _C = +100°C	ID	95 67	А
Pulsed Drain Current (380µs Pulse, Duty Cycle = 1%)		I _{DM}	380	Α
Maximum Continuous Body Diode Forward Current (Note 5)	Is	95	Α	
Pulsed Source Current (380µs Pulse, Duty Cycle = 1%)	I _{SM}	380	Α	
Avalanche Current, L = 0.1mH (Note 6)	las	56	Α	
Avalanche Energy, L = 0.1mH (Note 6)	Eas	226	mJ	

Thermal Characteristics

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 7)	P _D	1.6	W	
Thermal Resistance, Junction to Ambient (Note 7)	Steady State	Reja	95	°C/W
Total Power Dissipation (Note 8)	PD	3.3	W	
Thermal Resistance, Junction to Ambient (Note 8)	Steady State	Reja	46	°C/W
Thermal Resistance, Junction to Case (Note 5)	R ₀ JC	1.5	C/VV	
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C

Notes:

- 5. Thermal resistance from junction to soldering point (on the exposed drain pad).
- 6. I_{AS} and E_{AS} ratings are based on low frequency and duty cycles to keep $T_J = +25^{\circ}C$.
- 7. Device mounted on FR-4 PCB, with minimum recommended pad layout, single sided.
- 8. Device mounted on FR-4 substrate PCB, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.



Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 9)							
Drain-Source Breakdown Voltage	BVDSS	60	_	_	V	VGS = 0V, ID = 1mA	
Zero Gate Voltage Drain Current, T _J = +25°C	IDSS		_	1	μA	V _{DS} = 48V, V _{GS} = 0V	
Gate-Source Leakage	Igss	-	-	±100	nA	$V_{GS} = \pm 20V$, $V_{DS} = 0V$	
ON CHARACTERISTICS (Note 9)							
Gate Threshold Voltage	Vgs(TH)	1	2	3	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$	
Static Drain-Source On-Resistance	R _{DS(ON)}		4.6	7.3	mΩ	$V_{GS} = 10V, I_D = 50A$	
Static Drain-Source On-Resistance	R _{DS(ON)}		7.1	15	mΩ	$V_{GS} = 4.5V, I_D = 25A$	
Diode Forward Voltage	VsD		0.7	1.2	V	V _G S = 0V, I _S = 1.7A	
DYNAMIC CHARACTERISTICS (Note 10)							
Input Capacitance	C _{iss}		1882	_	pF		
Output Capacitance	Coss	_	374	_	pF	$V_{DS} = 30V, V_{GS} = 0V$ - f = 1MHz	
Reverse Transfer Capacitance	Crss	_	111	_	pF		
Gate Resistance	Rg		2.1	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$	
Total Gate Charge (V _{GS} = 4.5V)	Q_g	1	18.5	_	nC		
Total Gate Charge (V _{GS} = 10V)	Qg	_	37.3	_	nC	Vps = 30V. lp = 25A	
Gate-Source Charge	Qgs	_	5.0	_	nC	VDS = 30V, ID = 25A	
Gate-Drain Charge	Q_{gd}	_	11.2	_	nC		
Turn-On Delay Time	td(on)		5.7	_	ns		
Turn-On Rise Time	t _R		7.5	_	ns	$V_{GS} = 10V, V_{DS} = 30V$	
Turn-Off Delay Time	tD(OFF)	_	16.9	_	ns	$R_g = 3\Omega$, $I_D = 25A$	
Turn-Off Fall Time	t _F	_	6.3	_	ns		
Body Diode Reverse Recovery Time	trr	_	32	_	ns	15 - 35 A dl/dt - 100 A/us	
Body Diode Reverse Recovery Charge	Q _{RR}	_	30	_	nC	I _F = 25A, dI/dt = 100A/μs	


Notes:


^{9.} Short duration pulse test used to minimize self-heating effect.


^{10.} Guaranteed by design. Not subject to product testing.

















vs. Gate-Source Voltage







Figure 6 On-Resistance Variation with Temperature

















Figure 8 Gate Threshold Variation vs. Junction Temperature












Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site 1:


PowerDI5060-8




PowerDI5060-8					
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0.00	0.05	_		
b	0.33	0.51	0.41		
b2	0.200	0.350	0.273		
b3	0.40	0.80	0.60		
С	0.230	0.330	0.277		
D		5.15 BSC			
D1	4.70	5.10	4.90		
D2	3.70	4.10	3.90		
D3	3.90	4.30	4.10		
Е	(6.15 BSC	;		
E1	5.60	6.00	5.80		
E2	3.28	3.68	3.48		
E3	3.99	4.39	4.19		
е		1.27 BSC	;		
G	0.51	0.71	0.61		
K	0.51	-	-		
L	0.51	0.71	0.61		
L1	0.100	0.200	0.175		
М	3.235	4.035	3.635		
M1	1.00	1.40	1.21		
Θ	10°	12°	11°		
Θ1	6°	8°	7°		
All Dimensions in mm					

Site 2:

PowerDI5060-8/SWP (Type UX)



-D1-



PowerDI5060-8/SWP				
(Type UX)				
Dim	Min	Max	Тур	
Α	0.90	1.10	1.00	
A 1	0	0.05		
b	0.30	0.50	0.41	
b2	0.20	0.35	0.25	
b4	C).25REF		
С	0.230	0.330	0.277	
D	5	.15 BS0)	
D1	4.70	5.10	4.90	
D2	3.56	3.96	3.76	
D2a	3.78	4.18	3.98	
Е	6	.40 BS0)	
E1	5.60	6.00	5.80	
E2	3.46	3.86	3.66	
E2a	4.195	4.595	4.395	
е	1	.27BSC)	
k	1.05			
L	0.635	0.835	0.735	
La	0.635	0.835	0.735	
L1	0.200	0.400	0.300	
L1a	0.050REF			
L4	0.025	0.225	0.125	
M	3.205	4.005	3.605	
θ	10°	12°	11°	
θ1	6°	8°	7°	
All Dimensions in mm				

7 of 9 www.diodes.com




Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site 1:


PowerDI5060-8



Dimensions	Value (in mm)
С	1.270
G	0.660
G1	0.820
X	0.610
X1	4.100
X2	0.755
Х3	4.420
X4	5.610
Υ	1.270
Y1	0.600
Y2	1.020
Y3	0.295
Y4	1.825
Y5	3.810
Y6	0.180
Y7	6.610

Site 2:

PowerDI5060-8/SWP (Type UX)



Dimensions	Value (in mm)
С	1.270
G	0.660
G1	0.820
Х	0.610
X1	4.100
X2	5.190
Х3	4.420
Y	1.270
Y1	1.020
Y2	3.810
Y3	6.610



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com