



#### 55V 175°C N-CHANNEL ENHANCEMENT MODE MOSFET

## **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> Max T <sub>C</sub> = +25°C		
55V	$12m\Omega @ V_{GS} = 10V$	80A		
	$18m\Omega @ V_{GS} = 4.5V$	65A		

## **Features**

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching Ensures more Reliable and Robust End Application
- Low On-Resistance
- Low Input Capacitance
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

## **Description and Applications**

This MOSFET is designed to meet the stringent requirements of Automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:


- Engine Management Systems
- Body Control Electronics
- DC/DC Converters

### **Mechanical Data**


- Case: TO252 (DPAK)
- Case Material: Molded Plastic, "Green" Molding Compound.
   UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish Matte Tin Finish Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.33 grams (Approximate)



Top View



Pin Out Top View



**Equivalent Circuit** 


## **Ordering Information (Note 5)**

Part Number	Case	Packaging
DMNH6011LK3Q-13	TO252 (DPAK)	2,500/Tape & Reel

Notes: 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

## **Marking Information**



Oll = Manufacturer's Marking
NH6011L = Product Type Marking Code
YYWW = Date Code Marking
YY = Last Two Digits of Year (ex: 18= 2018)
WW = Week Code (01 to 53)



# **Maximum Ratings** (@ $T_A = +25^{\circ}C$ , unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage		V <sub>DSS</sub>	55	V
Gate-Source Voltage	$V_{GSS}$	±12	V	
Continuous Drain Current (Note 8), $V_{GS} = 10V$ $ T_C = +25^{\circ}C $ $ T_C = +100^{\circ}C $		I <sub>D</sub>	80 50	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I <sub>DM</sub>	180	Α	
Maximum Continuous Body Diode Forward Current (Note 8)		I <sub>S</sub>	80	А
Avalanche Current, L = 0.1mH (Note 9)		I <sub>AS</sub>	54	А
Avalanche Energy, L = 0.1mH (Note 9)		Eas	147	mJ

## Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 6)		$P_D$	1.6	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	80	°C/W
Total Power Dissipation (Note 7)		$P_D$	3.0	W
Thermal Resistance, Junction to Ambient (Note 7)  Steady State		$R_{\theta JA}$	42	°C/W
Thermal Resistance, Junction to Case (Note 8)		$R_{\theta JC}$	1.1	C/VV
Operating and Storage Temperature Range		T <sub>J,</sub> T <sub>STG</sub>	-55 to +175	°C


## Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic		Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 10)							
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	55	_	_	V	$V_{GS} = 0V, I_D = 250\mu A$	
Zero Gate Voltage Drain Current, T <sub>J</sub> = +25°C	I <sub>DSS</sub>	_	_	1	μA	$V_{DS} = 55V, V_{GS} = 0V$	
Gate-Source Leakage	I <sub>GSS</sub>	_	_	±100	nA	$V_{GS} = \pm 12V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 10)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	1	_	2	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$	
Static Drain-Source On-Resistance	D	_	8.3	12 mΩ	$V_{GS} = 10V, I_D = 25A$		
Static Dialii-Source Off-Resistance	R <sub>DS(ON)</sub>	_	9.0	18	11122	$V_{GS} = 4.5V, I_D = 25A$	
Diode Forward Voltage	V <sub>SD</sub>	_	0.7	1.2	V	V <sub>GS</sub> = 0V, I <sub>S</sub> = 1.7A	
DYNAMIC CHARACTERISTICS (Note 11)							
Input Capacitance	C <sub>iss</sub>	_	3,077	_	pF		
Output Capacitance	Coss	_	331	_	pF	$V_{DS} = 30V, V_{GS} = 0V,$ f = 1MHz	
Reverse Transfer Capacitance	C <sub>rss</sub>	_	127	_	pF	T = TIVIDZ	
Gate Resistance	Rg	_	1.7	_	Ω	$V_{DS} = 0V$ , $V_{GS} = 0V$ , $f = 1MHz$	
Total Gate Charge (V <sub>GS</sub> = 4.5V)	Qg	_	23.4	_	nC		
Total Gate Charge (V <sub>GS</sub> = 10V)	Qg	_	49.1	_	nC	Vps = 30V. lp = 25A	
Gate-Source Charge	Q <sub>gs</sub>	_	5.3	_	nC	VDS = 30V, ID = 25A	
Gate-Drain Charge	Q <sub>gd</sub>	_	9.6	_	nC	1	
Turn-On Delay Time	t <sub>D(ON)</sub>	_	5.9	_	ns	$V_{GS} = 10V, V_{DS} = 30V,$ $R_{G} = 3\Omega, I_{D} = 25A$	
Turn-On Rise Time	t <sub>R</sub>	_	8.7	_	ns		
Turn-Off Delay Time	t <sub>D(OFF)</sub>	_	28.2	_	ns		
Turn-Off Fall Time	t <sub>F</sub>	_	10.2	_	ns		
Body Diode Reverse Recovery Time	t <sub>RR</sub>	_	30.1	_	ns	I <sub>F</sub> = 25A, di/dt = 100A/μs	
Body Diode Reverse Recovery Charge	$Q_{RR}$	_	25.7	_	nC	$I_F = 25A$ , di/dt = 100A/ $\mu$ s	

- 6. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
- 7. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.
- 8. Thermal resistance from junction to soldering point (on the exposed drain pad).
- I<sub>AS</sub> and E<sub>AS</sub> ratings are based on low frequency and duty cycles to keep T<sub>J</sub> = +25°C.
   Short duration pulse test used to minimize self-heating effect.
   Guaranteed by design. Not subject to product testing.

Document number: DS39361 Rev. 2 - 2








Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage






Figure 5. Typical On-Resistance vs. Drain Current and Temperature








Figure 6. On-Resistance Variation with Temperature







Figure 7. On-Resistance Variation with Temperature









Figure 11. Gate Charge













Figure 13. Transient Thermal Resistance



## **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.




TO252 (DPAK)				
Dim	Min	in Max Ty		
Α	2.19	2.39	2.29	
A1	0.00	0.13	0.08	
A2	0.97	1.17	1.07	
b	0.64	0.88	0.783	
b2	0.76	1.14	0.95	
b3	5.21	5.46	5.33	
С	0.45	0.58	0.531	
D	6.00	6.20	6.10	
D1	5.21	-	-	
е	-	-	2.286	
Е	6.45	6.70	6.58	
E1	4.32	-	-	
Н	9.40	10.41	9.91	
L	1.40	1.78	1.59	
L3	0.88	1.27	1.08	
L4	0.64	1.02	0.83	
а	0°	10°	-	
All Dimensions in mm				

# **Suggested Pad Layout**

 $\label{prop:lease} Please see \ http://www.diodes.com/package-outlines.html for the latest version.$ 

## TO252 (DPAK)



Dimensions	Value (in mm)		
С	4.572		
X	1.060		
X1	5.632		
Y	2.600		
Y1	5.700		
Y2	10.700		



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018. Diodes Incorporated

www.diodes.com