

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _A = +25°C
-12V	16mΩ @ V _{GS} = -4.5V	-9.1A
	21.5mΩ @ V _{GS} = -2.5V	-7.9A
	26mΩ @ V _{GS} = -1.8V	-7.0A
	32mΩ @ V _{GS} = -1.5V	-6.3A

Description and Applications

This MOSFET is designed to meet the stringent requirements of Automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- Engine Management Systems
- DC-DC Converters
- Body Control Electronics


Features

- 0.6mm Profile – Ideal For Low Profile Applications
- PCB Footprint of 4mm²
- Low Gate Threshold Voltage
- Fast Switching Speed
- ESD Protected to 3kV
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **Qualified to AEC-Q101 Standards for High Reliability**
- **PPAP Capable (Note 4)**


Mechanical Data

- Case: U-DFN2020-6 (Type E)
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208 **(e4)**
- Weight: 0.0065 grams (Approximate)


U-DFN2020-6 (Type E)



Bottom View



Pin Out Bottom View




Internal Schematic

Ordering Information (Note 5)

Part Number	Marking	Reel Size (inches)	Quantity Per Reel
DMP1022UFDEQ-7	P4	7	3,000

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to <https://www.diodes.com/quality/product-compliance-definitions/>.
 5. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information



P4 = Product Type Marking Code
 YM = Date Code Marking
 Y = Year (ex: E = 2017)
 M = Month (ex: 9 = September)

Date Code Key

Year	2011	~	2015	2016	2017	2018	2019	2020	2021	2022	2023
Code	Y	~	C	D	E	F	G	H	I	J	K

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D

Maximum Ratings (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V_{DSS}	-12	V
Gate-Source Voltage			V_{GSS}	± 8	V
Continuous Drain Current (Note 7) $V_{GS} = -4.5\text{V}$	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	I_D	-9.1 -7.2	A
	$t < 5\text{s}$	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	I_D	-11.2 -9.0	A
Pulsed Drain Current (10 μs Pulse, Duty Cycle = 1%)			I_{DM}	-90	A
Continuous Source-Drain Diode Current		$T_A = +25^\circ\text{C}$ $T_C = +25^\circ\text{C}$	I_S	-2.5 -7.1	A
Pulsed Source-Drain Diode Current (10 μs Pulse, Duty Cycle = 1%)			I_{SM}	-50	A

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 6)	$T_A = +25^\circ\text{C}$	P_D	0.66	W
	$T_A = +70^\circ\text{C}$		0.42	
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	189	$^\circ\text{C/W}$
	$t < 5\text{s}$		123	
Total Power Dissipation (Note 7)	$T_A = +25^\circ\text{C}$	P_D	2.03	W
	$T_A = +70^\circ\text{C}$		1.3	
Thermal Resistance, Junction to Ambient (Note 7)	Steady State	$R_{\theta JA}$	61	$^\circ\text{C/W}$
	$t < 5\text{s}$		40	
Thermal Resistance, Junction to Case (Note 6)	Steady State	$R_{\theta JC}$	9.3	
Operating and Storage Temperature Range		T_J, T_{STG}	-55 to +150	$^\circ\text{C}$

- Notes:
6. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.
 7. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal vias to bottom layer 1-inch square copper plate.

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV _{DSS}	-12	—	—	V	V _{GS} = 0V, I _D = -250μA
Zero Gate Voltage Drain Current (T _J = +25°C)	I _{DSS}	—	—	-3.5	μA	V _{DS} = -12V, V _{GS} = 0V
Gate-Source Leakage	I _{GSS}	—	—	±10	μA	V _{GS} = ±5V, V _{DS} = 0V
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	V _{GS(TH)}	-0.35	—	-0.8	V	V _{DS} = V _{GS} , I _D = -250μA
V _{GS(TH)} Temperature Coefficient	ΔV _{GS(TH)} /ΔT _J	—	2.5	—	mV/°C	I _D = -250μA
On-State Drain Current	I _{D(ON)}	-10	—	—	A	V _{GS} = -4.5V, V _{DS} < -5A
Static Drain-Source On-Resistance	R _{DS(ON)}	—	12	16	mΩ	V _{GS} = -4.5V, I _D = -8.2A
			15	21.5		V _{GS} = -2.5V, I _D = -7.2A
			20	26		V _{GS} = -1.8V, I _D = -6.6A
			23	32		V _{GS} = -1.5V, I _D = -1A
			80	160		V _{GS} = -1.2V, I _D = -1A
Forward Transfer Admittance	Y _{fs}	—	12	—	S	V _{DS} = -4V, I _D = -8.2A
Diode Forward Voltage	V _{SD}	—	-0.8	-1.2	V	V _{GS} = 0V, I _S = -8A
DYNAMIC CHARACTERISTICS (Note 9)						
Input Capacitance	C _{iss}	—	2,953	—	pF	V _{DS} = -4V, V _{GS} = 0V, f = 1.0MHz
Output Capacitance	C _{oss}	—	756	—		
Reverse Transfer Capacitance	C _{rss}	—	678	—		
Gate Resistance	R _g	—	8.6	18	Ω	V _{DS} = 0V, V _{GS} = 0V, f = 1MHz
Total Gate Charge	Q _g	—	28.4	42.6	nC	V _{GS} = -5V, V _{DS} = -4V, I _D = -10A
Total Gate Charge	Q _g	—	25.3	38		
Gate-Source Charge	Q _{gs}	—	2.3	—		
Gate-Drain Charge	Q _{gd}	—	7.2	—		
Turn-On Delay Time	t _{D(ON)}	—	20	30	ns	V _{DS} = -4V, V _{GS} = -4.5V, R _G = 1Ω, R _L = 0.4Ω, I _D = -9.8A
Turn-On Rise Time	t _R	—	28	42		
Turn-Off Delay Time	t _{D(OFF)}	—	117	176		
Turn-Off Fall Time	t _F	—	93	139		
BODY DIODE CHARACTERISTICS						
Diode Forward Voltage	V _{SD}	—	-0.8	-1.2	V	V _{GS} = 0V, I _S = -9.8A
Continuous Source-Drain Diode Current (Note 6)	I _S	—	—	-2.5	A	T _A = +25°C
		—	—	-7.1		T _C = +25°C
Pulse Diode Forward Current (Note 8)	I _{SM}	—	—	-50		—
Body Diode Reverse Recovery Time (Note 8)	t _{RR}	—	28	56	ns	I _S = -9.8A, dI/dt = 100A/μs
Reverse Recovery Fall Time	t _a	—	10	—		
Reverse Recovery Rise Time	t _b	—	18	—		
Body Diode Reverse Recovery Charge (Note 8)	Q _{RR}	—	13	26	nC	

Notes: 8. Short duration pulse test used to minimize self-heating effect.
9. Guaranteed by design. Not subject to production testing.




Fig. 1 SOA, Safe Operation Area




Fig. 2 Single Pulse Maximum Power Dissipation




Fig. 3 Transient Thermal Resistance




Fig. 4 Typical Output Characteristics




Fig. 5 Typical Transfer Characteristics




Fig. 6 Typical On-Resistance vs. Drain Current and Gate Voltage




Fig. 7 Typical On-Resistance vs. Drain Current and Temperature




Fig. 8 On-Resistance Variation with Temperature




Fig. 9 On-Resistance Variation with Temperature




Fig. 10 Gate Threshold Variation vs. Ambient Temperature




Fig. 11 Diode Forward Voltage vs. Current




Fig. 12 Typical Junction Capacitance




Fig. 13 Typical Drain-Source Leakage Current vs. Voltage





Fig. 14 Gate-Charge Characteristics

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

U-DFN2020-6 (Type E)




U-DFN2020-6 (Type E)			
Dim	Min	Max	Typ
A	0.57	0.63	0.60
A1	0	0.05	0.03
A3	-	-	0.15
b	0.25	0.35	0.30
b1	0.185	0.285	0.235
D	1.95	2.05	2.00
D2	0.85	1.05	0.95
E	1.95	2.05	2.00
E2	1.40	1.60	1.50
e	-	-	0.65
L	0.25	0.35	0.30
L1	0.82	0.92	0.87
L(2X)	-	-	-
K1	-	-	0.305
K2	-	-	0.225
Z	-	-	0.20
All Dimensions in mm			

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

U-DFN2020-6 (Type E)



Dimensions	Value (in mm)
C	0.650
X	0.400
X1	0.285
X2	1.050
Y	0.500
Y1	0.920
Y2	1.600
Y3	2.300

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com