



DMP510DLW

Product Summary

BV _{DSS}	Rds(on) Max	I _D Max T _A = +25°C
-50V	10.0Ω @ V _{GS} = -5V	-174mA

Description and Applications

This MOSFET has been designed to minimize the on-state resistance (R_{DS(ON)}) and yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- Motor Control
- Power Management Functions
- Backlighting


50V P-CHANNEL ENHANCEMENT MODE MOSFET

Features and Benefits

- Low On-Resistance
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

Mechanical Data

- Case: SOT323
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Alloy 42
 Leadframe. Solderable per MIL-STD-202, Method 208 3
- Weight: 0.006 grams (Approximate)



Ordering Information (Note 4)

Part Number	Case	Packaging
DMP510DLW-7	SOT323	3000/Tape & Reel
DMP510DLW-13	SOT323	10000/Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

51D	۸

51D= Product Type Marking Code $\overline{Y}M = Date Code Marking$ Y or $\overline{Y} = Year (ex: H = 2020)$ M = Month (ex: 9 = September)

Date Code Key

Year	2017		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	E		Н		J	K	L	М	Ν	0	Р	R
	1								•	- ·		_
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage			V _{DSS}	-50	V
Gate-Source Voltage			Vgss	±20	V
Continuous Drain Current (Note 6) $V_{GS} = -5V$ State State T _A = +25°C T _A = +70°C			lD	-174 -139	mA
Maximum Continuous Body Diode Forward Curre	ls	-65	mA		
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1	%) (Note 6)	ldм	-1.0	А

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)		PD	320	mW
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	Reja	398	°C/W
Total Power Dissipation (Note 6)		PD	470	mW
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	R _{0JA}	273	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						·
Drain-Source Breakdown Voltage	BVDSS	-50		—	V	Vgs = 0V, Id = -250µA
Zero Gate Voltage Drain Current	I _{DSS}	—	—	-1.0	μA	$V_{DS} = -50V, V_{GS} = 0V$
Gate-Source Leakage	lgss	—	_	±100	nA	$V_{GS} = \pm 16V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	V _{GS(TH)}	-0.8		-2.0	V	$V_{DS} = V_{GS}, I_D = -1mA$
Static Drain-Source On-Resistance	RDS(ON)	—		10	Ω	VGS = -5V, ID = -0.1A
Diode Forward Voltage	Vsd	—	-0.78	-1.5	V	VGS = 0V, IS = -100mA
DYNAMIC CHARACTERISTICS (Note 8)						·
Input Capacitance	Ciss	-	24.6	—	pF	
Output Capacitance	Coss	—	4.8	—	pF	V _{DS} = -25V, V _{GS} = 0V, f = 1.0MHz
Reverse Transfer Capacitance	Crss	-	2.8	—	pF	
Gate Resistance	Rg	—	2000	—	Ω	$f = 1.0MHz$, $V_{GS} = 0V$, $V_{DS} = 0V$
Total Gate Charge (V _{GS} = -4.5V)	Qg	—	280	—	рС	
Total Gate Charge (V _{GS} = -10V)	Qg	—	560	—	рС	Vgs = -4.5V, Vds = -10V,
Gate-Source Charge	Qgs	—	90	—	рС	I _D = -100mA
Gate-Drain Charge	Q _{gd}	—	77	—	рС	
Turn-On Delay Time	t _{D(ON)}	—	2.8	—	ns	
Turn-On Rise Time	tR	—	2.6	—	ns	V _{DD} = -30V, I _D = -0.27A,
Turn-Off Delay Time	tD(OFF)	—	11.1	—	ns	$R_{GEN} = 50\Omega$, $V_{GS} = -10V$
Turn-Off Fall Time	tF	—	7.2	—	ns	1


5. Device mounted on FR-4 PCB, with minimum recommended pad layout. Notes:

Device mounted on 1" x 1" FR-4 PCB with high coverage 2oz. Copper, single sided.
 Short duration pulse test used to minimize self-heating effect.

8. Guaranteed by design. Not subject to product testing.




DMP510DLW





DMP510DLW Document number: DS40228 Rev. 2 - 2




DMP510DLW














Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT323								
Dim	Min	Max	Тур					
A1	0.00	0.10	0.05					
A2	0.90	1.00	0.95					
b	0.25	0.40	0.30					
С	0.10	0.18	0.11					
D	1.80	2.20	2.15					
Е	2.00	2.20	2.10					
E1	1.15	1.35	1.30					
е	C).650 B	SC					
e1	1.20	1.40	1.30					
F	0.375	0.475	0.425					
L	0.25	0.40	0.30					
а	0°	8°						
All	Dimen	sions i	in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	0.650
G	1.300
Х	0.470
Ŷ	0.600
Y1	2.500

SOT323

SOT323



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com