



#### 30V P-CHANNEL ENHANCEMENT MODE MOSFET

### **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> Max T <sub>C</sub> = +25°C		
201/	$6.8 \text{m}\Omega$ @ $V_{GS} = -10V$	-50A		
-30V	$13m\Omega$ @ $V_{GS} = -4.5V$	-36A		

## **Description and Applications**

This MOSFET has been designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- Backlighting
- Power Management Functions
- DC-DC Converters

## **Features and Benefits**

- Low R<sub>DS(ON)</sub> Ensures On State Losses are Minimized
- Small Form Factor Thermally Efficient Package Enables Higher Density End Products
- Occupies Just 33% of the Board Area Occupied by SO-8 Enabling Smaller End Product
- 100% Unclamped Inductive Switching (Test in Production)
   Ensures More Reliability
- HBM ESD Protection Level of 8kV Typical
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)


#### **Mechanical Data**

- Case: V-DFN3333-8 (Type B)
- Case Material: Molded Plastic, "Green" Molding Compound.
   UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Below Diagram Terminals: Finish –NiPdAu over Copper Leadframe.
   Solderable per MIL-STD-202, Method 208
- Weight: 0.030 grams (Approximate)






Top View



**Bottom View** 




### Ordering Information (Note 5)

Part Number	Case	Packaging
DMP3007SCGQ-7	V-DFN3333-8 (Type B)	2,000/Tape & Reel
DMP3007SCGQ-13	V-DFN3333-8 (Type B)	3,000/Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

## **Marking Information**



V07= Product Type Marking Code YYWW = Date Code Marking YY = Last Two Digits of Year (ex: 18 = 2018) WW = Week Code (01 to 53)



# **Maximum Ratings** (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V <sub>DSS</sub>	-30	V
Gate-Source Voltage			V <sub>GSS</sub>	±25	V
Continuous Drain Current (Note 8) $V_{GS} = -10V$ Steady $T_C = +25^{\circ}C$ State $T_C = +70^{\circ}C$		I <sub>D</sub>	-50 -40	А	
Maximum Continuous Body Diode Forward Current (Note 8)			Is	-40	Α
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)			I <sub>DM</sub>	-100	Α
Avalanche Current (Note 9) L = 1mH			I <sub>AS</sub>	-16	Α
Avalanche Energy (Note 9) L = 1mH			E <sub>AS</sub>	130	mJ

### Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 6)	$T_A = +25$ °C	$P_D$	1.0	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	124	°C/W
Total Power Dissipation (Note 7) T <sub>A</sub> = +25°C		P <sub>D</sub>	2.4	W
Thermal Resistance, Junction to Ambient (Note 7)  Steady State		$R_{\theta JA}$	52	°C/W
Thermal Resistance, Junction to Case (Note 8)	R <sub>0</sub> JC	4.0	°C/W	
Operating and Storage Temperature Range		T <sub>J</sub> , T <sub>STG</sub>	-55 to +150	°C

# **Electrical Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 10)							
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	-30	_	_	V	$V_{GS} = 0V, I_D = -250\mu A$	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	_	_	-1	μΑ	V <sub>DS</sub> = -24V, V <sub>GS</sub> = 0V	
Gate-Source Leakage		-	_	±10	μΑ	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 10)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	-1.0		-3.0	٧	$V_{DS} = V_{GS}$ , $I_D = -250\mu A$	
Static Drain-Source On-Resistance	J	-	5.7	6.8	mΩ	$V_{GS} = -10V, I_D = -11.5A$	
Static Dialii-Source Oil-Resistance	R <sub>DS(ON)</sub>	_	8.0	13		$V_{GS} = -4.5V, I_D = -8.5A$	
Diode Forward Voltage	V <sub>SD</sub>	_	-0.7	-1.2	V	$V_{GS} = 0V, I_{S} = -1A$	
DYNAMIC CHARACTERISTICS (Note 11)							
Input Capacitance	C <sub>iss</sub>		2,826	_	pF		
Output Capacitance	Coss	_	606	_	pF	$V_{DS} = -15V, V_{GS} = 0V,$ f = 1.0MHz	
Reverse Transfer Capacitance	C <sub>rss</sub>	_	305	_	pF	-1 = 1.UIVIDZ	
Gate Resistance	Rg	_	23	_	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1.0MHz$	
Total Gate Charge (V <sub>GS</sub> = -4.5V)	Qg	-	31.2	_	nC		
Total Gate Charge (V <sub>GS</sub> = -10V)	Qg	-	64.2	_	nC	15// 45/	
Gate-Source Charge	Q <sub>gs</sub>	-	10.6	_	nC	$V_{DS} = -15V, I_D = -11.5A$	
Gate-Drain Charge	Q <sub>gd</sub>	-	11.6	_	nC	7	
Turn-On Delay Time	t <sub>D(ON)</sub>	-	4.8	_	ns		
Turn-On Rise Time	t <sub>R</sub>		4.3	_	ns	$V_{DD} = -15V$ , $V_{GS} = -10V$ , $R_g = 6\Omega$ , $I_D = -11.5A$	
Turn-Off Delay Time	t <sub>D(OFF)</sub>		306	_	ns		
Turn-Off Fall Time	t <sub>F</sub>		125	_	ns		
Reverse Recovery Time	t <sub>RR</sub>	_	19	_	ns		
Reverse Recovery Charge	Q <sub>RR</sub>	_	9.8	_	nC	$I_S = -11.5A$ , $dI/dt = 100A/\mu s$	


 Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
 Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.
 Thermal resistance from junction to soldering point (on the exposed drain pad). Notes:


<sup>9.</sup>  $I_{AS}$  and  $E_{AS}$  ratings are based on low frequency and duty cycles to keep  $T_J = +25$ °C. 10. Short duration pulse test used to minimize self-heating effect.


<sup>11.</sup> Guaranteed by design. Not subject to product testing.














V<sub>GS</sub> GATE-SOURCE VOLTAGE (V) Figure 4 Typical Drain-Source On-Resistance vs. Gate-Source Voltage








Figure 6 On-Resistance Variation with Temperature













 $\label{eq:total_total} T_J, \, \text{JUNCTION TEMPERATURE (°C)}$  Figure 8 Gate Threshold Variation vs. Junction Temperature




V<sub>DS</sub>, DRAIN-SOURCE VOLTAGE (V) Figure 10 Typical Junction Capacitance



July 2018 © Diodes Incorporated






t1, PULSE DURATION TIME (sec) Figure 13 Transient Thermal Resistance



## **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### V-DFN3333-8 (Type B)




V-DFN3333-8					
(Type B)					
Dim	Min	Max	Тур		
Α	0.75	0.85	0.80		
A1	0.00	0.05	0.02		
A3	-		0.203		
b	0.27	0.37	0.32		
D	3.25	3.35	3.30		
D2	2.17	2.37	2.27		
Е	3.25	3.35	3.30		
E2	1.85	2.05	1.95		
е			0.65		
k	-		0.33		
L	0.35	0.45	0.40		
L1	-		0.34		
Z			0.515		
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### V-DFN3333-8 (Type B)



Dimensions	Value (in mm)
С	0.650
C1	1.950
G	0.650
Х	0.420
X1	2.370
Υ	0.700
Y1	0.400
Y2	2.150
Y3	0.450



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com