



Product Summary

BV _{DSS}	R _{DS(ON) max}	Ι _D T _A = +25°C
	14mΩ @ V _{GS} = -10V	-10.5A
-30V	25mΩ @ V _{GS} = -4.5V	-8A

Description

This new generation MOSFET is designed to minimize the on-state resistance ($R_{DS(ON)}$) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Applications


- Load Switch
- Power Management Functions
- DC-DC Converters



1	2	3	1
6	□ ₅Г	74	
	t Potto	m \/iow	

Pin Out Bottom View

U-DFN2523-6 Pin 1, 2 = Source Pin 1 Pin 3 = Gate



Bottom View

Equivalent Circuit

Ordering Information (Note 4)

	Part Number	Case	Packaging			
	DMP3013SFK-7	U-DFN2523-6	3000/Tape & Reel			
DMP3013SFK-13		U-DFN2523-6	10,000/Tape & Reel			
Notes:	: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.					

No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

U-	DFN2523-6
<u> </u>	BI NEOLO O



 $\begin{array}{l} \mathsf{OC} = \mathsf{Product} \ \mathsf{Type} \ \mathsf{Marking} \ \mathsf{Code} \\ \mathsf{YM} = \mathsf{Date} \ \mathsf{Code} \ \mathsf{Marking} \\ \mathsf{Y} = \mathsf{Year} \ (\mathsf{ex:} \ \mathsf{G} = 2019) \\ \mathsf{M} = \mathsf{Month} \ (\mathsf{ex:} \ 9 = \mathsf{September}) \end{array}$

Date Code Key

Year	2018	2019	20	020	2021	2022	2	2023	2024	202	25	2026
Code	F	G		H	I	J		K	L	N	1	Ν
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D

P-CHANNEL ENHANCEMENT MODE MOSFET

Features and Benefits

- Low On-Resistance
- Low Input Capacitance
- Low Input/Output Leakage
- 100% Unclamped Inductive Switching (Test in Production) Ensures More Reliability
- ESD Protected Gate
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Mechanical Data

- Case: U-DFN2523-6
- Case Material: Molded Plastic, "Green" Molding Compound; UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208 ^(A)
- Weight: 0.008 grams (Approximate)

Pin 4, 5, 6 = Drain



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage			V _{DSS}	-30	V
Gate-Source Voltage			V _{GSS}	±25	V
Continuous Drain Current (Note 6) V_{GS} = -10V	Steady State	$T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$	I _D	-10.5 -8.5	A
Continuous Drain Current (Note 6) V_{GS} = -4.5V	ID	-8.0 -6.5	A		
Maximum Continuous Body Diode Forward Current (Note 6)		Is	-2.0	A
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)			I _{DM}	-80	A
Avalanche Current (Note 7)	I _{AS}	-14	A		
Avalanche Energy (Note 7)	E _{AS}	100	mJ		

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)		PD	1.0	W
Thermal Resistance, Junction to Ambient (Note 5)		R _{OJA}	126	°C/W
Total Power Dissipation (Note 6)		PD	2.1	W
Thermal Resistance, Junction to Ambient (Note 6)		R _{0JA}	61	°C/W
Total Power Dissipation (Note 6)	$T_C = +25^{\circ}C$	PD	19.5	W
Thermal Resistance, Junction to Case (Note 6)		R _{eJC}	6.4	°C/W
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)							
Drain-Source Breakdown Voltage	BV _{DSS}	-30	—	—	V	$V_{GS} = 0V, I_D = -250\mu A$	
Zero Gate Voltage Drain Current T _J = +25°C	I _{DSS}	_	_	-1	μA	$V_{DS} = -24V, V_{GS} = 0V$	
Gate-Source Leakage	I _{GSS}		—	±10	μA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 8)						-	
Gate Threshold Voltage	V _{GS(TH)}	-1.0	_	-3.0	V	$V_{DS} = V_{GS}, I_D = -250 \mu A$	
Static Drain-Source On-Resistance	D		10	14	mΩ	V _{GS} = -10V, I _D = -9.5A	
Static Drain-Source On-Resistance	R _{DS(ON)}		14.2	25	1112	$V_{GS} = -4.5V, I_D = -6.9A$	
Diode Forward Voltage	V _{SD}		-0.7	-1.2	V	$V_{GS} = 0V, I_{S} = -1A$	
DYNAMIC CHARACTERISTICS (Note 9)			•	•	•		
Input Capacitance	C _{iss}	_	1674	—		$V_{DS} = -15V, V_{GS} = 0V,$ f = 1.0MHz	
Output Capacitance	Coss		302	_	pF		
Reverse Transfer Capacitance	Crss		230	_			
Gate Resistance	Rg		15.2	_	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1.0MHz$	
Total Gate Charge (V _{GS} = -5V)	Qg		16.2	_			
Total Gate Charge (V _{GS} = -10V)	Qg		33.7	_	nC		
Gate-Source Charge	Q _{gs}		3.5	_		$V_{DS} = -15V, I_D = -11.5A$	
Gate-Drain Charge	Q _{gd}		6.7	_			
Turn-On Delay Time	t _{D(ON)}	_	4.0	_			
Turn-On Rise Time	t _R	_	4.5	_		$V_{DD} = -15V, V_{GS} = -10V,$	
Turn-Off Delay Time	t _{D(OFF)}	_	96	_	ns	$R_{G} = 6\Omega, I_{D} = -11.5A$	
Turn-Off Fall Time	t _F	_	106.5	—	1		
Reverse Recovery Time	t _{RR}		46	—	ns		
Reverse Recovery Charge	Q _{RR}		25.5	—	nC	$I_{\rm S} = -11.5$ A, dl/dt = 100A/µs	

Notes:


Device mounted on FR-4 substrate PCB, 2oz copper, with minimum recommended pad layout.
Device mounted on FR-4 substrate PCB, 2oz copper, with thermal vias to bottom layer 1-inch square copper plate.


7. UIS in production with L = 1mH, T_J = +25°C.

Short duration pulse test used to minimize self-heating effect.
Guaranteed by design. Not subject to production testing.



DMP3013SFK







DMP3013SFK Document number: DS41334 Rev. 2 - 2












50






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

U-DFN2523-6




	U-DFN2523-6								
Dim	Min	Max	Тур						
Α	0.57	0.63	0.60						
A1	0	0.05	0.02						
A3	-	-	0.152						
b	0.25	0.35	0.30						
D	2.45	2.55	2.50						
D1	1.55	1.65	1.60						
е	-	-	0.65						
Е	2.25	2.35	2.30						
E1	1.18	1.28	1.23						
L	0.30	0.40	0.35						
L1	0.30	0.40	0.35						
All	Dimens	ions in	mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

U-DFN2523-6



Dimensions	Value (in mm)
С	0.650
Х	0.400
X1	1.700
Y	0.650
Y1	0.450
Y2	1.830
Y3	2.700



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com