



DMT10H010SPS

100V N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D T _C = +25°C (Note 9)
100V	8.8mΩ @ V _{GS} = 10V	100A
100 V	11.5mΩ @ V _{GS} = 6V	98A

Description

This new generation N-channel enhancement mode MOSFET is designed to minimize $R_{DS(ON)}$, yet maintain superior switching performance. This device is ideal for use in notebook battery power management and load switches.

Applications

- Motor controls
- DC-DC converters
- Power management

Features

- 100% Unclamped Inductive Switching Ensures More Reliable and Robust End Application
- Low R_{DS(ON)} Minimizes On-State Losses
- Fast Switching Speed
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen- and Antimony-Free. "Green" Device (Note 3)
 - For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at

https://www.diodes.com/products/automotive/automotive-products/.


Mechanical Data

- Package: PowerDI[®]5060-8
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram Below
- Terminal Finish Matte Tin Annealed over Copper Lead-Frame. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)


Site 1:




Top View



Bottom View



Internal Schematic



Top View Pin Configuration

Site 2:


PowerDI5060-8 (SWP) (Type UX)




Top View



Bottom View



Internal Schematic



Top View Pin Configuration

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.




Ordering Information (Note 4)

Orderable Part Number	Package	Packing		
Orderable Fait Number	rackage	Quantity	Carrier	
DMT10H010SPS-13	PowerDI5060-8	2,500	Tape & Reel	
DMT10H010SPS-13	PowerDI5060-8 (SWP) (Type UX)	2,500	Tape & Reel	

Notes: 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information





T10H010S = Product Type Marking Code

YYWW or YYWW= Date Code Marking

YY or YY = Last Two Digits of Year (ex: 23 = 2023)

WW = Week Code (01 to 53)

Maximum Ratings (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage		V _{DSS}	100	V
Gate-Source Voltage		V_{GSS}	±20	V
Continuous Drain Current, V _{GS} = 10V (Note 5)	$T_A = +25$ °C $T_A = +70$ °C	I _D	14 11	А
Continuous Drain Current, V _{GS} = 10V (Note 6)	$T_{C} = +25^{\circ}C$ (Note 9) $T_{C} = +70^{\circ}C$	Ι _D	100 90	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I _{DM}	250	Α	
Maximum Continuous Body Diode Forward Current		I _S	100	Α
Avalanche Current, L=0.3mH	I _{AS}	25	Α	
Avalanche Energy, L=0.3mH	E _{AS}	93.7	mJ	
Avalanche Current (Note 8), L=3mH	I _{AS}	14.3	Α	
Avalanche Energy (Note 8), L=3mH		E _{AS}	307	mJ

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	P _D	2.5	W
Thermal Resistance, Junction to Ambient (Note 5)		R _{0JA}	49	°C/W
Total Power Dissipation (Note 6)	T _C = +25°C	P _D	139	W
Thermal Resistance, Junction to Case (Note 6)		Rejc	0.9	°C/W
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +150	°C

Notes: 5. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.

- 6. Thermal resistance from junction to soldering point (on the exposed drain pad).
- 7. Short duration pulse test used to minimize self-heating effect.
- 8. Guaranteed by design. Not subject to product testing.
- 9. Package limited.



Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)							
Drain-Source Breakdown Voltage	BV _{DSS}	100	_	_	V	$V_{GS} = 0V$, $I_D = 1mA$	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1	μΑ	$V_{DS} = 80V, V_{GS} = 0V$	
Gate-Source Leakage	IGSS	_	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	V _{GS(TH)}	2	_	4	٧	$V_{DS} = V_{GS}$, $I_D = 250\mu A$	
Static Drain-Source On-Resistance	D		6.6	8.8	mΩ	$V_{GS} = 10V, I_D = 13A$	
Static Dialii-Source Off-Resistance	R _{DS(ON)}	_	8.5	11.5	11122	$V_{GS} = 6V, I_D = 13A$	
Diode Forward Voltage	V_{SD}	_	0.8	1.3	V	$V_{GS} = 0V, I_{S} = 13A$	
DYNAMIC CHARACTERISTICS (Note 8)							
Input Capacitance	C _{ISS}		4,468			V _{DS} = 50V, V _{GS} = 0V f = 1MHz	
Output Capacitance	Coss	_	746	_	pF		
Reverse Transfer Capacitance	C _{RSS}	_	32	_			
Gate Resistance	R_G	_	0.91	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$	
Total Gate Charge	Q_G	_	56.4	_		V 50V L 40A	
Gate-Source Charge	Q _{GS}	_	15.4	_	nC	$V_{DD} = 50V, I_D = 13A,$ $V_{GS} = 10V$	
Gate-Drain Charge	Q_{GD}	_	14	_			
Turn-On Delay Time	t _{D(ON)}	_	18.6	_			
Turn-On Rise Time	t _R	_	22.5	_		$V_{DD} = 50V, V_{GS} = 10V,$ $I_{D} = 13A, R_{g} = 6\Omega$	
Turn-Off Delay Time	t _{D(OFF)}		44.8	_	ns		
Turn-Off Fall Time	t _F	_	29.5	_		_	
Reverse Recovery Time	t _{RR}	_	54.5	_	ns	100 11/11 1000/	
Reverse Recovery Charge	Q _{RR}	_	106.4	_	nC	l _F = 13A, di/dt = 100A/μs	

Notes:

^{7.} Short duration pulse test used to minimize self-heating effect. 8. Guaranteed by design. Not subject to product testing.







V_{DS}, DRAIN-SOURCE VOLTAGE (V) Figure 1.Typical Output Characteristic






Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage



I_D, DRAIN CURRENT (A) Figure 5. Typical On-Resistance vs. Drain Current and Temperature



 $V_{\rm GS}$, GATE-SOURCE VOLTAGE (V) Figure 2. Typical Transfer Characteristic





Figure 4. Typical Transfer Characteristic



T_J, JUNCTION TEMPERATURE (°C) Figure 6. On-Resistance Variation with JunctionTemperature









Figure 7. On-Resistance Variation with Junction Temperature



V_{SD}, SOURCE-DRAIN VOLTAGE (V) Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. JunctionTemperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area






Figure 13. Transient Thermal Resistance




Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site 1:


PowerDI5060-8





PowerDI5060-8				
Dim	Min	Max	Тур	
Α	0.90	1.10	1.00	
A1	0.00	0.05	_	
b	0.33	0.51	0.41	
b2	0.200	0.350	0.273	
b3	0.40	0.80	0.60	
С	0.230	0.330	0.277	
D	•	5.15 BSC	;	
D1	4.70	5.10	4.90	
D2	3.70	4.10	3.90	
D3	3.90	4.30	4.10	
Е	(6.15 BSC	;	
E1	5.60	6.00	5.80	
E2	3.28	3.68	3.48	
E3	3.99	4.39	4.19	
е	,	1.27 BSC	;	
G	0.51	0.71	0.61	
K	0.51	-	-	
L	0.51	0.71	0.61	
L1	0.100	0.200	0.175	
M	3.235	4.035	3.635	
M1	1.00	1.40	1.21	
Θ	10°	12º	11º	
Θ1	6º	8º	7º	
All Dimensions in mm				

Site 2:


PowerDI5060-8 (SWP) (Type UX)







DETAIL A



PowerDI5060-8 (SWP)				
	(Type	UX)	i	
Dim	Min	Max	Тур	
Α	0.90	1.10	1.00	
A1	0	0.05	1	
b	0.30	0.50	0.41	
b2	0.20	0.35	0.25	
b4	C).25REF		
С	0.230	0.330	0.277	
D	5	.15 BS0)	
D1	4.70	5.10	4.90	
D2	3.56	3.96	3.76	
D2a	3.78	4.18	3.98	
Е	6	.40 BS0)	
E1	5.60	6.00	5.80	
E2	3.46	3.86	3.66	
E2a	4.195	4.595	4.395	
е	1.27BSC			
k	1.05		1	
L	0.635	0.835	0.735	
La	0.635	0.835	0.735	
L1	0.200	0.400	0.300	
L1a	0.050REF			
L4	0.025	0.225	0.125	
М	3.205	4.005	3.605	
θ	10°	12°	11°	
θ1	6°	8°	7°	
All Dimensions in mm				




Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site 1


PowerDI5060-8



Dimensions	Value (in mm)
С	1.270
G	0.660
G1	0.820
X	0.610
X1	4.100
X2	0.755
Х3	4.420
X4	5.610
Υ	1.270
Y1	0.600
Y2	1.020
Y3	0.295
Y4	1.825
Y5	3.810
Y6	0.180
Y7	6.610
-	

Site 2:

PowerDI5060-8 (SWP) (Type UX)



Dimensions	Value		
Dilliensions	(in mm)		
С	1.270		
G	0.660		
G1	0.820		
Х	0.610		
X1	4.100		
X2	5.190		
Х3	4.420		
Υ	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com