



### 100V N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI3333-8

## **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> Max T <sub>C</sub> = +25°C		
100V	32mΩ @ V <sub>GS</sub> = 10V	35A		

# Description

This MOSFET is designed to minimize the on-state resistance (RDS(ON)) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

# Applications


- Backlighting
- **Power Management Functions**
- **DC-DC Converters**

#### **Features and Benefits**

- 100% Unclamped Inductive Switching (UIS) Test in Production -Ensures More Reliable and Robust End Application
- Small Form Factor Thermally Efficient Package Enables Higher **Density End Products**
- Wettable Flank for Improved Optical Inspection
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/


#### **Mechanical Data**


- Case: PowerDI®3333-8
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Diagram
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.072 grams (Approximate)











# **Ordering Information** (Note 4)


Part Number	Case	Packaging
DMT10H032SFVW-7	PowerDI3333-8 (SWP) (Type UX)	2,000/Tape & Reel
DMT10H032SFVW-13	PowerDI3333-8 (SWP) (Type UX)	3,000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

# Marking Information

#### PowerDI3333-8 (SWP) (Type UX)



38W = Product Type Marking Code YYWW = Date Code Marking  $\overline{YY}$  = Last Two Digits of Year (ex: 20 = 2020) WW = Week Code (01 to 53)



## **Maximum Ratings** (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	$V_{DSS}$	100	V	
Gate-Source Voltage	Vgss	±20	V	
	Tc = +25°C	•	35	А
Continuous Drain Current (Note 7) Vgs = 10V	Tc = +70°C	ID	28	
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I <sub>DM</sub>	140	Α	
Maximum Continuous Body Diode Forward Current (Note 7)	Is	26	Α	
Pulsed Body Diode Forward Current (Note 8)	I <sub>SM</sub>	140	Α	
Avalanche Current, L = 0.3mH (Note 8)	las	13	Α	
Avalanche Energy, L = 0.3mH (Note 8)	Eas	25.35	mJ	

# Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 5)	PD	1.3	W	
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	$R_{\theta JA}$	97	°C/W
Total Power Dissipation (Note 6)	PD	2.5	W	
Thermal Resistance, Junction to Ambient (Note 6)  Steady State		$R_{\theta JA}$	50	°C/W
Thermal Resistance, Junction to Case (Note 7)	R <sub>θ</sub> JC	2.1	*C/VV	
Operating and Storage Temperature Range	TJ, TSTG	-55 to +150	°C	


# **Electrical Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 9)	Syllibol	IVIIII	Тур	IVIAA	Unit	Test Condition	
, ,		400	1			Tree and the second	
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	100	_	_	V	$V_{GS} = 0V$ , $I_D = 1mA$	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	—	_	1	μΑ	$V_{DS} = 80V$ , $V_{GS} = 0V$	
Gate-Source Leakage	Igss	_	_	±100	nA	$V_{GS} = \pm 20V$ , $V_{DS} = 0V$	
ON CHARACTERISTICS (Note 9)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	2	_	4	V	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250µA	
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	_	24	32	mΩ	$V_{GS} = 10V, I_{D} = 7A$	
Diode Forward Voltage	$V_{SD}$	_	0.86	1	V	$V_{GS} = 0V, I_{S} = 7A$	
DYNAMIC CHARACTERISTICS (Note 10)							
Input Capacitance	Ciss	_	544	_	pF	V <sub>DS</sub> = 50V, V <sub>GS</sub> = 0V, f = 1MHz	
Output Capacitance	Coss	_	181	_	pF		
Reverse Transfer Capacitance	Crss	_	6.0	_	pF		
Gate Resistance	Rg	_	1.2	_	Ω	$V_{DS} = 0V$ , $V_{GS} = 0V$ , $f = 1MHz$	
Total Gate Charge (V <sub>GS</sub> = 4.5V)	Qg	_	4.3	_	nC		
Total Gate Charge (V <sub>GS</sub> = 10V)	$Q_g$	_	8.0	_	nC	\/pa = 50\/ lp = 74	
Gate-Source Charge	Qgs	_	1.8	_	nC	V <sub>DS</sub> = 50V, I <sub>D</sub> = 7A	
Gate-Drain Charge	$Q_{gd}$	_	2.4	_	nC		
Turn-On Delay Time	tD(ON)	_	8.5	_	ns		
Turn-On Rise Time	t <sub>R</sub>	_	2.7	_	ns	V <sub>DS</sub> = 50V, I <sub>D</sub> = 7A	
Turn-Off Delay Time	t <sub>D(OFF)</sub>	_	11.9	_	ns	$V_{GS} = 10V$ , $R_{GEN} = 6\Omega$	
Turn-Off Fall Time	tF	_	6.2	_	ns		
Reverse Recovery Time	trr	_	33.2	_	ns	I= 74 di/dt = 1004/up	
Reverse Recovery Charge	Qrr	_	34.3	_	nC	$I_F = 7A$ , di/dt = 100A/ $\mu$ s	

Notes:

- 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.
- 6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1-inch square copper plate.
- 7. Thermal resistance from junction to soldering point (on the exposed drain pad).
- I<sub>AS</sub> and E<sub>AS</sub> ratings are based on low frequency and duty cycles to keep T<sub>J</sub> = +25°C.
   Short duration pulse test used to minimize self-heating effect.
   Guaranteed by design. Not subject to product testing.





15

ID, DRAIN CURRENT (A)

20

10

25

30

125

25

-50

50

T, JUNCTION TEMPERATURE (°C)

Figure 6. On-Resistance Variation with Temperature

75


100


0


5
















Figure 8. Gate Threshold Variation vs. Junction Temperature











Figure 13. Transient Thermal Resistance



# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

### PowerDI3333-8 (SWP) (Type UX)




PowerDI3333-8 (SWP)					
(Type UX)					
Dim	Min	Max	Тур		
Α	0.75	0.85	0.80		
A1	0.00	0.05			
b	0.25	0.40	0.32		
С	0.10	0.25	0.15		
D	3.20	3.40	3.30		
D1	2.95	3.15	3.05		
D2	2.30	2.70	2.50		
Е	3.20	3.40	3.30		
E1	2.95	3.15	3.05		
E2	1.60	2.00	1.80		
E3	0.95	1.35	1.15		
E4	0.10	0.30	0.20		
е			0.65		
k	0.50	0.90	0.70		
L	0.30	0.50	0.40		
θ	0°	12°	10°		
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI3333-8 (SWP) (Type UX)



Dimensions	Value (in mm)
С	0.650
Х	0.420
X1	0.420
X2	0.230
Х3	2.600
X4	3.500
Y	0.700
Y1	0.550
Y2	1.650
Y3	0.600
Y4	2.450
Y5	0.400
Y6	3.700



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com