

DMPH4029LFGQ

40V 175°C P-CHANNEL ENHANCEMENT MODE MOSFET PowerDI3333-8

Product Summary

BV _{DSS}	Rds(on) Max	I _D Max T _A = +25°C
-40V	$29m\Omega @ V_{GS} = -10V$	-8.0A
-40 v	$45mΩ @ V_{GS} = -4.5V$	-6.0A

Description and Applications

This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- Backlighting
- Power-management functions
- DC-DC converters


Features and Benefits

- Rated to +175°C—Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching Test in Production— Ensures More Reliable and Robust End Application
- Low RDS(ON)—Ensures On State Losses Are Minimized
- Small Form Factor Thermally Efficient Package Enables Higher Density End Products
- Occupies Just 33% of the Board Area Occupied by SO-8 Enabling Smaller End Product
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMPH4029LFGQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: PowerDI[®]3333-8
- Surface Mount Package
- Package Material: Molded Plastic, UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208
- Weight: 0.034 grams (Approximate)



Ordering Information (Note 4)

Part Number	Dackage	Packing		
Part Number	Package	Qty.	Carrier	
DMPH4029LFGQ-7	PowerDI3333-8	2000	Tape & Reel	
DMPH4029LFGQ-13	PowerDI3333-8	3000	Tape & Reel	

Notes: 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



H29 = Product Type Marking Code YYWW = Date Code Marking YY = Last Two Digits of Year (ex: 23 = 2023) WW = Week Code (01 to 53)



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	Vdss	-40	V		
Gate-Source Voltage			V _{GSS}	±20	V
	Steady State	T _A = +25°C T _A = +70°C	ID	-8.0 -6.7	А
Continuous Drain Current (Note 6) V _{GS} = -10V	Steady State	Tc = +25°C Tc = +70°C	lD	-22 -18	А
Pulsed Drain Current (380µs Pulse, Duty Cycle = 1	I _{DM}	-88	А		
Maximum Continuous Body Diode Forward Current	ls	-2.0	А		
Pulsed Source Current (380µs Pulse, Duty Cycle =	I _{SM}	-88	А		
Avalanche Current (Note 7) L = 0.1mH			las	-25	А
Avalanche Energy (Note 7) L = 0.1mH			Eas	32	mJ

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)		PD	1.2	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	Davi	125	°C/W
mermai Resistance, Junction to Ambient (Note 5)	t < 10s	Reja	85	
Total Power Dissipation (Note 6)		Po	2.8	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	Dev	54	
Thermal Resistance, Junction to Ambient (Note 6) t < 10s		Rəja	36	°C/W
Thermal Resistance, Junction to Case (Note 6)		Rejc	6	
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

				-			
Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)							
Drain-Source Breakdown Voltage	BVDSS	-40		_	V	$V_{GS} = 0V, I_{D} = -250 \mu A$	
Zero Gate Voltage Drain Current T _J = +25°C	I _{DSS}	—	—	-1	μA	$V_{DS} = -40V, V_{GS} = 0V$	
Gate-Source Leakage	Igss	—		±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 8)							
Gate Threshold Voltage	VGS(TH)	-1.0	—	-3.0	V	$V_{DS} = V_{GS}$, $I_D = -250 \mu A$	
Static Drain-Source On-Resistance	Descent	_	18	29	mΩ	$V_{GS} = -10V, I_{D} = -3A$	
Static Dialit-Source OII-Resistance	RDS(ON)	—	23	45	11122	$V_{GS} = -4.5V, I_D = -3A$	
Diode Forward Voltage	Vsd	—	-0.7	-1.2	V	$V_{GS} = 0V$, $I_{S} = -1A$	
DYNAMIC CHARACTERISTICS (Note 9)							
Input Capacitance	Ciss	_	1626		pF		
Output Capacitance	Coss	—	135	_	pF	V _{DS} = -20V, V _{GS} = 0V, f = 1.0MHz	
Reverse Transfer Capacitance	Crss	—	107		pF		
Gate Resistance	Rg	_	11	_	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$	
Total Gate Charge (V _{GS} = -4.5V)	Qg	_	17		nC		
Total Gate Charge (V _{GS} = -10V)	Qg	—	34		nC	Vps = -20V. lp = -3A	
Gate-Source Charge	Qgs	_	3.7		nC	VDS = -20V, ID = -3A	
Gate-Drain Charge	Q _{gd}	_	6.0	—	nC		
Turn-On Delay Time	tD(ON)	_	3.9	_	ns		
Turn-On Rise Time	tR	_	2.8	_	ns	$V_{GS} = -10V, V_{DS} = -20V,$	
Turn-Off Delay Time	tD(OFF)	_	83	_	ns	$R_G = 3\Omega$, $I_D = -3A$	
Turn-Off Fall Time	t⊢	_	30		ns		
Body Diode Reverse Recovery Time	trr	_	17.3	—	ns	IF = -3A, di/dt = 100A/µs	
Body Diode Reverse Recovery Charge	Qrr	_	7.2	_	nC	IF = -3A, di/dt = 100A/µs	


Notes: 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.

6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.

7. I_{AS} and E_{AS} ratings are based on low frequency and duty cycles to keep $T_J = +25^{\circ}$ C. 8. Short duration pulse test used to minimize self-heating effect. 9. Guaranteed by design. Not subject to product testing.





DMPH4029LFGQ







DMPH4029LFGQ














t1, PULSE DURATION TIME (sec) Figure 14. Transient Thermal Resistance

1

10

100

1000

0.1

0.0001


0.001

0.01



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




PowerDI3333-8

_			-			
PowerDI3333-8						
Dim	Min	Max	Тур			
Α	0.75	0.85	0.80			
A1	0.00	0.05	0.02			
A3	1	-	0.203			
Ь	0.27	0.37	0.32			
b2	-	-	0.20			
D	3.25	3.35	3.30			
D2	2.22	2.32	2.27			
ш	3.25	3.35	3.30			
E2	1.56	1.66	1.61			
E3	0.79	0.89	0.84			
e	1	-	0.65			
_	0.35	0.45	0.40			
L1	-	-	0.39			
z	-	-	0.515			
aaa	0.25					
bbb	0.10					
CCC	0.10					
All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI3333-8



Dimensions	Value (in mm)			
С	0.650			
Х	0.420			
X1	0.420			
X2	0.230			
X3	2.370			
Y	0.700			
Y1	1.850			
Y2	2.250			
Y3	3.700			
Y4	0.540			



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com