



115V N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	BV _{DSS} @ T _{J Max}	R _{DS(ON)} Max	I _D Max T _A = +25°C
115V 120V		85mΩ @ V _{GS} = 4.5V	3.5A
		90mΩ @ V _{GS} = 2.5V	3.4A

Features and Benefits

- Low Q_g & Q_{gd}
- Small Footprint 1.5mm x 1.5mm
- ESD Protection
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Description and Applications


This new generation MOSFET is designed to minimize the on-state resistance (R_{DS(ON)}), making it ideal for high efficiency power management applications.


- Battery managements
- Load switches
- · Battery protections

Mechanical Data

- Package: X4-DSN1515-9
- Terminal Connections: See Diagram Below
- Moisture Sensitivity: Level 1 per J-STD-020
- UBM Size:250μm
- Terminal Material: Finish NiAu. Solderable per MIL-STD-202, Method 208 @4
- Weight: 0.0006 grams (Approximate)







Top-View Pin Configuration

Equivalent Circuit

Ordering Information (Notes 4 & 5)

Part Number	Dookogo	Packing			
Fait Nullibei	Package	Qty.	Carrier		
DMT12H060LCA9-7	X4-DSN1515-9	3000	Tape & Reel		

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Device with exposed silicon sidewall is non-isolated area.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



6A = Product Type Marking Code \underline{YW} = Date Code Marking \underline{Y} = Year (ex: 2 = 2022)

W = Week (ex: a =week 27; z represents week 52 and 53)

Date Code Kev

zate ceas ite;												
Year	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	1	2	3	4	5	6	7	8	9	0	1	2

Week	1-26	27-52	53
Code	A-Z	a-z	Z



Maximum Ratings (@ $T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage		VDSS	115	V
Gate-Source Voltage		Vgss	±5.5	V
Continuous Drain Current (Note 6) V _{GS} = 4.5V	$T_A = +25$ °C $T_A = +70$ °C	lD	3.5 2.8	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)		Ірм	26	Α
Maximum Body Diode Continuous Current (Note 6)		Is	3.5	Α
Pulsed Body Diode Continuous Current (10µs Pulse, Duty Cycle = 1%)		Ism	26	Α
Avalanche Current, L = 0.3mH (Note 7)		I _{AS}	10	Α
Avalanche Energy, L = 0.3mH (Note 7)		Eas	15	mJ

ESD Ratings (Note 11)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	2000	V	1C
Electrostatic Discharge - Machine Model	ESD MM	200	V	M2

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 8)	PD	1.1	W
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 8)	RөJA	115	°C/W
Power Dissipation (Note 6)	P _D	1.9	W
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 6)	RөJA	65	°C/W
Operating and Storage Temperature Range	TJ, TSTG	-55 to +150	°C


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 9)			- 714			1001 0011011011
Drain-Source Breakdown Voltage	BV _{DSS}	115	_	_	V	V _G S = 0V, I _D = 10mA
Zero Gate Voltage Drain Current T _J = +25°C	IDSS	_	_	1	μΑ	V _{DS} = 92V, V _{GS} = 0V
Cata Causa Laghana	,	_	_	±50	μΑ	$V_{GS} = \pm 8V$, $V_{DS} = 0V$
Gate-Source Leakage	Igss	_	_	±10	μΑ	$V_{GS} = \pm 5.5V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 9)						·
Gate Threshold Voltage	Vgs(TH)	0.5	_	1.4	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$
			56	85		$V_{GS} = 4.5V, I_{D} = 3A$
Static Drain-Source On-Resistance	RDS(ON)	_	61	90	mΩ	$V_{GS} = 2.5V, I_{D} = 2A$
		_	75	130		$V_{GS} = 1.5V, I_{D} = 50mA$
Diode Forward Voltage	V _{SD}	_	0.7	1.0	V	$V_{GS} = 0V$, $I_{S} = 1A$
Reverse Recovery Charge	Q _{RR}	_	53	_	nC	I_ 4.5A di/dt 200A/wa
Reverse Recovery Time	t _{RR}	_	30	_	ns	$I_F = 4.5A$, di/dt = 300A/ μ s
DYNAMIC CHARACTERISTICS (Note 10)						
Input Capacitance	C _{iss}		560	_		
Output Capacitance	Coss	_	80	_	pF	$V_{DS} = 50V$, $V_{GS} = 0V$, $f = 1MHz$
Reverse Transfer Capacitance	Crss	_	9.5	_		I = IIVII IZ
Series Gate Resistance	Rg	_	4.4	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$
Total Gate Charge	Qg	_	8	_		
Gate-Source Charge	Qgs	_	1	_	nC	$V_{DS} = 50V, R_{L} = 11\Omega$
Gate-Drain Charge	Qgd	_	2.4	_	nC	$V_{GS} = 5V$, $R_{GEN} = 3\Omega$
Gate Charge at V _{TH}	Q _{g(TH)}	_	0.5	_]	
Turn-On Delay Time	t _{D(ON)}	_	2	_		
Turn-On Rise Time	t _R	_	8	_	1	$V_{DS} = 50V, R_{L} = 11\Omega$
Turn-Off Delay Time	t _{D(OFF)}	_	29	_	ns	$V_{GS} = 5V$, $R_{GEN} = 3\Omega$
Turn-Off Fall Time	tr	_	11	_	1	

6. Device mounted on FR-4 material with 1inch 2 (6.45cm 2), 2oz. (0.071mm thick) Cu. Notes:

- 7. Repetitive rating, pulse width limited by junction temperature.
 8. Device mounted on FR-4 PCB with minimum recommended pad layout, single sided.
- 9. Short duration pulse test used to minimize self-heating effect.
- 10. Guaranteed by design. Not subject to production testing.11. Refer to ANSI/ESDA/JEDEC specification JS-001-2017 and AEC-Q100-003-Rev-E.








Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 5. Typical On-Resistance vs. Drain Current and Temperature




Figure 2. Typical Transfer Characteristic




Figure 4. Typical Transfer Characteristic




Figure 6. On-Resistance Variation with Temperature






Figure 7. On-Resistance Variation with Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance




Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

X4-DSN1515-9




X4-DSN1515-9							
Dim	Min Max Typ						
Α	0.17	0.25	0.225				
b	0.21	0.29	0.25				
ם	1.420	1.50	1.46				
Е	1.420	1.50	1.46				
е			0.50				
All Dimensions in mm							



Suggested Pad Layout

 $\label{prop:lease} Please see \ http://www.diodes.com/package-outlines.html for the latest version.$

X4-DSN1515-9



Dimensions	Value (in mm)
С	0.50
C1	1.00
C2	1.00
D	0.25



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com