



DMT64M2LPSW

60V N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	Rds(on) Max	Ι _D T _C = +25°C
60V	4.4mΩ @ V _{GS} = 10V	100A
	6.4mΩ @ V _{GS} = 4.5V	85A

Description and Applications

This MOSFET is designed to minimize the on-state resistance (RDS(ON)) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

- High Frequency Switching
- Synchronous Rectification
- **DC-DC Converters**


PowerDI5060-8 (SWP) (Standard)

Features

- 100% Unclamped Inductive Switching (UIS) Test in Production -Ensures More Reliable and Robust End Application
- High Conversion Efficiency
- Low RDS(ON) Minimizes Power Losses
- Low Q_G Minimizes Switching Losses
- Wettable Flank for Improved Optical Inspection
- Fast Switching Speed
- Low Input Capacitance
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Case: PowerDI®5060-8
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (e3)
- Weight: 0.097 grams (Approximate)



Ordering Information (Note 4)

Part Number	Case	Packaging
DMT64M2LPSW-13	PowerDI5060-8 (SWP) (Standard)	2500/Tape & Reel

1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied. Notes: 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



 $\mathcal{D}_{\mathcal{A}}^{\mathcal{A}} = \mathsf{Manufacturer's} \mathsf{Marking}$ T64M2LSW = Product Type Marking Code YYWW or YYWW= Date Code Marking YY or \overline{YY} = Year (ex: 20 = 2020) WW = Week (01 to 53)

PowerDI is a registered trademark of Diodes Incorporated. DMT64M2LPSW Document number: DS41603 Rev. 3 - 2



Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			VDSS	60	V
Gate-Source Voltage			V _{GSS}	±20	V
Continuous Drain Current (Note 5)	Steady State	T _A = +25°C T _A = +70°C	lo	20.7 16.6	А
Continuous Drain Current (Note 6) $T_{C} = +25^{\circ}C$ $T_{C} = +70^{\circ}C$		lo	100 82	А	
Maximum Continuous Body Diode Forward Current (Note 6)			ls	100	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)			ldм	400	А
Pulsed Body Diode Forward Current (10µs Pulse, Duty Cycle = 1%)			lsм	400	А
Avalanche Current, L = 1mH			las	18.2	А
Avalanche Energy, L = 1mH			Eas	165.6	mJ

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	PD	2.8	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	R _{ÐJA}	44	°C/W
Total Power Dissipation (Note 6)	Tc = +25°C	PD	83.3	W
Thermal Resistance, Junction to Case (Note 6)		Rejc	1.5	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Мах	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)	Symbol	IVIIII	Тур	IVIAX	Unit	Test condition	
Drain-Source Breakdown Voltage	BV _{DSS}	60			V	$V_{GS} = 0V, I_D = 1mA$	
Zero Gate Voltage Drain Current				1	μA	$V_{\text{GS}} = 0V, \text{ ID} = 111\text{A}$ $V_{\text{DS}} = 48\text{V}, \text{ V}_{\text{GS}} = 0\text{V}$	
Gate-Source Leakage	IDSS			±100	nA		
ON CHARACTERISTICS (Note 7)	Igss	_	—	±100	ΠA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
Gate Threshold Voltage		1.2	_	2.5	V		
	Vgs(th)			-	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$	
Static Drain-Source On-Resistance	RDS(ON)	_	3.3	4.4	mΩ	$V_{GS} = 10V, I_D = 50A$	
	. ,	_	4.7	6.4		Vgs = 4.5V, ID = 12.5A	
Diode Forward Voltage	Vsd	—	0.8	1.2	V	Vgs = 0V, Is = 50A	
DYNAMIC CHARACTERISTICS (Note 8)				-	1		
Input Capacitance	Ciss	_	2799	—		V _{DS} = 30V, V _{GS} = 0V, f = 1MHz	
Output Capacitance	Coss		950		pF		
Reverse Transfer Capacitance	Crss		79	_			
Gate Resistance	Rg	_	0.63		Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$	
Total Gate Charge (V _{GS} = 10V)	Q _G		46.7			V _{DD} = 30V, I _D = 50A	
Total Gate Charge (V _{GS} = 4.5V)	QG		24.1		-0		
Gate-Source Charge	QGS		8.2		nC		
Gate-Drain Charge	Q _{GD}		11.0				
Turn-On Delay Time	t _{D(ON)}	_	6.5			$V_{DD} = 30V, V_{GS} = 10V,$ $I_D = 30A, R_G = 3.3\Omega$	
Turn-On Rise Time	t _R		6.9				
Turn-Off Delay Time	td(OFF)		26.1		ns		
Turn-Off Fall Time	tF		11.2	—			
Body Diode Reverse Recovery Time	trr		40.1	—	ns		
Body Diode Reverse Recovery Charge	Qrr	_	51.1		nC	I _F = 30A, di/dt = 100A/μs	


 Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.
Thermal resistance from junction to soldering point (on the exposed drain pad). Notes:


7. Short duration pulse test used to minimize self-heating effect.

8. Guaranteed by design. Not subject to product testing.





DMT64M2LPSW












DMT64M2LPSW Document number: DS41603 Rev. 3 - 2








Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




PowerDI5060-8 (SWP) (Standard)

Pov	PowerDI5060-8 (SWP) (Standard)					
Dim	Min	Max	Тур			
Α	0.90	1.10	1.00			
A1	0	0.05				
b	0.30	0.50	0.41			
b2	0.20	0.35	0.25			
b4	().25REF	-			
С	0.230	0.330	0.277			
D	5	5.15 BSC				
D1	4.70	5.10	4.90			
D2	3.56	3.96	3.76			
D2a	3.78	4.18	3.98			
E	6	.40 BS0	0			
E1	5.60	6.00	5.80			
E2	3.46	3.86	3.66			
E2a	4.195	4.595	4.395			
е	1	.27BSC)			
k	1.05					
L	0.635	0.835	0.735			
La	0.635	0.835	0.735			
L1	0.200	0.400	0.300			
L4	0.025	0.225	0.125			
М	3.205	4.005	3.605			
θ	10°	12°	11°			
θ1	6°	8°	7°			
All	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8 (SWP) (Standard)



Dimensions	Value (in mm)		
С	1.270		
G	0.660		
G1	0.820		
Х	0.610		
X1	4.100		
X2	4.420		
Y	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com