



60V N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D T _C = +25°C
601/	5.7mΩ @ V _{GS} = 10V	64.6A
60V	8.1mΩ @ V _{GS} = 4.5V	54.2A

Description and Applications

This MOSFET is designed to meet the stringent requirements of Automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- Synchronous Rectifier
- Power Management Functions
- DC-DC Converters

Features and Benefits


- 100% Unclamped Inductive Switching (UIS) Test in Production –
 Ensures More Reliable And Robust End Application
- High Conversion Efficiency
- Low R_{DS(ON)} Minimizes On State Losses
- Low Input Capacitance
- Fast Switching Speed
- ESD Protected Gate
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMT67M8LCGQ is suitable for automotive applications requiring specific change control and is AEC-Q101 qualified, is PPAP capable, and is manufactured in IATF16949:2016 certified facilities.


Mechanical Data


- Case: V-DFN3333-8
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Below Diagram
- Terminals: Finish—NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (24)
- Weight: 0.027 grams (Approximate)

V-DFN3333-8 (Type B)









Top View

Bottom View

Equivalent Circuit

Ordering Information (Note 4)

Part Number	Case	Packaging
DMT67M8LCGQ-7	V-DFN3333-8 (Type B)	2,000/Tape & Reel
DMT67M8LCGQ-13	V-DFN3333-8 (Type B)	3,000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information

Site1:



678 = Product Type Marking Code YYWW = Date Code Marking YY = Year (ex: 19 = 2019) WW = Week (01 to 53)

Site2:



678 = Product Type Marking Code YWX = Date Code Marking Y = Year (ex: 9 = 2019) W = Week (ex: a = Week 27; z Represents Week 52 and 53) X = Internal Code (ex: U = Monday)

Date Code Key

Year	2017	2018	2019	2020	2021	2022	2023	2024	2025
Code	7	8	9	0	1	2	3	4	5

Week	1-26	27-52	53
Code	A-Z	a-z	Z

	Internal Code	Sun	Mon	Tue	Wed	Thu	Fri	Sat
ſ	Code	Т	Ü	V	W	X	Υ	Z



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage		V _{DSS}	60	V
Gate-Source Voltage		V _{GSS}	±20	V
Continuous Drain Current, V _{GS} = 10V (Note 6)	$T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$	I _D	16 12.8	А
Continuous Drain Current, V _{GS} = 10V (Note 7)	$T_C = +25^{\circ}C$ $T_C = +70^{\circ}C$	I _D	64.6 51.7	А
Pulsed Drain Current (10μs Pulse, Duty Cycle = 1%)		I _{DM}	256	Α
Maximum Continuous Body Diode Forward Current (Note 6	5)	Is	64	Α
Pulsed Body Diode Forward Current (10μs Pulse, Duty Cyc	I _{SM}	256	Α	
Avalanche Current, L=0.3mH	I _{AS}	23.7	Α	
Avalanche Energy, L=0.3mH		E _{AS}	84.5	mJ

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	P_{D}	0.9	W
Thermal Resistance, Junction to Ambient (Note 5)		$R_{ heta JA}$	138	°C/W
Total Power Dissipation (Note 6)	T _A = +25°C	P_{D}	2.2	W
Thermal Resistance, Junction to Ambient (Note 6)	$R_{ heta JA}$	57	°C/W	
Thermal Resistance, Junction to Case (Note 7)	$R_{ heta JC}$	3.5	°C/W	
Operating and Storage Temperature Range		T _J , T _{STG}	-55 to +150	°C


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)							
Drain-Source Breakdown Voltage	BV _{DSS}	60	_	_	V	$V_{GS} = 0V$, $I_D = 1mA$	
Zero Gate Voltage Drain Current	I _{DSS}	1	_	1	μΑ	$V_{DS} = 48V, V_{GS} = 0V$	
Gate-Source Leakage	I _{GSS}	_	_	±10	μΑ	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 8)							
Gate Threshold Voltage	V _{GS(TH)}	1.2	_	2.5	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$	
Static Drain-Source On-Resistance		_	4.3	5.7	mΩ	$V_{GS} = 10V, I_D = 20A$	
Static Drain-Source On-Resistance	R _{DS(ON)}	_	6.1	8.1	11177	$V_{GS} = 4.5V, I_D = 18A$	
Diode Forward Voltage	V_{SD}	_	0.8	1.2	V	$V_{GS} = 0V, I_{S} = 13.5A$	
DYNAMIC CHARACTERISTICS (Note 9)							
Input Capacitance	C _{iss}	_	2130	_		\\\\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	
Output Capacitance	Coss	_	786	_	pF	$V_{DS} = 30V$, $V_{GS} = 0V$, $f = 1MHz$	
Reverse Transfer Capacitance	C _{rss}	_	70	_			
Gate Resistance	Rg	_	0.6	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$	
Total Gate Charge (V _{GS} = 4.5V)	Q_g	_	20	_			
Total Gate Charge (V _{GS} = 10V)	Qg	_	37.5	_	nC	V 20V I 20A	
Gate-Source Charge	Q_{gs}	_	5.4	_	IIC	$V_{DS} = 30V, I_{D} = 20A$	
Gate-Drain Charge	Q_{gd}	_	9.5	_			
Turn-On Delay Time	t _{D(ON)}	_	5.5	_			
Turn-On Rise Time	t _R	_	6.8	_		$V_{DD} = 30V, V_{GS} = 10V,$	
Turn-Off Delay Time	t _{D(OFF)}	_	22.1	_	ns	$I_D = 20A$, $R_G = 3\Omega$	
Turn-Off Fall Time	t _F	_	10.8	_			
Reverse Recovery Time	t _{RR}	_	26.9	_	ns	1 200 4:/44 2000///-	
Reverse Recovery Charge	Q _{RR}	_	56.8	_	nC	I _F = 20A, di/dt = 300A/μs	

Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
 Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.
 Thermal resistance from junction to soldering point (on the exposed drain pad).
 Short duration pulse test used to minimize self-heating effect.

9. Guaranteed by design. Not subject to product testing.








Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage






Figure 5. Typical On-Resistance vs. Drain Current and Temperature








Figure 6. On-Resistance Variation with Temperature






Figure 7. On-Resistance Variation with Temperature




Figure 8. Gate Threshold Variation vs. Temperature






Figure 9. Diode Forward Voltage vs. Current



.



10 8 6 $V_{GS}(V)$ $V_{DS} = 30V, I_{D} = 20A$ 2 0 5 20 25 30 0 10 15 35 40 Qg (nC) Figure 11. Gate Charge

100







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




V-DFN3333-8							
(Type B)							
Dim	Min	Max	Тур				
Α	0.75	0.85	0.80				
A1	0.00	0.05	0.02				
A3	-		0.203				
b	0.27	0.37	0.32				
D	3.25	3.35	3.30				
D2	2.17	2.37	2.27				
E	3.25	3.35	3.30				
E2	1.85	2.05	1.95				
е	-		0.65				
k	1		0.33				
L	0.35	0.45	0.40				
L1	-		0.34				
Z	-		0.515				
All							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

V-DFN3333-8 (Type B)



Dimensions	Value (in mm)
С	0.650
C1	1.950
G	0.650
X	0.420
X1	2.370
Υ	0.700
Y1	0.400
Y2	2.150
Y3	0.450



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com