

Rated to +175°C—Ideal for High Ambient Temperature

Lead-Free Finish; RoHS Compliant (Notes 1 & 2) Halogen and Antimony Free. "Green" Device (Note 3)

Case Material: Molded Plastic, "Green" Molding Compound.

100% Unclamped Inductive Switching—Ensures More Reliable

**Features** 

Environments

**Mechanical Data** 

Case: TO263AB (D2PAK)

and Robust End Application

Low R<sub>DS(ON)</sub>—Minimizes Power Losses Low Qg—Minimizes Switching Losses

UL Flammability Classification Rating 94V-0

Moisture Sensitivity: Level 1 per J-STD-020 Terminal Connections: See Diagram Below

Weight: 1.7 grams (Approximate)

## **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> Max T <sub>C</sub> = +25°C
100V	9.5mΩ @ V <sub>GS</sub> = 10V	100A


### **Description and Applications**


This new generation N-channel enhancement mode MOSFET is designed to minimize  $R_{DS(ON)}$  yet maintain superior switching performance. This device is ideal for high-efficiency power management applications.

- Synchronous Rectification
- Inverter
- DC-DC Converters



Top View





Internal Schematic

## Ordering Information (Note 4)

Part Number	Case	Packaging
DMTH10H010LCTB-13	TO263AB (D2PAK)	800 / Tape & Reel

1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied. 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and


-

Notes:

Lead-free. 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

# **Marking Information**



J | = Manufacturer's Marking
T1H10LCTB = Product Type Marking Code
YYWW = Date Code Marking
YY = Last Two Digits of Year (ex: 18 = 2018)
WW = Week (01 to 53)



### Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	V <sub>DSS</sub>	100	V	
Gate-Source Voltage	V <sub>GSS</sub>	±20	V	
Continuous Drain Current	T <sub>C</sub> = +25°C T <sub>C</sub> = +100°C	I <sub>D</sub>	100 71	А
Maximum Continuous Body Diode Forward Current	T <sub>C</sub> = +25°C	Is	110	A
Pulsed Drain Current (10µs Pulse, T <sub>C</sub> =+25°C, Package Limited )		I <sub>DM</sub>	400	A
Pulsed Body Diode Forward Current (10µs Pulse, Tc=+25°C, Packag	I <sub>SM</sub>	400	A	
Avalanche Current, L=0.3mH (Note 7)	I <sub>AS</sub>	35	A	
Avalanche Energy, L=0.3mH (Note 7)	E <sub>AS</sub>	187	mJ	

### Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T <sub>A</sub> = +25°C	PD	3.9	W
Thermal Resistance, Junction to Ambient (Note 5)		R <sub>ƏJA</sub>	32	°C/W
Total Power Dissipation	T <sub>C</sub> = +25°C	PD	125	W
Thermal Resistance, Junction to Case		Rejc	1.0	°C/W
Operating and Storage Temperature Range		T <sub>J,</sub> T <sub>STG</sub>	-55 to +175	°C


# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

			_				
Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 6)							
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	100		—	V	$V_{GS} = 0V, I_D = 1mA$	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	_		1	μA	$V_{DS} = 80V, V_{GS} = 0V$	
Gate-Source Leakage	I <sub>GSS</sub>		_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 6)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	1.4	2.0	3.5	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$	
Static Drain-Source On-Resistance			8.7	9.5	mΩ	$V_{GS} = 10V, I_D = 13A$	
	R <sub>DS(ON)</sub>		13.2	17	11122	$V_{GS} = 4.5V, I_D = 13A$	
Diode Forward Voltage	V <sub>SD</sub>	_	0.8	1.3	V	$V_{GS} = 0V, I_{S} = 13A$	
DYNAMIC CHARACTERISTICS (Note 7)							
Input Capacitance	C <sub>iss</sub>	_	2592	—		$V_{DS} = 50V, V_{GS} = 0V$ f = 1MHz	
Output Capacitance	Coss	—	792	_	pF		
Reverse Transfer Capacitance	C <sub>rss</sub>	—	45	—			
Gate Resistance	Rg	—	2	_	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$	
Total Gate Charge	Qg	_	53.7	-		$V_{DD} = 50V, I_D = 13A, V_{GS} = 10V$	
Gate-Source Charge	Q <sub>gs</sub>	—	10.6	_	nC		
Gate-Drain Charge	Q <sub>gd</sub>	—	8.2	_			
Turn-On Delay Time	t <sub>D(ON)</sub>	_	11.6	-		V <sub>DD</sub> = 50V, V <sub>GS</sub> = 10V,	
Turn-On Rise Time	t <sub>R</sub>	_	14.1	—	ns		
Turn-Off Delay Time	t <sub>D(OFF)</sub>		42.9	_	ns	$I_D = 13A, R_g = 6\Omega$	
Turn-Off Fall Time	t <sub>F</sub>	_	22	—			
Reverse Recovery Time	t <sub>RR</sub>	_	49.8	_	ns		
Reverse Recovery Charge	Q <sub>RR</sub>	_	85.1	—	nC	I <sub>F</sub> = 13A, di/dt = 100A/µs	


 Device mounted on FR-4 substrate PCB, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.
Short duration pulse test used to minimize self-heating effect.
Guaranteed by design. Not subject to product testing. Notes:



#### 30 V<sub>GS</sub> = 10.0V $V_{GS} = 6.0V$ V<sub>GS</sub> = 5.0V 25 = 4.5V ′GS I<sub>D</sub>, DRAIN CURRENT (A) /<sub>GS</sub> = 4.0V 20 $V_{GS} = 3.5V$ 15 10 5 $V_{GS} = 3.0V$ 0 0 0.5 1.5 2 3 1 2.5 V<sub>DS</sub>, DRAIN - SOURCE VOLTAGE (V) Figure 1 Typical Output Characteristics 0.01 $\mathsf{R}_{\mathsf{DS}(\mathsf{ON})},$ DRAIN-SOURCE ON-RESISTANCE ( $\Omega)$ 0.009 0.008 $V_{GS} = 10V$ 0.007 0.006 0.005 0.004 0.003 0.002 10 15 20 25 30 35 40 I<sub>D</sub>, DRAIN-SOURCE CURRENT (A) 0 5 45 50 Figure 3 Typical On-Resistance vs. Drain Current and Gate Voltage 0.02 $\mathsf{R}_{\mathsf{DS}(\mathsf{ON})},$ DRAIN-SOURCE ON-RESISTANCE $(\Omega)$ $V_{GS} = 10V_{CS}$ 0.018 0.016 T<sub>A</sub> = 175°C 0.014 T<sub>A</sub> =150°C 0.012 T<sub>A</sub> =125°C T<sub>A</sub> =85 ℃ 0.01 0.008 =25 ℃ 0.006 T<sub>A</sub> =-55°C 0.004 0.002 0 15 20 25 0 5 10 30 DRAIN SOURCE CURRENT (A) I<sub>D</sub>, DRAIN SOURCE CONTENT Figure 5 Typical On-Resistance vs. Drain Current and Junction Temperature








DMTH10H010LCTB Document number: DS38064 Rev. 3 - 2








# **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.



TO263AB (D2PAK)						
Dim	Min	Max	Тур			
Α	4.07	4.82	-			
A1	0.00	0.25	-			
b	0.51	0.99	-			
b2	1.15	1.77	-			
c	0.356	0.73	-			
c2	1.143	-				
D	8.39	9.65	-			
D1	6.55	6.95	-			
е	:	2.54 TYP				
ш	9.66	10.66	-			
E1	6.23	-				
Н	14.61	15.87	-			
L	1.78	-				
L1	-	- 1.67				
L2	-	1.77	-			
L3	-	-	0.254			
а	0°	8°	-			
All Dimensions in mm						

# Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	5.08
Х	1.10
X1	10.41
Y	3.50
Y1	7.01
Y2	15.99

### TO263AB (D2PAK)



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

- 1. are intended to implant into the body, or
- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com