

# 100V 175°C DUAL N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

#### **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> max	I <sub>D</sub> max T <sub>C</sub> = +25°C
100V	$33m\Omega$ @ V <sub>GS</sub> = 10V	25A

#### **Description and Applications**

This new generation MOSFET features low on-resistance and fast switching, making it ideal for high efficiency power management applications.

- DC-DC converters
- Motors


#### **Features and Benefits**

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching (UIS) Test in Production Ensures More Reliable and Robust End Application
- Low Input Capacitance
- Fast Switching Speed
- Wettable Flank for Improved Optical Inspection
- Additional Tin-Plated on Sidewall Pads for Optical Solder Inspection
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

#### **Mechanical Data**

- Package: PowerDI<sup>®</sup>5060-8
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Copper Leadframe.
   Solderable per MIL-STD-202, Method 208 (a3)
- Weight: 0.097 grams (Approximate)

PowerDI5060-8/SWP (Type UXD)



#### **Ordering Information** (Note 4)

Part Number	Paakaga	Packing		
Part Number	Package	Qty.	Carrier	
DMTH10H038SPDW-13	PowerDI5060-8/SWP (Type UXD)	2500	Tape & Reel	


Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. PowerDI is a registered trademark of Diodes Incorporated.



## **Marking Information**



⊃¦¦ = Manufacturer's Marking H1038SPDW = Product Type Marking Code YYWW = Date Code Marking  $\overline{YY}$  = Year (ex: 22 = 2022) WW = Week (01 to 53)

## Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	VDSS	100	V	
Gate-Source Voltage	V <sub>GSS</sub>	±20	V	
Continuous Drain Current, $V_{GS} = 10V$ (Note 5) $T_{C} = +25^{\circ}C$ $T_{C} = +100^{\circ}C$		lo	25 18	А
Maximum Body Diode Forward Current	Is	25	A	
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I <sub>DM</sub>	100	A	
Pulsed Body Diode Forward Current (10µs Pulse, Tc=+25°C, Package Lin	Ism	100	Α	
Avalanche Current, L = 0.3mH	las	12.5	Α	
Avalanche Energy, L = 0.3mH	E <sub>AS</sub>	23.4	mJ	

## **Thermal Characteristics**

Characteristic		Symbol	Value	Unit
Thermal Resistance, Junction to Ambient (Note 6)		R <sub>θJA</sub>	55	°C/W
Total Power Dissipation T <sub>A</sub> = +25°C		PD	2.7	W
Thermal Resistance, Junction to Case (Note 5)		Rejc	3.8	°C/W
Total Power Dissipation $T_C = +25^{\circ}C$		P <sub>D</sub>	39	W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C

Notes:

5. Thermal resistance from junction to solder point (on the exposed drain pin).6. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.



## **Electrical Characteristics** (@T<sub>C</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)							
Drain-Source Breakdown Voltage	BVDSS	100	_	_	V	VGS = 0V, ID = 1mA	
Zero Gate Voltage Drain Current	IDSS	_	_	1	μΑ	V <sub>DS</sub> = 80V, V <sub>GS</sub> = 0V	
Gate-Source Leakage	I <sub>GSS</sub>	_	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)		I.	u		I	-	
Gate Threshold Voltage	VGS(TH)	2	_	4	V	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	_	25	33	mΩ	V <sub>GS</sub> = 10V, I <sub>D</sub> = 10A	
Diode Forward Voltage	V <sub>SD</sub>	_	0.9	1	V	V <sub>GS</sub> = 0V, I <sub>S</sub> = 10A	
DYNAMIC CHARACTERISTICS (Note 8)		I.	u		I	-	
Input Capacitance	Ciss	_	544	_	pF	50)/ )/ 0)/	
Output Capacitance	Coss	_	181	_	pF	V <sub>DS</sub> = 50V, V <sub>GS</sub> = 0V - f = 1MHz	
Reverse Transfer Capacitance	Crss	_	6.0	_	pF	11 = 11VID2	
Gate Resistance	Rg	_	1.2	_	Ω	$V_{DS} = 0V$ , $V_{GS} = 0V$ , $f = 1MHz$	
Total Gate Charge (V <sub>GS</sub> = 4.5V)	Qg	_	4.3		nC		
Total Gate Charge (V <sub>GS</sub> = 10V)	Qg	_	8.0	_	nC	7, 50,4 74	
Gate-Source Charge	Qgs	_	1.8	_	nC	$V_{DS} = 50V, I_{D} = 7A$	
Gate-Drain Charge	Qgd	_	2.4	_	nC		
Turn-On Delay Time	t <sub>D</sub> (ON)	_	8.5	_	ns		
Turn-On Rise Time	tR	_	2.7	_	ns	$V_{DS} = 50V$ , $I_{D} = 7A$ $V_{GS} = 10V$ , $R_{GEN} = 6\Omega$	
Turn-Off Delay Time	t <sub>D(OFF)</sub>		11.9	_	ns		
Turn-Off Fall Time	tF	_	6.2	_	ns	1	
Reverse Recovery Time	trr		33.2		ns	1- 74 di/dt 1004/up	
Reverse Recovery Charge	Q <sub>RR</sub>	_	34.3	_	nC	I <sub>F</sub> = 7A, di/dt = 100A/μs	

Notes:

<sup>7.</sup> Short duration pulse test used to minimize self-heating effect. 8. Guaranteed by design. Not subject to product testing.








Figure 1. Typical Output Characteristic




Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 5. Typical On-Resistance vs. Drain Current and Junction Temperature




Figure 2. Typical Transfer Characteristic




Figure 4. Typical Transfer Characteristic




Figure 6. On-Resistance Variation with Junction Temperature








Figure 7. On-Resistance Variation with Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance





## **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5060-8/SWP (Type UXD)










PowerDI5060-8/SWP (Type UXD)					
Dim	Min Max		Тур		
Α	0.90	1.10	1.00		
A1	0.00	0.05			
b	0.30	0.50	0.41		
b2	0.20	0.35	0.25		
b4	(	).25REF	=		
С	0.230	0.330	0.277		
D	5.15 BSC				
D1	4.70	5.10	4.90		
D2	1.46	1.66	1.55		
D3	3.78	3.78 4.18 3.9			
Е	6	.40 BS0	)		
E1	5.60	6.00	5.80		
E2	3.46	3.86	3.66		
E2a	4.195				
е	1	.27BSC	)		
k	1.05				
L	0.635	0.835	0.735		
La	0.635	0.835	0.735		
L1	0.200	0.400	0.300		
M	3.205	4.005	3.605		
W	0.025	0.225	0.125		
θ	10°	12°	11°		
θ1	6°	8°	7°		
All	All Dimensions in mm				

## **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5060-8/SWP (Type UXD)



Dimensions	Value		
Dillielisions	(in mm)		
С	1.270		
G	0.660		
G1	0.820		
Х	0.610		
X1	1.720		
X2	4.420		
Υ	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (<a href="https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/">https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/</a>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com