



100V 175°C DUAL N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _C = +25°C	
100V	17.4mΩ @ V _{GS} = 10V	59A	
100 V	$30.3 \text{m}\Omega$ @ V _{GS} = 4.5V	45A	

Features and Benefits

- Rated to +175°C—Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching (UIS) Test in Production— Ensures More Reliable and Robust End Application
- High Conversion Efficiency
- Low R_{DS(ON)}—Minimizes On State Losses
- Low Input Capacitance
- Fast Switching Speed
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMTH10H017LPDQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Description and Applications

This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP, and is ideal for use in:

- Synchronous Rectifier
- DC-DC Converters
- Primary Side Switching

Mechanical Data

- Case: PowerDI[®]5060-8
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish—Matte Tin Annealed over Copper Leadframe.
 Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)



Ordering Information (Note 4)


Part Number	Case	Packaging
DMTH10H017LPDQ-13	PowerDI5060-8 (Type E)	2500 / Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information



⊃¦¦= Manufacturer's Marking H10H017LD = Product Type Marking Code YYWW = Date Code Marking YY = Year (ex: 19 = 2019) WW = Week (01 to 53)

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	VDSS	100	V	
Gate-Source Voltage	Vgss	±20	V	
Continuous Drain Current, V _{GS} = 10V (Note 7)	T _C = +25°C	I-	59	А
Continuous Diain Current, VGS = 10V (Note 7)	$T_{C} = +100^{\circ}C$	I _D	42	
	$T_A = +25$ °C		13	
Continuous Drain Current, Vgs = 10V (Note 6)	$T_A = +85^{\circ}C$	ID	10	Α
	$T_A = +100^{\circ}C$		9	
Maximum Body Diode Forward Current (Note 6)	Is	60	Α	
Pulsed Drain Current (10µs Pulse, T _C = +25°C, Package Limited)	I _{DM}	236	Α	
Pulsed Body Diode Forward Current (10µs Pulse, Tc = +25°C, Package	Ism	236	Α	
Avalanche Current, L = 3mH (Note 8)	IAS	10	Α	
Avalanche Energy, L = 3mH (Note 8)	Eas	150	mJ	
Avalanche Current, L = 1mH (Note 8)	I _{AS}	10	Α	
Avalanche Energy, L = 1mH (Note 8)	Eas	50	mJ	

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	$T_A = +25$ °C	P _D	1.5	W
Thermal Resistance, Junction to Ambient (Note 5)		Rөja	100	°C/W
Total Power Dissipation (Note 6)	T _A = +25°C	PD	2.6	W
Thermal Resistance, Junction to Ambient (Note 6)		Reja	56	°C/W
Total Power Dissipation	T _C = +25°C	P _D	93	W
Thermal Resistance, Junction to Case (Note 7)		Rejc	1.6	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C

Notes:

- 5. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
- 6. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.
- 7. Thermal resistance from junction to solder point (on the exposed drain pin).
- 8. I_{AS} and E_{AS} ratings are based on low frequency and duty cycles to keep $T_J = +25$ °C.



Electrical Characteristics (@T_C = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 9)	•		•				
Drain-Source Breakdown Voltage	BVDSS	100	_	_	V	V _{GS} = 0V, I _D = 1mA	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1	μA	V _{DS} = 80V, V _{GS} = 0V	
Gate-Source Leakage	I _{GSS}	_	_	±100	nA	$V_{GS} = \pm 16V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 9)	•						
Gate Threshold Voltage	Vgs(TH)	1	_	3	V	V _{DS} = V _{GS} , I _D = 250μA	
Static Drain-Source On-Resistance	D	_	13.7	17.4	mΩ	V _G S = 10V, I _D = 17A	
Static Dialii-Source Off-Resistance	R _{DS(ON)}	_	23.8	30.3	11112	V _{GS} = 4.5V, I _D = 10A	
Diode Forward Voltage	VsD	_	0.8	1.3	V	V _G S = 0V, I _S = 17A	
DYNAMIC CHARACTERISTICS (Note 10)				•	•		
Input Capacitance	Ciss	_	1986	_		V _{DS} = 50V, V _{GS} = 0V, f = 1MHz	
Output Capacitance	Coss	_	333	_	pF		
Reverse Transfer Capacitance	Crss	_	20	_		1 – 11/11/12	
Gate Resistance	Rg	_	1.17	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$	
Total Gate Charge (V _{GS} = 4.5V)	Qg	_	14.4	_			
Total Gate Charge (V _{GS} = 10V)	Qg	_	28.6	_	nC	V _{DS} = 50V, I _D = 20A	
Gate-Source Charge	Qgs	_	5.2	_	IIC		
Gate-Drain Charge	Qgd	_	8.2	_			
Turn-On Delay Time	t _{D(ON)}	_	9.8	_		V _{DD} = 50V, V _{GS} = 10V,	
Turn-On Rise Time	t _R	_	16.3	_			
Turn-Off Delay Time	tD(OFF)	_	32.6	_	ns	$R_G = 11\Omega, I_D = 20A$	
Turn-Off Fall Time	tF	_	21.6	_			
Body Diode Reverse Recovery Time	t _{RR}		40.6	_	ns	I _F = 17A, di/dt = 100A/μs	
Body Diode Reverse Recovery Charge	Q _{RR}	_	58.1	_	nC	I _F = 17A, di/dt = 100A/µs	

Notes:

^{9.} Short duration pulse test used to minimize self-heating effect. 10. Guaranteed by design. Not subject to product testing.




4.5

5

20

16





I_D, DRAIN CURRENT (A) Figure 5. Typical On-Resistance vs. Drain Current and Temperature

15

20

10

25

50 75 100 125 150 175

0

0.008

0.006 0.004 0.6

0.4

-50

 $T_J = -55^{\circ}C$

25

30








Figure 7. On-Resistance Variation with Temperature




Figure 9. Diode Forward Voltage vs. Current 10 8 6 $V_{GS}(V)$ 4 $V_{DS} = 50V, I_{D} = 20A$ 2 0 0 5 10 15 20 25 30 Q_q (nC)

Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. JunctionTemperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8 (Type E)




PowerDI5060-8 (Type E)					
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0	0.05	0.02		
b	0.33	0.51	0.41		
b1	0.300	0.366	0.333		
b2	0.20	0.35	0.25		
С	0.23	0.33	0.277		
D	5	.15 BS0	\sim		
D1	4.85	4.95	4.90		
D2	1.40	1.60	1.50		
D3			3.98		
Е		.15 BS(2		
E1	5.75	5.85	5.80		
E2	3.56	3.76	3.66		
е	1	.27BSC			
k		_	1.27		
k1	0.56	_	_		
L	0.51	0.71	0.61		
La	0.51	0.71	0.61		
L1	0.05	0.20	0.175		
L4	_	_	0.125		
M	3.50	3.71	3.605		
X		_	1.400		
у	_	_	1.900		
θ	10°	12°	11°		
θ1	6°	8°	7°		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8 (Type E)



Dimensions	Value		
Dilliensions	(in mm)		
С	1.270		
G	0.660		
G1	0.820		
X	0.610		
X1	3.910		
X2	1.650		
Х3	1.650		
X4	4.420		
Y	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com