

DMTH42M4SPS

40V +175°C N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

## Product Summary

BV <sub>DSS</sub>	Rds(on) Max	I <sub>D</sub> Tc = +25°С
40V	2.4mΩ @ V <sub>GS</sub> = 10V	200A

# **Description and Applications**

This MOSFET is designed to minimize the on-state resistance (RDS(ON)) yet maintain superior switching performance, making it ideal for high efficiency power management applications.


- Engine management systems
- Body control electronics
- **DC-DC** converters


#### Features and benefits

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching (UIS) Test in Production -Ensures More Reliable and Robust End Application
- Thermally Efficient Package-Cooler Running Applications
- High Conversion Efficiency
- Low RDS(ON) Minimizes On State Losses
- <1.1mm Package Profile Ideal for Thin Applications
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

#### **Mechanical Data**

- Package: PowerDI<sup>®</sup>5060-8
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 @3
  - Weight: 0.097 grams (Approximate)





# Ordering Information (Note 4)

Part Number	Paakaga	Pac	Packing		
Fart Nulliber	Package	Qty.	Carrier		
DMTH42M4SPS-13	PowerDI5060-8 (Type K)	2,500	Tape & Reel		


1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied. Notes:

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

# Marking Information



 H = Manufacturer's Marking TH42M4SS = Product Type Marking Code YYWW = Date Code Marking YY = Last Two Digits of Year (ex: 22 = 2022) WW = Week Code (01 to 53)

PowerDI is a registered trademark of Diodes Incorporated. DMTH42M4SPS

Document number: DS45215 Rev. 2 - 2



# Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	Vdss	40	V	
Gate-Source Voltage	Vgss	±20	V	
Continuous Drain Current, V <sub>GS</sub> = 10V (Note 6)	Tc = +25°C Tc = +100°C	ID	200 140	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)		I <sub>DM</sub>	800	A
Continuous Body Diode Forward Current (Note 6)	Tc = +25°C	ls	200	А
Pulsed Body Diode Forward Current (10µs Pulse, Duty Cycle = 1%)	lsм	800	А	
Avalanche Current, L = 0.1mH	las	72.8	А	
Avalanche Energy, L = 0.1mH	E <sub>AS</sub>	265	mJ	

#### **Thermal Characteristics**

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T <sub>A</sub> = +25°C	PD	3.06	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	RθJA	49	°C/W
Total Power Dissipation (Note 6)	Tc = +25°C	PD	150	W
Thermal Resistance, Junction to Case (Note 6)		R <sub>θ</sub> JC	1.0	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C

# Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)					•		
Drain-Source Breakdown Voltage	BVDSS	40	_	_	V	$V_{GS} = 0V, I_{D} = 250 \mu A$	
Zero Gate Voltage Drain Current	IDSS	—	_	1	μA	V <sub>DS</sub> = 32V, V <sub>GS</sub> = 0V	
Gate-Source Leakage	lgss	—	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	VGS(TH)	2	—	4	V	$V_{DS} = V_{GS}$ , $I_D = 250 \mu A$	
Static Drain-Source On-Resistance	RDS(ON)	_	1.8	2.4	mΩ	V <sub>GS</sub> = 10V, I <sub>D</sub> = 30A	
Diode Forward Voltage	V <sub>SD</sub>	—	0.8	1.2	V	$V_{GS} = 0V, I_{S} = 20A$	
DYNAMIC CHARACTERISTICS (Note 8)							
Input Capacitance	Ciss		6968	_		V <sub>DS</sub> = 20V, V <sub>GS</sub> = 0V, f = 1MHz	
Output Capacitance	Coss	—	1812		pF		
Reverse Transfer Capacitance	Crss	—	59	_			
Gate Resistance	Rg	_	1.21	—	Ω	$V_{DS} = 0V$ , $V_{GS} = 0V$ , $f = 1MHz$	
Total Gate Charge	Qg	_	79.5	_		$V_{DD} = 20V, I_D = 90A,$ $V_{GS} = 10V$	
Gate-Source Charge	Q <sub>gs</sub>	_	20.6	—	nC		
Gate-Drain Charge	Q <sub>gd</sub>	_	16.5	_			
Turn-On Delay Time	tD(ON)	_	13.3	—		$V_{DD}$ = 20V, $V_{GS}$ = 10V, I <sub>D</sub> = 90A, R <sub>G</sub> = 3.5Ω	
Turn-On Rise Time	t <sub>R</sub>	_	41.3		ns		
Turn-Off Delay Time	tD(OFF)		35.1	_			
Turn-Off Fall Time	tF		13.7	—	]		
Reverse Recovery Time	t <sub>RR</sub>		62	—	ns	L= 500 di/dt 1000/up	
Reverse Recovery Charge	QRR	_	103		nC	IF = 50A, di/dt = 100A/μs	


Notes: 5. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.

Device information of the substrate recordary, 202 copper, with financial basis to
Thermal resistance from junction to soldering point (on the exposed drain pad).
Short duration pulse test used to minimize self-heating effect.
Guaranteed by design. Not subject to product testing.




#### DMTH42M4SPS






DMTH42M4SPS Document number: DS45215 Rev. 2 - 2








DMTH42M4SPS Document number: DS45215 Rev. 2 - 2 4 of 7 www.diodes.com








# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.




PowerDI5060-8 (Type K)

	PowerDI5060-8 (Type K)				
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0	0.05	0.02		
b	0.33	0.51	0.41		
b1	0.300	0.366	0.333		
b2	0.20	0.35	0.25		
С	0.23	0.33	0.277		
D	5	.15 BS0	0		
D1	4.85	4.95	4.90		
D2	-	-	3.98		
E	6	.15 BS0	0		
E1	5.75	5.85	5.80		
E2	3.56	3.725	3.66		
е	1	.27BSC	)		
k	-	-	1.27		
L	0.51	0.71	0.61		
La	0.51	0.675	0.61		
L1 L4	0.05	0.20	0.175		
L4	-	-	0.125		
Μ	3.50	3.71	3.605		
х	-	-	1.400		
У	-	-	1.900		
θ	10°	12°	11°		
θ1	6°	8°	7°		
All	All Dimensions in mm				

### **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5060-8 (Type K)



Dimensions	Value (in mm)		
С	1.270		
G	0.660		
G1	0.820		
Х	0.610		
X1	3.910		
X2	4.420		
Y	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' provided Diodes' Standard Terms and Conditions of Sale products are subject to (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

#### www.diodes.com