



60V 175°C N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _C = +25°C (Note 9)
60V	3.1mΩ @ V _{GS} = 10V	100A

Description and Applications

This new generation MOSFET features low on-resistance and fast switching, making it ideal for high-efficiency power-management applications.

- DC motor controls
- Synchronous rectifications
- DC/DC converters


Features


- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching (UIS) Test in Production Ensures More Reliable And Robust End Application
- Low R_{DS(ON)} Minimizes Power Losses
- Low Q_q Minimizes Switching Losses
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An automotive-compliant part is available under separate datasheet (<u>DMTH6004SPSQ</u>)


Mechanical Data

- Package: PowerDI[®]5060-8
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Finish Matte Tin Annealed over Copper Leadframe.
 Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)

Site1:









Site2:

PowerDI5060-8/SWP (Type UX)





Internal Schematic



Notes: 1.

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.




Ordering Information (Note 4)

Part Number	Packago	Packing		
Fait Number	Package	Qty.	Carrier	
DMTH6004SPS-13	PowerDI5060-8	2,500	Tape & Reel	
DMTH6004SPS-13	PowerDI5060-8/SWP (Type UX)	2,500	Tape & Reel	

Note: 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information





☐ Hanufacturer's Marking
☐ H6004SS = Product Type Marking Code
☐ YYWW or YYWW = Date Code Marking
☐ YY or YY = Year (ex: 23 = 2023)
☐ WW = Week (01 to 53)



Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V_{DSS}	60	V
Gate-Source Voltage			Vgss	±20	V
Continuous Drain Current (Note 5) Steady state $T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$		ΙD	25 21	Α	
Continuous Drain Current (Notes 6 & 9) $Tc = +25^{\circ}C$ $Tc = +100^{\circ}C$			lo	100 100	Α
Maximum Continuous Body Diode Forward Current (Notes 6 & 9)			Is	100	Α
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)			lрм	400	Α
Pulsed Body Diode Forward Current (10µs Pulse, Duty Cycle = 1%)			I _{SM}	400	Α
Avalanche Current, L = 0.2mH	Avalanche Current, L = 0.2mH			45	Α
Avalanche Energy, L = 0.2mH			Eas	200	mJ

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	PD	3.2	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady state	Reja	47	°C/W
Total Power Dissipation (Note 6)	T _C = +25°C	P _D	167	W
Thermal Resistance, Junction to Case (Note 6)		Rejc	0.9	°C/W
Operating and Storage Temperature Range		$T_{J,}T_{STG}$	-55 to +175	°C

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						
Drain-Source Breakdown Voltage	BV _{DSS}	60	1		V	$V_{GS} = 0V$, $I_D = 1mA$
Zero Gate Voltage Drain Current	IDSS	l		1	μΑ	V _{DS} = 48V, V _{GS} = 0V
Gate-Source Leakage	Igss	1	1	±100	nA	$V_{GS} = \pm 20V$, $V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	V _{GS(TH)}	2	_	4	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$
Static Drain-Source On-Resistance	R _{DS(ON)}	1	2.5	3.1	mΩ	$V_{GS} = 10V, I_{D} = 50A$
Diode Forward Voltage	VsD		0.9	1.2	V	V _G S = 0V, I _S = 20A
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	Ciss	1	4556	_		V _{DS} = 30V, V _{GS} = 0V, f = 1MHz
Output Capacitance	Coss	l	1383	_	pF	
Reverse Transfer Capacitance	Crss		105.2	_		
Gate Resistance	Rg	_	0.66	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$
Total Gate Charge	Qg	_	95.4	_		V 00V I 00A
Gate-Source Charge	Qgs		21.6	_	nC	$V_{DD} = 30V, I_{D} = 90A,$ $V_{GS} = 10V$
Gate-Drain Charge	Q_{gd}		20.4	_		VGS = 10V
Turn-On Delay Time	td(ON)		13.2	_		
Turn-On Rise Time	t _R	_	11.7	_	20	$V_{DD} = 30V, V_{GS} = 10V,$ $I_{D} = 90A, R_{G} = 3.5\Omega$
Turn-Off Delay Time	tD(OFF)		31	_	ns	
Turn-Off Fall Time	tF	1	12	_		
Body Diode Reverse Recovery Time	t _{RR}	_	50.5	_	ns	I
Body Diode Reverse Recovery Charge	Qrr		80.8	_	nC	IF = 50A, di/dt = 100A/μs


Notes: 5. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.


- 6. Thermal resistance from junction to soldering point (on the exposed drain pad).7. Short duration pulse test used to minimize self-heating effect.
- Short duration pulse test used to minimize sen-neating en
 B. Guaranteed by design. Not subject to product testing.
- Package limited.











and Gate Voltage

Figure 5 Typical On-Resistance vs Drain Current and Temperature





Figure 2 Typical Transfer Characteristic



2.2 R_{DS(ON)}, DRAIN-SOURCE ON-RESISTANCE (NORMALIZED) 2 1.8 $V_{GS} = 10V, I_{D} = 90A$ 1.6 1.4 1.2 $V_{GS} = 20V, I_{D} = 100A$ 1 8.0 0.6 0.4 -50 -25 25 50 75 100 125 150 175 T₁, JUNCTION TEMPERATURE (°C)

Figure 6 On-Resistance Variation with Temperature










Figure 7 On-Resistance Variation with Temperature









Figure 8 Gate Threshold Variation vs Temperature



1000 R_{DS(ON)} Limited 100 ID, DRAIN CURRENT (A) P_W =10ms 10 P_W =100μs $T_{J(Max)} = 175^{\circ}C$ $T_C = 25^{\circ}C$ Single Pulse $P_W = 10 \mu s$ **DUT** on Infinite Heatsink V_{GS}= 10V 0.1 100 V_{DS} , DRAIN-SOURCE VOLTAGE (V) Figure 12. SOA, Safe Operation Area






Figure 13. Transient Thermal Resistance




Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site 1:


PowerDI5060-8



PowerDI5060-8					
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0.00	0.05	-		
b	0.33	0.51	0.41		
b2	0.200	0.350	0.273		
b3	0.40	0.80	0.60		
С	0.230	0.330	0.277		
D		5.15 BSC	;		
D1	4.70	5.10	4.90		
D2	3.70	4.10	3.90		
D3	3.90	4.30	4.10		
Е	(6.15 BSC	,		
E1	5.60	6.00	5.80		
E2	3.28	3.68	3.48		
E3	3.99	4.39	4.19		
е	•	1.27 BSC			
G	0.51	0.71	0.61		
K	0.51	-	_		
L	0.51	0.71	0.61		
L1	0.100	0.200	0.175		
М	3.235	4.035	3.635		
M1	1.00	1.40	1.21		
Θ	10°	12°	11°		
Θ1	6°	8°	7°		
All Dimensions in mm					

Site 2:

PowerDI5060-8/SWP (Type UX)



PowerDI5060-8/SWP					
(Type UX)					
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0	0.05			
b	0.30	0.50	0.41		
b2	0.20	0.35	0.25		
b4).25REF			
С	0.230	0.330	0.277		
D	5	.15 BS0)		
D1	4.70	5.10	4.90		
D2	3.56	3.96	3.76		
D2a	3.78	4.18	3.98		
Е		.40 BS0			
E1	5.60	6.00	5.80		
E2	3.46	3.86	3.66		
E2a	4.195	4.595	4.395		
е		.27BSC)		
k	1.05				
L	0.635	0.835	0.735		
La	0.635	0.835	0.735		
L1	0.200	0.400	0.300		
L1a	0.050REF				
L4	0.025	0.225	0.125		
M	3.205	4.005	3.605		
θ	10°	12°	11°		
θ1	6°	8°	7°		
All Dimensions in mm					




Suggested Pad Layout

 $\label{prop:lease} Please see \ http://www.diodes.com/package-outlines.html \ for \ the \ latest \ version.$

Site 1:


PowerDI5060-8



C 1.270 G 0.660 G1 0.820 X 0.610 X1 4.100 X2 0.755 X3 4.420 X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180 Y7 6.610	Dimensions	Value (in mm)
G1 0.820 X 0.610 X1 4.100 X2 0.755 X3 4.420 X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	С	1.270
X 0.610 X1 4.100 X2 0.755 X3 4.420 X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	G	0.660
X1 4.100 X2 0.755 X3 4.420 X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	G1	0.820
X2 0.755 X3 4.420 X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	Х	0.610
X3 4.420 X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	X1	4.100
X4 5.610 Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	X2	0.755
Y 1.270 Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	Х3	4.420
Y1 0.600 Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	X4	5.610
Y2 1.020 Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	Υ	1.270
Y3 0.295 Y4 1.825 Y5 3.810 Y6 0.180	Y1	0.600
Y4 1.825 Y5 3.810 Y6 0.180	Y2	1.020
Y5 3.810 Y6 0.180	Y3	0.295
Y6 0.180	Y4	1.825
	Y5	3.810
Y7 6.610	Y6	0.180
	Y7	6.610

Site 2:

PowerDI5060-8/SWP (Type UX)



Dimensions	Value (in mm)
С	1.270
G	0.660
G1	0.820
X	0.610
X1	4.100
X2	5.190
Х3	4.420
Y	1.270
Y1	1.020
Y2	3.810
Y3	6.610



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com