



### 30V 175°C N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

### **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> Max T <sub>C</sub> = +25°C
	3.8mΩ @ V <sub>GS</sub> = 10V	145A
30V	6mΩ @ V <sub>GS</sub> = 4.5V	115A

## **Description and Applications**

This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- Backlighting
- Power Management Functions
- DC-DC Converters

## **Features and Benefits**

- Low Rds(ON) Minimizes On-State Losses
- Excellent Q<sub>gd</sub> x R<sub>DS(ON)</sub> Product (FOM)
- Small Form Factor Thermally Efficient Package Enables Higher Density End Products
- 100% Unclamped Inductive Switching Ensures More Reliability
- Rated to +175°C Ideal for High Ambient Temperature Environments
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMTH3004LPSQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


#### **Mechanical Data**


- Case: PowerDI<sup>®</sup>5060-8
- Case Material: Molded Plastic, "Green" Molding Compound.
  UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Diagram
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)



Top View







**Ordering Information** (Note 4)

Part Number	Case	Packaging
DMTH3004LPSQ-13	PowerDI5060-8	2,500/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

## **Marking Information**



⊃¦¦ = Manufacturer's Marking H3004LS = Product Type Marking Code YYWW = Date Code Marking YY = Year (ex: 21 = 2021) WW = Week (01 to 53)



# **Maximum Ratings** (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Drain-Source Voltage		$V_{DSS}$	30	V
Gate-Source Voltage		Vgss	+20 -16	V
Continuous Drain Current (Note 5)	T <sub>A</sub> = +25°C T <sub>A</sub> = +100°C	lo	22 16	А
Continuous Drain Current (Note 6)	$T_{C} = +25^{\circ}C$ $T_{C} = +100^{\circ}C$	lo	145 103	А
Maximum Continuous Body Diode Forward Current	Is	100	Α	
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I <sub>DM</sub>	180	Α	
Avalanche Current, L=0.3mH	I <sub>AS</sub>	27	Α	
Avalanche Energy, L=0.3mH	E <sub>AS</sub>	110	mJ	

## **Thermal Characteristics**

Characteristic	Symbol	Value	Unit	
Total Power Dissipation	PD	136	W	
Thermal Resistance, Junction to Ambient (Note 5)	Reja	47	°C/W	
Thermal Resistance, Junction to Case (Note 6)	R <sub>0</sub> JC	1.1	1 10/00	
Operating and Storage Temperature Range	Т <sub>J</sub> , Тsтg	-55 to +175	°C	

### Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)							
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	30	_	_	V	$V_{GS} = 0V, I_{D} = 250\mu A$	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	_	_	1	μΑ	$V_{DS} = 24V, V_{GS} = 0V$	
Zero Gate Voltage Drain Current (Note 8)	I <sub>DSS</sub>		_	10	μΑ	V <sub>DS</sub> = 24V, V <sub>GS</sub> = 0V T <sub>J</sub> = +125°C	
Gate-Source Leakage	Igss	1	l	±100	nA	V <sub>GS</sub> = +20V, V <sub>DS</sub> = 0V V <sub>GS</sub> = -16V, V <sub>DS</sub> = 0V	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	Vgs(th)	1	1.6	3	V	$V_{DS} = V_{GS}$ , $I_D = 250\mu A$	
Static Drain-Source On-Resistance	RDS(ON)	_	3.3	3.8	mΩ	$V_{GS} = 10V, I_D = 20A$	
Static Dialif-Source Off-Resistance	RDS(ON)	_	5	6		$V_{GS} = 4.5V, I_{D} = 7A$	
Diode Forward Voltage	VsD		0.70	1	V	$V_{GS} = 0V$ , $I_{S} = 1A$	
DYNAMIC CHARACTERISTICS							
Input Capacitance (Note 8)	Ciss		2370	_		V <sub>DS</sub> = 15V, V <sub>GS</sub> = 0V, f = 1MHz	
Output Capacitance (Note 8)	Coss	_	1360	_	pF		
Reverse Transfer Capacitance (Note 8)	Crss		240	_			
Gate Resistance	Rg	0.14	0.7	1.75	Ω	$V_{DS} = 0V$ , $V_{GS} = 0V$ , $f = 1MHz$	
SWITCHING CHARACTERISTICS (Note 8)							
Total Gate Charge (VGS = 10V)	Qg		43.7	_			
Gate-Source Charge	$Q_{gs}$	_	6.9	_	nC	$V_{DS} = 15V, I_{D} = 20A$	
Gate-Drain Charge	$Q_{gd}$		8	_			
Turn-On Delay Time	td(ON)		6.2	_		$V_{DD} = 15V, V_{GS} = 10V,$ $R_{G} = 3\Omega, R_{L} = 0.75\Omega$	
Turn-On Rise Time	t <sub>R</sub>		4.2	_	ns		
Turn-Off Delay Time	tD(OFF)		21	_	115		
Turn-Off Fall Time	tF	_	8	_			
Body Diode Reverse Recovery Time	trr	_	25	_	ns L 454 H/H 5004/		
Body Diode Reverse Recovery Charge	Q <sub>RR</sub>		37	_	nC IF = 15A, 0	I <sub>F</sub> = 15A, dI/dt = 500A/μs	


Notes:

Device mounted with exposed drain pad on 25mm by 25mm 2oz copper on a single- sided 1.6mm FR-4 PCB; device is measured under still air conditions whilst operating in a steady state.
 Thermal resistance from junction to soldering point (on the exposed drain pad).
 Short duration pulse test used to minimize self-heating effect.


<sup>8.</sup> Guaranteed by design. Not subject to production testing.










Gate Voltage












Figure 6. On-Resistance Variation with Junction Temperature






Figure 7. On-Resistance Variation with Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature





Figure 10. Typical Junction Capacitance









Figure 13. Transient Thermal Resistance



## **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

## PowerDI5060-8




PowerDI5060-8					
Dim	Min	Тур			
Α	0.90	1.10	1.00		
A1	0.00	0.05	-		
b	0.33	0.51	0.41		
b2	0.200	0.350	0.273		
b3	0.40	0.80	0.60		
C	0.230	0.330	0.277		
D		5.15 BSC	;		
D1	4.70	5.10	4.90		
D2	3.70	4.10	3.90		
D3	3.90	4.30	4.10		
Е	(	6.15 BSC	;		
E1	5.60	6.00	5.80		
E2	3.28	3.68	3.48		
E3	3.99	4.39	4.19		
е	1.27 BSC				
G	0.51	0.71	0.61		
K	0.51	-	-		
L	0.51	0.71	0.61		
L1	0.100	0.200	0.175		
M	3.235	4.035	3.635		
M1	1.00	1.40	1.21		
Θ	10°	12°	11°		
Θ1	6°	8°	7°		
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5060-8



Dimensions	Value (in mm)		
С	1.270		
G	0.660		
G1	0.820		
X	0.610		
X1	4.100		
X2	0.755		
Х3	4.420		
X4	5.610		
Y	1.270		
Y1	0.600		
Y2	1.020		
Y3	0.295		
Y4	1.825		
Y5	3.810		
<b>Y6</b> 0.180			
Y7	6.610		



#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com