



40V +175°C N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI3333-8

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _C = +25°C
40V	8.9mΩ @ V _{GS} = 10V	49.0A
40 V	13.5mΩ @ V _{GS} = 4.5V	40.0A

Features and Benefits

- Rated to +175°C Ideal for High Ambient Temperature Environments
- Low Rds(ON) Ensures On-State Losses are Minimized
- Excellent Qgd x RDS(ON) Product (FOM)
- Wettable Flank for Improved Optical Inspection
- 100% Unclamped Inductive Switching (UIS) Test in Production –
 Ensures More Reliable and Robust End Application
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMTH47M2LFVWQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Description and Applications


This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:


- Backlighting
- Power-management functions
- DC-DC converters

Mechanical Data

- Package: PowerDI[®]3333-8
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Copper Leadframe; Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.027 grams (Approximate)







Ordering Information (Note 4)

Part Number	Package	Packing		
Fait Number	Package	Qty.	Carrier	
DMTH47M2LFVWQ-7	PowerDI3333-8 (SWP) (Type UX)	2,000	Tape & Reel	
DMTH47M2LFVWQ-13	PowerDI3333-8 (SWP) (Type UX)	3,000	Tape & Reel	

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information

PowerDI3333-8 (SWP) (Type UX)



M2L = Product Type Marking Code

YYWW = Date Code Marking

YY = Last Two Digits of Year (ex: 23 = 2023)

WW = Week Code (01 to 53)

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V _{DSS}	40	V
Gate-Source Voltage			Vgss	±20	V
(Continuous Drain Current (Note 5) Voc = 10V		$T_{C} = +25^{\circ}C$ $T_{C} = +100^{\circ}C$	ID	49.0 34.7	А
Continuous Drain Current (Note 6), V _{GS} = 10V	Steady State	T _A = +25°C T _A = +100°C	ID	13.6 9.6	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 19	I _{DM}	196	А		
Maximum Continuous Body Diode Forward Current (Note 5)			Is	49	А
Pulsed Body Diode Forward Current (10µs Pulse, Duty Cycle = 1%)			Isм	196	Α
Avalanche Current, L = 0.1mH			las	24	А
Avalanche Energy, L = 0.1mH			Eas	28.8	mJ

Thermal Characteristics

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 6)	T _A = +25°C	PD	2.9	W
Thermal Resistance, Junction to Ambient (Note 6) Steady State		Reja	52	°C/W
Total Power Dissipation (Note 5)	PD	37.5	W	
Thermal Resistance, Junction to Case (Note 5)	R ₀ JC	4	°C/W	
Operating and Storage Temperature Range	TJ, TSTG	-55 to +175	°C	

Notes:

^{5.} Thermal resistance from junction to soldering point (on the exposed drain pad).

^{6.} Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)							
Drain-Source Breakdown Voltage		40	_	_	V	V _G S = 0V, I _D = 250µA	
Zero Gate Voltage Drain Current	IDSS		_	1	μA	V _{DS} = 32V, V _{GS} = 0V	
Gate-Source Leakage				±100	nA	$V_{GS} = \pm 20V$, $V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	Vgs(TH)	1.2	-	2.3	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$	
Static Drain-Source On-Resistance	Dag.		6.6	8.9	mΩ	$V_{GS} = 10V, I_D = 20A$	
Static Drain-Source On-Resistance	R _{DS(ON)}		8.9	13.5	11122	$V_{GS} = 4.5V, I_D = 10A$	
Diode Forward Voltage	VsD		0.87	1.2	V	V _G S = 0V, I _S = 20A	
DYNAMIC CHARACTERISTICS (Note 8)	DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	C _{iss}		881	_			
Output Capacitance	Coss		496		pF	$V_{DS} = 20V$, $V_{GS} = 0V$ f = 1MHz	
Reverse Transfer Capacitance	Crss	_	19.5	_		1 - 1101112	
Gate Resistance	Rg	_	2.06	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$	
Total Gate Charge (V _{GS} = 10V)	Q_g		12.3	_			
Total Gate Charge (V _{GS} = 4.5V)	Qg		5.8	_	nC	\/ 20\/ I= 20\	
Gate-Source Charge	Qgs		2.6	_	IIC	V _{DS} = 20V, I _D = 20A	
Gate-Drain Charge	Q_{gd}	_	1.6	_			
Turn-On Delay Time	tD(ON)	_	3.82	_			
Turn-On Rise Time	t _R	_	4.76	_		V _{DD} = 20V, V _{GS} = 10V	
Turn-Off Delay Time	tD(OFF)	_	12.6	_	ns	$R_g = 3\Omega$, $I_D = 20A$	
Turn-Off Fall Time	t _F	_	4.83	_			
Body Diode Reverse Recovery Time	t _{RR}	_	31.9	_	ns	I- 20 A dI/dt 400 A/v.c	
Body Diode Reverse Recovery Charge	Q _{RR}	_	25.0		nC	I _F = 20A, dI/dt = 100A/μs	

Notes:

^{7.} Short duration pulse test used to minimize self-heating effect. 8. Guaranteed by design. Not subject to production testing.










Figure 2. Typical Transfer Characteristic






0.022

Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage








Figure 5. Typical On-Resistance vs. Drain Current and Junction Temperature

Figure 6. On-Resistance Variation with Junction Temperature






Figure 7. On-Resistance Variation with Junction Temperature




Figure 8. Gate Threshold Variation vs. Junction Temperature





Figure 9. Diode Forward Voltage vs. Current






Figure 11. Gate Charge




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI3333-8 (SWP) (Type UX)




PowerDI3333-8 (SWP)						
(Type UX)						
Dim	Min	Max	Тур			
Α	0.75	0.85	0.80			
A1	0.00	0.05				
b	0.25	0.40	0.32			
С	0.10	0.25	0.15			
D	3.20	3.40	3.30			
D1	2.95	3.15	3.05			
D2	2.30	2.70	2.50			
Е	3.20	3.40	3.30			
E1	2.95	3.15	3.05			
E2	1.60	2.00	1.80			
E3	0.95	1.35	1.15			
E4	0.10	0.30	0.20			
е	_	_	0.65			
k	0.50	0.90	0.70			
L	0.30	0.50	0.40			
θ	0°	12°	10°			
All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI3333-8 (SWP) (Type UX)



Dimensions	Value (in mm)				
С	0.650				
Х	0.420				
X1	0.420				
X2	0.230				
Х3	2.600				
X4	3.500				
Y	0.700				
Y1	0.550				
Y2	1.650				
Y3	0.600				
Y4	2.450				
Y5	0.400				
Y6	3.700				



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes' products provided subject to Diodes' Standard Terms and Conditions of Sale are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com