



#### 60V 175°C NPN LOW SAT MEDIUM POWER TRANSISTOR IN POWERDI5060-8

#### **Features**


- BV<sub>CEO</sub> > 60V
- I<sub>C</sub> = 3A Continuous Collector Current
- I<sub>CM</sub> = 8A Peak Pulse Current
- $R_{CE(SAT)}$  <  $90m\Omega$
- Rated to +175°C Ideal for High Ambient Temperature Environments
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An Automotive-Compliant Part is Available Under Separate Datasheet (<u>DXTN3C60PSQ</u>)


#### **Mechanical Data**


- Case: PowerDI<sup>®</sup> 5060-8
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Finish Matte Tin Annealed over Copper Leadframe;
   Solderable per MIL-STD-202, Method 208 <sup>3</sup>
- Weight: 0.097 grams (Approximate)

#### **Applications**

- Power Management
- Load Switch
- Linear Mode Voltage Regulator
- Backlighting Applications







Internal Schematic

Top View Pin Configuration


#### Ordering Information (Note 4)

Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
DXTN3C60PS-13	AEC-Q101	DXTN3C60PS	13	12	1,000

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

### **Marking Information**



DXTN3 = Product Type Marking Code C60PS = Product Type Marking Code YYWW = Date Code Marking YY = Last Two Digits of Year (ex: 19 = 2019) WW = Week Code (01 to 53)



### Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V <sub>CBO</sub>	60	V
Collector-Emitter Voltage	V <sub>CEO</sub>	60	V
Emitter-Base Voltage	V <sub>EBO</sub>	7	V
Base Current	I <sub>B</sub>	500	mA
Continuous Collector Current	Ic	3	Α
Peak Pulse Collector Current	I <sub>CM</sub>	8	А

# Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Power Dissipation	(Note 5)	P <sub>D</sub>	2.5	W	
Thermal Desigtance Junction to Ambient	(Note 5)	D	60	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{ heta JA}$	140		
Thermal Resistance, Junction to Case	(Note 5, 7)	D	2	°C/W	
Thermal Resistance, Junction to Case	(Note 6, 7)	R <sub>eJC</sub>	12		
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +175	°C		

# ESD Ratings (Note 8)


Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	8000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С


Notes:

- 5. For a device mounted with the collector lead on 25mm x 25mm 2oz copper that is on a single-sided 1.6mm FR4 PCB; device is measured under still air conditions whilst operating in a steady-state.
  6. Same as note (5), except mounted on minimum recommended pad layout.
  7. Thermal resistance from junction to the top of the case.
  8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.





# Typical Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)





Max Power Dissipation vs. Copper Area





3.0 Note 5 Note 5 Note 6 Note 100 125 150 175 Temperature (°C) Derating Curve




#### **Electrical Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS							
Collector-Base Breakdown Voltage	BV <sub>CBO</sub>	60	_	_	V	I <sub>C</sub> = 100μA	
Collector-Emitter Breakdown Voltage (Note 9)	BV <sub>CEO</sub>	60	_	_	V	I <sub>C</sub> = 10mA	
Emitter-Base Breakdown Voltage	BV <sub>EBO</sub>	7	_	_	V	I <sub>E</sub> = 100μA	
Collector-Base Cutoff Current	I <sub>CBO</sub>	_	_	100	nA	V <sub>CB</sub> = 48V	
Collector-base Cuton Current		_	_	50	μA	V <sub>CB</sub> = 48V @T <sub>J</sub> = +150°C	
Emitter Cutoff Current	I <sub>EBO</sub>	_	_	100	nA	V <sub>EB</sub> = 7V	
Collector-Emitter Cutoff Current	I <sub>CES</sub>	_	_	100	nA	V <sub>CES</sub> = 48V	
ON CHARACTERISTICS (Note 9)							
		200	400	_		$I_C = 500 \text{mA}, V_{CE} = 2V$	
DC Current Gain	h	200	330	_		$I_C = 1A$ , $V_{CE} = 2V$	
DC Current Gain	h <sub>FE</sub>	100	180	1	_	$I_C = 2A$ , $V_{CE} = 2V$	
		50	100	1		$I_C = 3A$ , $V_{CE} = 2V$	
Collector-Emitter Saturation Voltage	Vor(out)	_	70	120	mV	$I_C = 1A, I_B = 50mA$	
Collector-Effilter Gaturation Voltage	V <sub>CE</sub> (SAT)	_	180	270	mV	$I_C = 3A$ , $I_B = 300mA$	
Collector-Emitter Saturation Resistance	R <sub>CE(SAT)</sub>	_	60	90	mΩ	IC = 3A, IB = 300IIIA	
Base-Emitter Saturation Voltage	V	_	0.86	1.0	V	$I_C = 1A$ , $I_B = 100mA$	
Dase-Emilier Saturation voltage	V <sub>BE(SAT)</sub>	_	1.0	1.2		$I_C = 2A$ , $I_B = 200mA$	
Base-Emitter Turn-On Voltage	V <sub>BE(ON)</sub>	_	0.65	0.85	>	$I_C = 0.1A, V_{CE} = 2V$	
SMALL SIGNAL CHARACTERISTICS							
Current Gain-Bandwidth Product	f⊤	_	140	_	MHz	$V_{CE} = 10V, I_{C} = 100mA, f = 10MHz$	
Output Capacitance	C <sub>obo</sub>	_	17	_	pF	V <sub>CB</sub> = 10V, f = 1MHz	
Delay Time	$t_{D}$	_	15	_	ns		
Rise Time	t <sub>R</sub>	_	120	_	ns		
Turn-On Time	t <sub>(ON)</sub>	_	135		ns	V <sub>CC</sub> = 12.5V, I <sub>C</sub> = 1A	
Storage Time	t <sub>S</sub>	_	800		ns	$I_{B1} = -I_{B2} = 0.05A$	
Fall Time	t <sub>F</sub>	_	300	_	ns	]	
Turn-Off Time	t <sub>(OFF)</sub>	_	1100	_	ns		


Note: 9. Measured under pulsed conditions. Pulse width  $\leq 300 \mu s$ . Duty cycle  $\leq 2\%$ .





### Typical Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


















### Typical Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.) (continued)








#### **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5060-8




PowerDI5060-8					
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0.00	0.05	-		
b	0.33	0.51	0.41		
b2	0.200	0.350	0.273		
b3	0.40	0.80	0.60		
С	0.230	0.330	0.277		
D	Į	5.15 BSC			
D1	4.70	5.10	4.90		
D2	3.70	4.10	3.90		
D3	3.90	4.30	4.10		
Е	•	6.15 BSC	;		
E1	5.60	6.00	5.80		
E2	3.28	3.68	3.48		
E3	3.99	4.39	4.19		
е	1.27 BSC				
G	0.51	0.71	0.61		
K	0.51	-	-		
L	0.51	0.71	0.61		
L1	0.100	0.200	0.175		
M	3.235	4.035	3.635		
M1	1.00	1.40	1.21		
θ	10°	12º	11º		
θ1	6°	80	7º		
All Dimensions in mm					

### **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5060-8



Dimensions	Value (in mm)				
С	1.270				
G	0.660				
G1	0.820				
X	0.610				
X1	4.100				
X2	0.755				
Х3	4.420				
X4	5.610				
Υ	1.270				
Y1	0.600				
Y2	1.020				
Y3	0.295				
Y4	1.825				
Y5	3.810				
Y6	0.180				
Y7	6.610				



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com