



DSS3540MQ

40V PNP LOW SAT TRANSISTOR IN DFN1006-3

Features

- BV_{CEO} > -40V
- I_C = -500mA High Collector Current
- I_{CM} = -1A Peak Pulse Current
- P_D = 1000mW Power Dissipation
- Low Collector-Emitter Saturation Voltage, V_{CE(sat)}
- 0.60mm² Package Footprint, 13 times Smaller than SOT23
- 0.5mm Height Package Minimizing Off-Board Profile
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DSS3540MQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Package: X1-DFN1006-3
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu @4
 Solderable per MIL-STD-202, Method 208
- Weight: 0.0009 grams (Approximate)


X1-DFN1006-3



Bottom View



Device Symbol



Top View Device Schematic

Ordering Information (Note 4)


Product	Compliance	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
DSS3540MQ-7B	Automotive	TD	7	8	10,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

X1-DFN1006-3



TD = Product Type Marking Code Bar denotes Base and Emitter Side



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	-40	V
Collector-Emitter Voltage	V _{CEO}	-40	V
Emitter-Base Voltage	V _{EBO}	-6	V
Collector Current - Continuous	Ic	-500	mA
Peak Pulse Collector Current	Ісм	-1	Α
Peak Base Current	Івм	-100	mA

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Power Dissipation	(Note 5)	400		mW	
Fower Dissipation	(Note 6)	P _D	1000	IIIVV	
Thermal Resistance, Junction to Ambient	(Note 5)		310	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{\theta JA}$	120	*C/VV	
Thermal Resistance, Junction to Lead	$R_{ heta JL}$	120	°C/W		
Operating and Storage and Temperature Range	T _J , T _{STG}	-55 to +150	°C		

ESD Ratings (Note 8)


Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Charged Device Model	ESD CDM	1000	V	C3


Notes:

- 5. For the device mounted on minimum recommended pad layout 1oz copper that is on a single-sided 1.6mm FR4 PCB; device is measured under still air conditions whilst operating in steady state condition. The entire exposed collector pad is attached to the heatsink.
- 6. Same as Note 5, except the exposed collector pad is mounted on 25mm x 25mm 2oz copper.
- 7. Thermal resistance from junction to solder-point (on the exposed collector pad).
- 8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics







Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS						
Collector-Base Breakdown Voltage	BV _{CBO}	-40			V	$I_C = -100\mu A, I_E = 0$
Collector-Emitter Breakdown Voltage (Note 9)	BV _{CEO}	-40			V	$I_C = -10 \text{mA}, I_B = 0$
Emitter-Base Breakdown Voltage	BV _{EBO}	-6	_	_	V	$I_E = -100\mu A, I_C = 0$
Collector-Base Cutoff Current	I _{CBO}	_		-100 -50	nΑ μΑ	$V_{CB} = -30V, I_E = 0$ $V_{CB} = -30V, I_E = 0, T_A = +150$ °C
Emitter-Base Cutoff Current	I _{EBO}	_	_	-100	nA	$V_{EB} = -5V, I_C = 0$
Collector-Emitter Cutoff Current				-100	nA	$V_{CE} = -30V, V_X = \pm 0.25V$
Collector-Emiller Cuton Current	ICEX	_		-100		$V_{CE} = -30V, V_X = 3V$
Collector-Emitter Cutoff Current	I _{CES}	_	_	-100	nA	V _{CE} = -30V
ON CHARACTERISTICS (Note 9)						
	h _{FE}	200	_	_		$V_{CE} = -2V, I_{C} = -10mA$
DC Current Gain		150	_	_	_	$V_{CE} = -2V, I_{C} = -100mA$
		40	_	_		$V_{CE} = -2V, I_{C} = -500mA$
	V _{CE(sat)}	_	_	-50	mV	$I_C = -10 \text{mA}, I_B = -0.5 \text{mA}$
Collector-Emitter Saturation Voltage		_	_	-130		$I_C = -100 \text{mA}, I_B = -5 \text{mA}$
Concotor Ennitor Cataration Voltage		_	_	-200		$I_C = -200 \text{mA}, I_B = -10 \text{mA}$
		_	_	-350		$I_C = -500 \text{mA}, I_B = -50 \text{mA}$
Collector-Emitter Saturation Resistance	R _{CE(sat)}	_		700	mΩ	$I_C = -500 \text{mA}, I_B = -50 \text{mA}$
Base-Emitter Saturation Voltage	V _{BE(sat)}	_	_	-1.2	V	$I_C = -500 \text{mA}, I_B = -50 \text{mA}$
Base-Emitter Turn On Voltage	V _{BE(on)}	_	_	-1.1	V	V _{CE} = -2V, I _C = -100mA
SMALL SIGNAL CHARACTERISTICS						
Output Capacitance	C _{obo}		_	10	pF	V _{CB} = -10V, f = 1.0MHz
Current Gain-Bandwidth Product	f _t	100	_	_	MHz	$V_{CE} = -5V$, $I_{C} = -100$ mA, $f = 100$ MHz


Note:


9. Measured under pulsed conditions. Pulse width \leq 300 μ s. Duty cycle \leq 2%.




Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)







800 700 600 DC CURRENT GAIN 500 T_A = 85°C 400 T_A = 25°C 300 200 100 0 1 10 100 -I_C, COLLECTOR CURRENT (mA) 0.1 1,000 Fig. 5 Typical DC Current Gain vs. Collector Current







Fig. 9 Typical Collector-Emitter Saturation Resistance vs. Collector Current



Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



X1-DFN1006-3					
Dim	Min	Max	Тур		
Α	0.47	0.53	0.50		
A1	0.00	0.05	0.03		
b	0.10	0.20	0.15		
b2	0.45	0.55	0.50		
D	0.95	1.075	1.00		
Е	0.55	0.675	0.60		
е	-	-	0.35		
L1	0.20	0.30	0.25		
L2	0.20	0.30	0.25		
L3	-	-	0.40		
Z	0.02	0.08	0.05		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)		
C	0.70		
G1	0.30		
G2	0.20		
Х	0.40		
X1	1.10		
Ý	0.25		
Y1	0.70		



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com