

40V PNP LOW VCESAT TRANSISTOR IN PowerDI3333-8

Features

- BV_{CEO} > -40V
- Small Form Factor Thermally Efficient Package.
 Enables Higher Density End Products
- I_C = -2A Continuous Collector Current
- I_{CM} = -3A Peak Pulse Current
- Low Saturation Voltage V_{CE(sat)} < -225mV @ -1A
- Complementary NPN Type: DXTN22040CFGQ
- Rated to +175°C Ideal For High Temperature Environment
- Wettable Flank For Improved Optical Inspection
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DXTP22040CFGQ is suitable for automotive applications requiring specific change control and is AEC-Q101 qualified, is PPAP capable, and is manufactured in IATF16949:2016 certified facilities.

Mechanical Data

- Case: PowerDI[®]3333-8
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.03 grams (Approximate)


Applications


- High-Side Switch
- Supply Line Switching
- Motor Driving

PowerDI3333-8 (SWP) (Type UX)



Top View





Device Symbol

Ordering Information (Note 4)


Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
DXTP22040CFGQ-7	Automotive	2K3	7	12	2,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

PowerDI3333-8 (SWP) (Type UX)



2K3 = Product Type Marking Code

YYWW = Date Code Marking

YY = Last Two Digits of Year (ex: 19 = 2019)

WW = Week Code (01 to 53)



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Collector-Base Voltage	V _{CBO}	-50	V	
Collector-Emitter Voltage	V _{CEO}	-40	V	
Emitter-Base Voltage	V _{EBO}	-7	V	
Continuous Collector Current	Ic	-2	۸	
Peak Pulse Collector Current	I _{CM}	-3	A	
Continuous Base Current	Ι _Β	-100	mΛ	
Peak Pulse Base Current	I _{BM}	-200	mA mA	

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
	(Note 5)		1.07	W
Power Dissipation	(Note 6)	P _D	2.3	W
	(Note 7)		3.4	W
	(Note 5)		140	°C/W
Thermal Resistance, Junction to Ambient	(Note 6)	R _{θJA}	65	°C/W
	(Note 7)		44	°C/W
Thermal Resistance, Junction to Leads (Note	Rejl	11	°C/W	
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +175	°C	

ESD Ratings (Note 9)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge – Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge – Machine Model	ESD MM	400	V	C

5. For a device mounted with the collector tab on MRP FR4-PCB; device is measured under still air conditions whilst operating in a steady-state.


- 6. Same as Note 5, except the device is mounted on 25mm × 25mm 2oz copper.
- 7. Same as Note 5, except the device is mounted on 50mm × 50mm 2oz copper.


 8. Thermal resistance from junction to solder-point (at the collector tab).


 9. Refer to JEDEC specification JESD22-A114 and JESD22-A115.





Thermal Characteristics and Derating Information

















Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV _{CBO}	-50	-71	_	V	$I_C = -100 \mu A$
Collector-Emitter Breakdown Voltage (Note 10)	BV _{CEO}	-40	-50	_	V	$I_C = -10mA$
Emitter-Base Breakdown Voltage	BV _{EBO}	-7	-8.6	_	V	$I_E = -100 \mu A$
Collector-Base Cut-Off Current	I _{CBO}	-	-1 -0.1	-20 -10	nΑ μΑ	V _{CB} = -50V V _{CB} = -40V, T _A = +150°C
Emitter-Base Cut-Off Current	I _{EBO}	_	-1	-20	nA	V _{EB} = -6V
Collector-Emitter Cut-Off Current	ICES	_	-1	-20	nA	V _{CE} = -40V, V _{BE} = 0V
Static Forward Current Transfer Ratio (Note 10)	h _{FE}	200 200 150 80	340 299 261 196	600 — —	_	I _C = -100mA, V _{CE} = -2V I _C = -500mA, V _{CE} = -2V I _C = -1A, V _{CE} = -2V I _C = -2A, V _{CE} = -2V
Collector-Emitter Saturation Voltage (Note 10)	VCE(sat)		-52 -42 -71 -129 -189-	-100 -130 -225 -350 -600	mV	$I_C = -100$ mA, $I_B = -1$ mA $I_C = -500$ mA, $I_B = -50$ mA $I_C = -1$ A, $I_B = -100$ mA $I_C = -2$ A, $I_B = -200$ mA $I_C = -3$ A, $I_B = -300$ mA
Collector-Emitter Saturation Resistance (Note 10)	R _{CE(sat)}	_	_	225	mΩ	$I_C = -1A$, $I_B = -100mA$
Base-Emitter Saturation Voltage (Note 10)	V _{BE(sat)}		-0.88	-1	V	$I_C = -1A$, $I_B = -100mA$
Base-Emitter Turn-On Voltage (Note 10)	V _{BE(on)}	_	-0.77	-0.9	V	$I_C = -1A$, $V_{CE} = -2V$
Transition Frequency	f⊤	_	120	_	MHz	$I_C = -50 \text{mA}, V_{CE} = -10 \text{V}$ f = 100MHz
Output Capacitance	C _{obo}	_	12	_	pF	$V_{CB} = -10V$, $f = 1MHz$
	t _{delay}		11.6	_	ns	
Switching Characteristics	t _{rise}	_	128	_	ns	$V_{CC} = -10V, I_{C} = -500mA$
Ownering Characteristics	t _{storage}		524	_	ns	$I_{B1} = -I_{B2} = -50 \text{mA}$
	t _{fall}	_	69.4	_	ns	

Note: 10. Measured under pulsed conditions. Pulse width ≤ 300µs. Duty cycle ≤ 2%.




Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)






V_{CE(sat)}vs I_C








h_{FE} vs I_C

V_{BE(sat)} vs I_C






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI3333-8 (SWP) (Type UX)




PowerDI3333-8 (SWP)					
(Type UX)					
Dim	Min Max		Тур		
Α	0.75	0.85	0.80		
A1	0.00	0.05	-		
b	0.25	0.40	0.32		
С	0.10	0.25	0.15		
D	3.20	3.40	3.30		
D1	2.95	3.15	3.05		
D2	2.30	2.70	2.50		
E	3.20	3.40	3.30		
E1	2.95	3.15	3.05		
E2	1.60	2.00	1.80		
E3	0.95	1.35	1.15		
E4	0.10	0.30	0.20		
е	_	_	0.65		
k	0.50	0.90	0.70		
L	0.30	0.50	0.40		
θ	0°	12°	10°		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI3333-8 (SWP) (Type UX)



Dimensions	Value (in mm)
С	0.650
X	0.420
X1	0.420
X2	0.230
Х3	2.600
X4	3.500
Υ	0.700
Y1	0.550
Y2	1.650
Y3	0.600
Y4	2.450
Y5	0.400
Y6	3.700



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com