



DST857BDJ


45V DUAL PNP SMALL SIGNAL TRANSISTOR IN SOT963

Features

- Epitaxial Planar Die Construction
- Ideally Suited for Automated Assembly Processes
- Complementary NPN Type Available (DST847BDJ)
- Ultra Small Package
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Mechanical Data

- Case: SOT963
- Case Material: Molded Plastic, "Green" Molding Compound;
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Weight: 0.0027 grams (Approximate)




Ordering Information

Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
DST857BDJ-7	Standard	TB	7	8	10,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



TB = Product Type Marking Code



Absolute Maximum Rating (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	-50	V
Collector-Emitter Voltage	V _{CEO}	-45	V
Emitter-Base Voltage	V _{EBO}	-6.0	V
Collector Current - Continuous (Note 5)	Ic	-100	mA

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	P_{D}	300	mW
Thermal Resistance, Junction to Ambient (Note 5)	$R_{ hetaJA}$	417	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Note: 5. Device mounted on FR-4 PCB with minimum recommended pad layout.


ESD Rating (Note 6)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	200	V	В

Note: 6. Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics and Derating Information



1,000

| Single Pulse | R_{0,JA}(t) = r(t) * R_{0,JA} | R_{0,JA} | T_J · T_A = P * R_{0,JA}(t) | Duty Cycle, D = t₁/t₂ | Duty Cycle, D = t₁/t₂ | Duty Cycle, D = t₁/t₂ | Duty Cycle, D = t₂/t₃ | Duty Cycle, D = t₁/t₂ | Duty Cycle, D = t₁





Fig. 3 Power Dissipation vs. Ambient Temperature




Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Characteristic (Note 7)	Symbol	Min	Typical	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	V _{(BR)CBO}	-50	-100		V	$I_C = -10\mu A, I_B = 0$
Collector-Emitter Breakdown Voltage	V _{(BR)CES}	-50	-90	ı	V	$I_C = -10\mu A, I_B = 0$
Collector-Emitter Breakdown Voltage	V _{(BR)CEO}	-45	-65	-	V	$I_C = -1 \text{mA}, I_B = 0$
Emitter-Base Breakdown Voltage	V _{(BR)EBO}	-6	-8.5	-	V	$I_E = -1\mu A, I_C = 0$
Collector Cut-Off Current	I _{CBO}	=		-15	nA	V _{CB} = -30V
DC Current Gain	h _{FE}	-	340	=	_	$I_C = -10\mu A, V_{CE} = -5V$
Do Garrett Gairi	IIFE.	200	330	470		$I_C = -2.0 \text{mA}, V_{CE} = -5 \text{V}$
Collector-Emitter Saturation Voltage	VCE(SAT) -	-	-70	-175	mV	$I_C = -10mA$, $I_B = -0.5mA$
Concolor Emiliar Calaration Voltage		-300	-500		$I_C = -100 \text{mA}, I_B = -5.0 \text{mA}$	
Base-Emitter Saturation Voltage	V _{BE(SAT)}	-	-760	-1000	mv I	$I_C = -10mA$, $I_B = -0.5mA$
Base Emilier Galdration Voltage		ı	-885	-1100		$I_C = -100 \text{mA}, I_B = -5.0 \text{mA}$
Base-Emitter Turn-On Voltage	\/==(a, v	-600	-670	-780	ı mv ı	$I_C = -2.0 \text{mA}, V_{CE} = -5 \text{V}$
base-Emiller Furn-On Vollage	V _{BE(ON)}		-715	-850		$I_C = -10 \text{mA}, V_{CE} = -5 \text{V}$
Current Gain-Bandwidth Product	f⊤	100	340	-	MHz	$V_{CE} = -5V, I_{C} = -10mA,$
	11					f = 100MHz
Output Capacitance	C _{obo}	-	2.0	-	pF	$V_{CB} = -10V, f = 1.0MHz$


7. Measured under pulsed conditions. Pulse width \leq 300 μ s. Duty cycle \leq 2%. Note:























Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




SOT963				
Dim	Min	Max	Тур	
Α	0.40	0.50	0.45	
A1	0.00	0.05		
b	0.10	0.20	0.15	
C	0.120	0.180	0.150	
D	0.95	1.05	1.00	
Е	0.95	1.05	1.00	
E1	0.75	0.85	0.80	
е			0.35	
e1			0.70	
L1	0.05	0.15	0.10	
All Dimensions in mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT963



Dimensions	Value (in mm)			
С	0.350			
Х	0.200			
Υ	0.200			
Y1	1.100			



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com