



**GBJ3510** 

#### 35A GLASS PASSIVATED BRIDGE RECTIFIER

#### **Features**

- Glass Passivated Die Construction
- High Case Dielectric Strength of 2500V<sub>RMS</sub>
- Low Reverse Leakage Current
- Surge Overload Rating to 400A Peak
- Ideal for Printed Circuit Board Applications
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)

### **Mechanical Data**

- Case: GBJ
- Case Material: Molded Plastic. UL Flammability Classification 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Tin Plated Leads, Solderable per MIL-STD-202. Method 208 (3)
- Polarity: Molded on Body
- Mounting: Through Hole for #6 Screw
- Mounting Torque: 5.0 in-lbs Maximum
- Marking: Part Number
- Weight: 6.6 grams (Approximate)

## **Ordering Information (Note 3)**

Part Number	Qualification	Case	Packaging
GBJ3510-F	Commercial	GBJ	15/Tube

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
- 2. See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green"
- 3. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

## **Maximum Ratings** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	1000	V
RMS Reverse Voltage	V <sub>R(RMS)</sub>	700	V
Average Forward Rectified Output Current With Heatsink $T_C = +80^{\circ}C$ (Note 4) Without Heatsink $T_C = +25^{\circ}C$	lo	35 3.6	А
Non-Repetitive Peak Forward Surge Current 8.3 ms Single Half Sine-Wave Superimposed on rated Load	I <sub>FSM</sub>	400	А
$I^2$ t Rating for Fusing (3ms < t < 8.3ms) (Note 4)	l <sup>2</sup> t	664	A <sup>2</sup> S
Mounting Torque (Recommended Torque: 0.5N.m)	TOR	0.8	N.m

## **Thermal Characteristics**

Characteristic		Symbol	Value	Unit
Typical Thermal Resistance Junction to Case	(Note 5)	$R_{ heta JC}$	1.0	°C/W
Typical Thermal Resistance Junction to Lead	(Note 5)	$R_{ hetaJL}$	1.5	°C/W
Operating and Storage Temperature Range		T <sub>J</sub> , T <sub>STG</sub>	-55 to +150	°C

Notes:


- 4. Non-repetitive, for t > 1ms and < 8.3ms.
- 5. Thermal resistance from junction to case per element. Unit mounted on 250 x 250 x 25mm aluminum plate heat sink.





# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic		Symbol	Value	Unit
Forward Voltage (Per Element)	@ I <sub>F</sub> = 17.5A	$V_{FM}$	1.1	V
Peak Reverse Current at Rated DC Blocking Voltage	@ T <sub>C</sub> = +25°C @ T <sub>C</sub> = +125°C	Ь	10 500	μΑ
Typical Total Capacitance (Per Element)	(Note 6)	C <sub>T</sub>	150	pF

Note: 6. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.















# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

GBJ



GBJ			
Dim	Min	Max	
Α	29.70	30.30	
В	19.70	20.30	
C	17.00	18.00	
D	3.80	4.20	
Е	7.30	7.70	
G	9.80	10.20	
Н	2.00	2.40	
	0.90	1.10	
7	2.30	2.70	
K	3.0 X 45°		
٦	4.40	4.80	
М	3.40	3.80	
N	3.10	3.40	
P	2.50	2.90	
R	0.60	0.80	
S	10.80	11.20	
All Dimensions in mm			



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com