




35A SINGLE-PHASE STANDARD RECOVERY BRIDGE RECTIFIER

Features

- Glass Passivated Die Construction
- High Case Dielectric Strength of 2500V_{RMS}
- Low Forward Voltage Drop
- Low Reverse Leakage Current
- Surge Overload Rating to 400A Peak
- Ideal for Printed Circuit Board Applications
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

Mechanical Data

- Package: GBJ
- Package Material: Molded Plastic. UL Flammability Classification 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Tin Plated Leads (Matte Tin Finish), Solderable per MIL-STD-202, Method 208 (3)
- Polarity: Molded on Body
- Mounting: Through Hole for #6 Screw
- Mounting Torque: 5.0 in-lbs Maximum
- Weight: 6.6 grams (Approximate)



Ordering Information (Note 4)


Part Number	Package	Packing		
Part Number	Гаскауе	Qty.	Carrier	
GBJ35JL-F	GBJ	15	Tube	

EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
 See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Marking Information

Notes:



^{4.} For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Maximum Ratings (@ T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit	
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		Vrrm Vrwm Vr	600	V
RMS Reverse Voltage		VR(RMS)	420	V
Average Forward Rectified Output Current (Note 5)	With Heatsink $T_C = +80^{\circ}C$ Without Heatsink $T_C = +25^{\circ}C$		35 4.7	А
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	@ T」= +25°C @ T」= +125°C	ESM	400 320	А
Non-Repetitive Peak Forward Surge Current 1.0ms Single Half Sine-Wave Superimposed on Rated Load	@ T」= +25°C @ T」= +125°C	ESM	800 640	А
I ² t Rating for Fusing (3ms < t < 8.3ms) (Note 5)		l ² t	664	A ² s
Mounting Torque (Recommended Torque: 0.5N.m)		TOR	0.8	N.m
		SV,	~	
Thermal Characteristics				

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Typical Thermal Resistance Junction to Case	(Note 6)	Rejc	4	°C/W
Typical Thermal Resistance Junction to Lead	(Note 6)	Rejl	10	°C/W
Typical Thermal Resistance Junction to Ambient	(Note 6)	Reja	20	°C/W
Typical Thermal Resistance Junction to Case	(Note 7)	Rejc	1.0	°C/W
Typical Thermal Resistance Junction to Lead	(Note 7)	Rejl	2	°C/W
Typical Thermal Resistance Junction to Ambient	(Note 7)	Reja	2	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C


Electrical Characteristics (@ TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Breakdown Voltage	Vr	600	_	_	V	I _R = 10μΑ
Forward Voltage (Per Element)	VF	_	0.86	0.92	V	I _F = 17.5A, T _S = +25°C
Reverse Leakage Current (Per Element)	ÎR	_	_	10	μA	V _R = 600V, T _J = +25°C
Total Capacitance (Per Element)	Ст	_	240	_	pF	$f = 1MHz, V_R = 4Vdc$

Notes:

5. Non-repetitive, for t > 1ms and < 8.3ms.
6. Thermal resistance per element without heatsink.
7. Thermal resistance from junction to case per element. Unit mounted on 250mm x 250mm x 25mm aluminum plate heat sink.








GBJ35JL

Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.





IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' Standard Terms 5 Diodes' provided and Conditions of Sale products are subject to (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-potice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com