

5.0 x 3.2mm

# **CMOS 32.768kHz**

**KX501** 



5.0 x 3.2mm Ceramic SMD

#### **Product Features**

- AT Cut 32.768 kHz XO
- CMOS compatible logic levels
- Ultra low active current ( $< 10\mu$ A)
- Very tight temperature stability
- Designed for standard reflow and washing techniques
- Pb-free and RoHS/Green compliant


# **Product Description**


The KX501 Series real time clock oscillator achieves superb stability over a broad range of operating conditions. It utilizes Pericom proprietary technology to achieve ultra low current less than  $10\mu A$ . The output clock signal is compatible with LVCMOS/LVTTL logic levels. The device, available on tape and reel, is contained in a 5.0 x 3.2mm surface-mount ceramic package.


# **Applications**

• Real-Time Clock Oscillator where low current and tight stability are needed

#### Package: (Scale: none; Dimensions are in mm)








#### **Pin Functions:**

Pin	Function					
1	OE Function					
2	Ground					
3	Clock Output					
4	$V_{\mathrm{DD}}$					

### **Part Ordering Information:**



Following the above format, SaRonix-eCera part numbers will be assigned upon confirmation of exact customer requirements.

SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-435-0800 TW: +886-3-4518888

13-0004

• www.saronix-ecera.com

# **Ultra Low Current KX Series Crystal Oscillator** 5.0 x 3.2mm

#### **Electrical Performance**

Parameter	Min.	Тур.	Max.	Units	Notes	
Output Frequency		32.768		kHz		
Supply Voltage	+1.71	+1.8	+1.89	V		
	+2.25	+2.5	+2.75	V	S	
	+2.85	+3.0	+3.15	V	See part ordering options	
	+3.0	+3.3	+3.6	V		
Supply Current, Output Enabled		7.5	10	μΑ	No load	
Supply Current, Standby Mode			0.5	μΑ	Output Hi-Z	
Frequency Stability			±50	ppm	See part ordering options, and note 1	
Operating Temperature Range	-40		+85	С	See part ordering options	
Output Logic 0, V <sub>OL</sub>			0.1 V <sub>DD</sub>	V		
Output Logic 1, V <sub>OH</sub>	0.9 V <sub>DD</sub>			V		
Output Load			15	pF	See Note 2	
Duty Cycle	45		55	%	measured 50% of V <sub>DD</sub>	
Rise and Fall Time		35	50	ns	measured 20/80% of V <sub>DD</sub>	
Start-up time			10	ms		

#### Notes:

For specifications other than those listed, please contact sales.

#### **Output Enable / Disable Function**

Parameter	Min.	Тур.	Max.	Units	Notes
Input Voltage (pin 1), Output Enable	0.7 V <sub>DD</sub>			V	or open
Input Voltage (pin 1), Output Disable (low power standby)			0.3 V <sub>DD</sub>	V	Output is Hi-Z
Internal Pullup Resistance		100		kΩ	
Output Disable Delay			100	ns	
Output Enable Delay			10	ms	

## **Absolute Maximum Ratings**

Parameter	Min.	Тур.	Max.	Units	Notes
Storage Temperature	-55		+125	°C	

For the latest product information visit: http://www.pericom.com/products/timing/oscillators/KX501/

For test circuit go to: http://www.pericom.com/pdf/sre/tc cmos2.pdf

For soldering reflow profile and reliability test ratings go to: http://www.pericom.com/pdf/sre/reflow.pdf

For tape and reel information go to: http://www.pericom.com/pdf/sre/tr 5032 xo.pdf

SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-435-0800 TW: +886-3-4518888 • www.saronix-ecera.com



KX501 REV B

As specified. Stability includes all combinations of operating temperature, load changes, rated input (supply) voltage changes, initial calibration tolerance (25°C), aging (1 year at 25°C average effective ambient temperature), shock and vibration.