



A Product Line of Diodes Incorporated



### FMMT459

#### **500V NPN HIGH VOLTAGE TRANSISTOR IN SOT23**

#### Feature


- BV<sub>CEV</sub> > 500V
- BV<sub>ECV</sub> > 6V reverse blocking
- I<sub>C</sub> = 150mA high Continuous Collector Current
- I<sub>CM</sub> Up to 500mA Peak Pulse Current
- 625mW Power Dissipation
- Low Saturation Voltage <-90mV @ 50mA</li>
- Excellent h<sub>FE</sub> Characteristics Up To 120mA
- Totally Lead-Free & Fully RoHS compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

#### **Mechanical Data**

- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 <sup>(23)</sup>
- Weight 0.008 grams (approximate)

#### **Applications**

- Off-line switching applications
- RCD circuits
- PFC disable switch in PSU
- Emergency lighting
- Piezo actuators
- Telecom protected line switching



#### Ordering Information (Note 4)

Part Number	Compliance	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
FMMT459TA	AEC-Q101	459	7	8	3,000

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.


2. See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

# **Marking Information**

Notes:







# Absolute Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V <sub>CBO</sub>	500	V
Collector-Emitter Voltage	V <sub>CEV</sub>	500	V
Collector-Emitter Voltage	V <sub>CEO</sub>	450	V
Emitter-Base Voltage	V <sub>EBO</sub>	7	V
Emitter-Collector Voltage	V <sub>ECV</sub>	6	V
Continuous Collector Current	Ic	150	mA
Peak Pulse Current	I <sub>CM</sub>	500	mA
Base Current	IB	200	mA

#### Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	PD	625	mW
Power Dissipation (Note 6)	PD	806	mW
Thermal Resistance, Junction to Ambient (Note 5)	R <sub>0JA</sub>	200	°C/W
Thermal Resistance, Junction to Ambient (Note 6)	R <sub>0JA</sub>	155	°C/W
Thermal Resistance, Junction to Leads (Note 7)	R <sub>θJL</sub>	194	°C/W
Operating and Storage Temperature Range	T <sub>J,</sub> T <sub>STG</sub>	-55 to +150	۵°

### ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С

Notes: 5. For a device mounted with the collector lead on 25mm x 25mm 1oz copper that is on a single-sided FR4 PCB; device is measured under still air conditions whilst operating in a steady-state.


6. Same as note 5, except the device is measured at t  $\leq$  5 sec.

Thermal resistance from junction to solder-point (at the end of the collector lead).
Refer to JEDEC specification JESD22-A114 and JESD22-A115.





# Thermal Characteristics and Derating Information



**Transient Thermal Impedance** 

**Pulse Power Dissipation** 





# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV <sub>CBO</sub>	500	700	—	V	I <sub>C</sub> = 100μA
Collector-Emitter Breakdown Voltage	BVCEV	500	700	—	V	I <sub>C</sub> = 10μA; 0.3V > V <sub>BE</sub> > -1V
Collector-Emitter Breakdown Voltage (Note 9)	BV <sub>CEO</sub>	450	500	—	V	I <sub>C</sub> = 1mA
Emitter-Base Breakdown Voltage	BV <sub>EBO</sub>	7	8.1	—	V	I <sub>E</sub> = 100μA
Emitter-Base Breakdown Voltage (Reverse Blocking)	BV <sub>ECV</sub>	6	8.1	—	V	I <sub>C</sub> = 1μA; 0.3V > V <sub>BC</sub> > -6V
Collector Cutoff Current	I <sub>CBO</sub>	—	<10	100	nA	V <sub>CB</sub> = 450V
Emitter Cutoff Current	I <sub>EBO</sub>	—	<10	100	nA	V <sub>EB</sub> = 5.6V
Collector Emitter Cutoff Current	I <sub>CES</sub>	—	<10	100	nA	V <sub>CE</sub> = 450V
Static Forward Current Transfer Ratio (Note 9)	h <sub>FE</sub>	50	120	—	—	I <sub>C</sub> = 30mA, V <sub>CE</sub> = 10V
Static Folward Current Transfer Ratio (Note 9)		—	70	_		I <sub>C</sub> = 50mA, V <sub>CE</sub> = 10V
Collector-Emitter Saturation Voltage (Note 9)	Vorum	—	60	75	mV	I <sub>C</sub> = 20mA, I <sub>B</sub> = 2mA
	V <sub>CE(sat)</sub>	—	70	90	mV	I <sub>C</sub> = 50mA, I <sub>B</sub> = 6mA
Base-Emitter Turn-On Voltage (Note 9)	V <sub>BE(on)</sub>	—	0.71	0.9	V	I <sub>C</sub> = 50mA, V <sub>CE</sub> = 10V
Base-Emitter Saturation Voltage (Note 9)	V <sub>BE(sat)</sub>	—	0.76	0.9	V	I <sub>C</sub> = 50mA, I <sub>B</sub> = 5mA
Output Capacitance	C <sub>obo</sub>	—	—	5	pF	V <sub>CB</sub> = 20V, f = 1MHz
Transition Frequency	f <sub>T</sub>	50	_		MHz	V <sub>CE</sub> = 20V, I <sub>C</sub> = 10mA, f = 20MHz
Turn-On Time	t <sub>on</sub>	—	113		ns	$V_{\rm C} = 100V, I_{\rm C} = 50mA$
Turn-Off Time	t <sub>off</sub>	—	3450	_	ns	I <sub>B1</sub> = 5mA, I <sub>B2</sub> = -10mA

9. Measured under pulsed conditions. Pulse width  $\leq$  300µs. Duty cycle  $\leq$  2%. Notes:





## Typical Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)








# **Package Outline Dimensions**


Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for latest version.



SOT23					
Dim	Min	Max	Тур		
Α	0.37	0.51	0.40		
В	1.20	1.40	1.30		
С	2.30	2.50	2.40		
D	0.89	1.03	0.915		
F	0.45	0.60	0.535		
G	1.78	2.05	1.83		
Н	2.80	3.00	2.90		
J	0.013	0.10	0.05		
Κ	0.890	1.00	0.975		
K1	0.903	1.10	1.025		
L	0.45	0.61	0.55		
L1	0.25	0.55	0.40		
М	0.085	0.150	0.110		
а	8°				
All	All Dimensions in mm				

### Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



Dimensions	Value (in mm)
Z	2.9
Х	0.8
Y	0.9
С	2.0
E	1.35

For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking. Note:





#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2014, Diodes Incorporated

#### www.diodes.com