

# 2.5V/3.3V CMOS FS XO

# **NX71SB**



7.0 x 5.0mm Ceramic SMD

## **Product Features**

- 4 selectable output frequencies
- Very low phase jitter < 1ps RMS max.
- Wide frequency range  $5 \sim 250 \text{MHz}$
- Low supply current 60mA max.
- Industrial Temperature Range
- Pb-free & RoHS compliant
- Fast lead time


## **Product Description**

The NX71SB XO series is a high performance CMOS crystal oscillator family with very low jitter performance and selectable output frequencies. Depending on customers' needs, this family devices can support up to 4 different frequencies using the FS select pins. It supports various options including wider frequency range, 2.5V/3.3V voltage, and various stabilities. It is designed to meet the clock source specifications for communication systems, and other high performance equipment.


## **Applications**

- Networking systems
- Servers and storage systems
- Profession video equipments
- Test and measurement
- FPGA/ASIC clock generation

#### Package: (Scale: none, Dimensions are in mm)








\*Extended high frequency power decoupling is recommended (see test circuit for minimum recommendation). To ensure optimal performance, do not route RF traces beneath the package.

#### **Part Ordering Information:**



Recommended Land Pattern:

#### **Pin Functions:**

Pin	Function					
1	FS1					
2	FS0					
3	Ground					
4	Output					
5	NC					
6	$V_{\mathrm{DD}}$					

#### **Frequency Select Table:**

FS0	FS1	Output
0	0	Freq. 1*
0	1	Freq. 2*
1	0	Freq. 3*
1	1	Freq. 4*

\*Freq. 1, Freq. 2, Freq. 3, Freq. 4 can be any frequencies within the output frequency range.

SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-232-9100 TW: +886-3-4518888

15-0027



NX71SB



## Ultra Low Jitter PLL Crystal Oscillator 7.0 x 5.0mm

#### **Electrical Performance**

Parameter		Min.	Тур.	Max.	Units	Notes
Output Frequence	cy	5		250	MHz	
Supply Voltage		3.135	3.3	3.465	***	
		2.375	2.5	2.625	V	
Supply Current				60	mA	
Frequency Stabi	lity	±20		±50	ppm	±20ppm is for -20°C to 70°C only
Operating Temp	erature Range	-40		+85	°C	
Output Logic 0,	$V_{ m OL}$			0.4	V	
Output Logic 1,	$V_{ m OH}$	V <sub>DD</sub> -0.4			V	
Output Load				15	pF	
Duty Cycle		45		55	%	Measured 50% V <sub>DD</sub>
Rise and Fall Tir	me			3	ns	Measured 20/80% of waveform
Jitter, Accumula	ted, RMS (1-σ)			6	ps	20.000 adjacent periods
Jitter, Phase, RMS	<40MHz		0.4	1	ps	12kHz to 5 MHz frequency band
	40 to 250MHz		0.4	1	ps	12kHz to 20 MHz frequency band
	125MHz, 156.25MHz		0.4	0.6	ps	12kHz to 20 MHz frequency band
Jitter, pk-pk				40	ps	100,000 random periods

#### Notes:

- Stability includes all combinations of operating temperature, load changes, rated input (supply) voltage changes, initial calibration tolerance (25°C), aging (1 year at 25°C average effective ambient temperature), shock and vibration.
- Phase jitter typical value is depending on output frequencies.
- For specifications other than those listed, please contact sales.

### **Frequency Select Function**

Parameter	Min.	Тур.	Max.	Units	Notes
Input Voltage (pin 1 & pin 2), FS1 & FS0	0.7 V <sub>DD</sub>			V	
Input Voltage (pin 1 & pin 2), FS1 & FS0			0.3 V <sub>DD</sub>	V	
Settling Time after FS Change			10	ms	
Start up Time			10	ms	

#### **Absolute Maximum Ratings**

Parameter	Min.	Тур.	Max.	Units	Notes
Storage Temperature	-55		+125	°C	

For the latest product information visit: http://www.pericom.com/products/crystals-and-crystal-oscillators/hiflex-xo/?part=NX71SB

For test circuit go to: http://www.pericom.com/pdf/sre/tc-6pcmos-sb.pdf

For soldering reflow profile and reliability test ratings go to: http://www.pericom.com/pdf/sre/reflow.pdf

For tape and reel information go to: http://www.pericom.com/pdf/sre/tr 7050 xo.pdf



NX71SB