

COMPLEMENTARY NPN / PNP SMALL SIGNAL TRANSISTOR IN SOT363

Features & Benefits

- Complementary Pairs:
 - One 2222A Type (NPN)
 - One 2907A Type (PNP)
- Ideal for Low-Power Amplification and Switching
- Totally Lead-Free & Fully RoHS compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The MMDT2227Q is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF16949 certified facilities.


https://www.diodes.com/quality/product-definitions/

Mechanical Data


- Package: SOT363
- Package Material: Molded Plastic, "Green" Molding Compound UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 ³
- Weight: 0.006 grams (approximate)







Device Symbol



Pin-Out


Ordering Information (Note 4)

Orderable Part Number	Marking	Reel size (inches)	Tape width (mm)	Pack	ing
Orderable Part Number	Warking	Reel Size (Iliches)	rape widin (min)	Quantity	Carrier
MMDT2227Q-7-F	K27	7	8	3,000	Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



 $\begin{array}{l} \text{K27} = \text{Product Type Marking Code} \\ \text{YM} = \text{Date Code Marking} \\ \text{Y or } \overline{\text{Y}} = \text{Year (ex: K = 2023)} \\ \text{M or } \overline{\text{M}} = \text{Month (ex: 2 = February)} \end{array}$

Date Code Key

Year	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032	2033
Code	J	K	L	М	N	0	Р	R	S	T	U	V
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	4	2	2	4	5	6	7	0	0	0	N	ר



Maximum Ratings, 2222A Type (NPN) (@ T_{amb} = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	$V_{\sf CBO}$	75	V
Collector-Emitter Voltage	V_{CEO}	40	V
Emitter-Base Voltage	V_{EBO}	6	٧
Continuous Collector Current	Ic	600	mA

Maximum Ratings, 2907A Type (PNP) (@ T_{amb} = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V_{CBO}	-60	V
Collector-Emitter Voltage	V_{CEO}	-60	V
Emitter-Base Voltage	V _{EBO}	-6	V
Continuous Collector Current	Ic	-600	mA

Thermal Characteristics (@ Tamb = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Power Dissipation (Note 5)		P _D	200	mW
Thermal Resistance, Junction to Ambient (Note 5)		$R_{ hetaJA}$	625	2011
Thermal Resistance, Junction to Case (Note 6)		$R_{ heta JC}$	150	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C	

ESD Ratings (Note 7)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С

Notes: 5. For the device mounted on minimum recommended pad layout FR-4, device is measured under still air conditions whilst operating in a steady-state.

6. Thermal resistance from junction to the top of package.

7. Refer to JEDEC specification JESD22-A114 and JESD22-A115.

Thermal Characteristic and Derating Information




Figure 1. P_D v T_A




Electrical Characteristics, 2222A Type (NPN) (@ T_{amb} = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)					
Collector-Base Breakdown Voltage	BV _{CBO}	75		V	$I_C = 100\mu A$
Collector-Emitter Breakdown Voltage	BV _{CEO}	40	_	V	I _C = 10mA
Emitter-Base Breakdown Voltage	BV _{EBO}	6.0	_	V	I _E = 100μA
Collector Cutoff Current	I _{CBO}		10	nA μA	$V_{CB} = 60V$ $V_{CB} = 60V$, $T_{amb} = +150$ °C
Collector Cutoff Current	I _{CEX}	_	10	nA	V _{CE} = 60V, V _{EB(off)} = 3.0V
Emitter Cutoff Current	I _{EBO}	_	10	nA	V _{EB} = 5.0V
Base Cutoff Current	I _{BL}	_	20	nA	$V_{CE} = 60V, V_{EB(off)} = 3.0V$
ON CHARACTERISTICS (Note 8)				ı	, , , , ,
DC Current Gain	h _{FE}	35 50 75 100 40 50 35	 300 		$\begin{split} &I_{C}=100\mu\text{A}, \ V_{CE}=10V\\ &I_{C}=1\text{mA}, \ V_{CE}=10V\\ &I_{C}=10\text{mA}, \ V_{CE}=10V\\ &I_{C}=150\text{mA}, \ V_{CE}=10V\\ &I_{C}=500\text{mA}, \ V_{CE}=10V\\ &I_{C}=10\text{mA}, \ V_{CE}=10V, \ T_{amb}=-55^{\circ}\text{C}\\ &I_{C}=150\text{mA}, \ V_{CE}=1V\\ \end{split}$
Collector-Emitter Saturation Voltage	V _{CE(sat)}	_	0.3 1.0	V	$I_C = 150 \text{mA}, I_B = 15 \text{mA}$ $I_C = 500 \text{mA}, I_B = 50 \text{mA}$
Base-Emitter Saturation Voltage	V _{BE(sat)}	0.6	1.2 2.0	V	$I_C = 150 \text{mA}, I_B = 15 \text{mA}$ $I_C = 500 \text{mA}, I_B = 50 \text{mA}$
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C _{obo}	_	8	pF	$V_{CB} = 10V, f = 1MHz$
Input Capacitance	C _{ibo}	_	25	pF	$V_{EB} = 0.5V$, $f = 1MHz$
Current Gain-Bandwidth Product	f⊤	300		MHz	$V_{CE} = 20V, I_{C} = 20mA,$ f = 100MHz
Noise Figure	NF		4.0	dB	$V_{CE} = 10V, I_{C} = 100\mu A,$ $R_{S} = 1k\Omega, f = 1kHz$
SWITCHING CHARACTERISTICS					
Delay Time	t _d	_	10	ns	$V_{CC} = 30V, I_C = 150mA,$
Rise Time	t _r		25	ns	$V_{BE(off)} = -0.5V, I_{B1} = 15mA$
Storage Time	ts		225	ns	$V_{CC} = 30V, I_C = 150mA,$
Fall Time	t _f	_	60	ns	$I_{B1} = -I_{B2} = 15mA$

Note: 8. Pulse test: Pulse width $\leq 300 \mu s$, duty cycle $\leq 2\%$.





Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)





Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)








Figure 10. h_{FE} v I_C




Figure 9. V_{CE} v I_B



Electrical Characteristics, 2907A Type (PNP) (@Tamb = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 9)					
Collector-Base Breakdown Voltage	BV _{CBO}	-60	_	V	I _C = -100μA
Collector-Emitter Breakdown Voltage	BV _{CEO}	-60	_	V	I _C = -10mA
Emitter-Base Breakdown Voltage	BV _{EBO}	-6.0	_	V	$I_E = -100 \mu A$
Collector Cutoff Current	I _{CBO}	_	-10	nA μA	V _{CB} = -50V
Collector Cutoff Current	I _{CEX}	_	-50	nΑ	$V_{CB} = -50V$, $T_{amb} = +125^{\circ}C$ $V_{CE} = -30V$, $V_{EB(off)} = -0.5V$
Base Cutoff Current	I _{BL}	_	-50	nA	$V_{CE} = -30V, V_{EB(off)} = -0.5V$
ON CHARACTERISTICS (Note 9)				1	10E 101, 1EB(0H) 1101
DC Current Gain	hFE	75 100 100 100 50	 300 	_	$\begin{split} I_{C} &= -100 \mu A, \ V_{CE} = -10V \\ I_{C} &= -1.0 m A, \ V_{CE} = -10V \\ I_{C} &= -150 m A, \ V_{CE} = -10V \\ I_{C} &= -150 m A, \ V_{CE} = -10V \\ I_{C} &= -500 m A, \ V_{CE} = -10V \end{split}$
Collector-Emitter Saturation Voltage	V _{CE(sat)}	_	-0.4 -1.6	V	$I_C = -150 \text{mA}, I_B = -15 \text{mA}$ $I_C = -500 \text{mA}, I_B = -50 \text{mA}$
Base-Emitter Saturation Voltage	V _{BE(sat)}	_	-1.3 -2.6	V	I _C = 150mA, I _B = 15mA I _C = 500mA, I _B = 50mA
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C _{obo}	_	8.0	pF	$V_{CB} = -10V$, $f = 1MHz$
Input Capacitance	C _{ibo}	_	30	pF	$V_{EB} = -2V$, $f = 1MHz$
Current Gain-Bandwidth Product	f _T	200	_	MHz	$V_{CE} = -20V$, $I_{C} = -50mA$, $f = 100MHz$
SWITCHING CHARACTERISTICS					
Turn-On Time	t _{on}		45	ns	_
Delay Time	t _d	_	10	ns	$V_{CC} = -30V, I_C = -150mA,$
Rise Time	t _r	_	40	ns	I _{B1} = -15mA
Turn-Off Time	t _{off}	_	100	ns	_
Storage Time	ts	_	80	ns	$V_{CC} = -6V, I_C = -150mA,$
Fall Time	t _f	_	30	ns	$I_{B1} = I_{B2} = -15mA$

Note: 9. Short duration pulse test used to minimize self-heating effect.



Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)





Figure 11. I_c v V_{CE}






Figure 13. $V_{CE(sat)} v I_{C}$




Figure 14. V_{CE(sat)} v I_C




Figure 15. V_{BE(sat)} v I_C




Figure 16. V_{BE(on)} v I_C



Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)





Figure 17. Capacitance v V_R







Figure 19. h_{FE} v I_C




Package Outline Dimensions

Please see https://www.diodes.com/design/support/packaging/diodes-packaging/ for the latest version.

SOT363






SOT363							
Dim	Min	Max	Тур				
A1	0.00	0.10	0.05				
A2	0.90	1.00	0.95				
b	0.10	0.30	0.25				
C	0.10	0.22	0.11				
D	1.80	2.20	2.15				
Е	2.00	2.20	2.10				
E1	1.15	1.35	1.30				
е	0.650 BSC						
F	0.40	0.45	0.425				
١	0.25	0.40	0.30				
а	0°	8°					
All I	All Dimensions in mm						

Suggested Pad Layout

Please see https://www.diodes.com/design/support/packaging/diodes-packaging/ for the latest version.

SOT363



Dimensions	Value
Dillielisions	(in mm)
С	0.650
G	1.300
Х	0.420
Y	0.600
Y1	2.500



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com

MMDT2227Q Document number: DS40088 Rev. 2 - 2