

2.5V/3.3V HCSL FS XO

NX74SB



7.0 x 5.0mm Ceramic SMD

Product Features

- 4 selectable output frequencies
- Meet PCle Gen2 and Gen3 clock requirements at 100MHz
- Very low phase jitter < 1.0ps RMS max.
- Wide frequency range $5 \sim 212.5 \text{MHz}$
- Thicker crystal for improved reliability
- Low supply current 70mA max.
- Industrial Temperature Range
- Pb-free & RoHS compliant
- Fast lead time


Product Description


The NX74SB XO series is a high performance HCSL crystal oscillator family with very low jitter performance. Depending on customers' needs, this family devices can support 4 different frequencies using the FS select pins. It supports various options including wider frequency range, 2.5V/3.3V voltage, and various stabilities. It is designed to meet the clock source specifications for communication systems, and other high performance equipment.


Applications

- Networking systems
- Servers and storage systems
- FPGA/ASIC clock generation

Package: (Scale: none, Dimensions are in mm)








*Extended high frequency power decoupling is recommended (see test circuit for minimum recommendation). To ensure optimal performance, do not route RF traces beneath the package.

Part Ordering Information:



Recommended Land Pattern:

Pin Functions:

Pin	Function					
1	FS1					
2	FS0					
3	Ground					
4	Q					
5	\overline{Q}					
6	V _{CC}					

Frequency Select Table:

_	•	
FS0	FS1	Output
0	0	Freq. 1*
0	1	Freq. 2*
1	0	Freq. 3*
1	1	Freq. 4*

*Freq. 1, Freq. 2, Freq. 3, Freq. 4 can be any frequencies within the output frequency range.

SaRonix-eCera[™] is a Pericom® Semiconductor company • US: +1-408-232-9100 TW: +886-3-4518888





Ultra Low Jitter PLL Crystal Oscillator 7.0 x 5.0mm

Electrical Performance

Parameter		Min.	Тур.	Max.	Units	Notes
Output Frequency		5		212.5	MHz	
C and William		3.135	3.3	3.465	V	
Supply voltage	Supply Voltage		2.5	2.625	v	
Supply Current, Out	tput Enabled			70	mA	
Frequency Stability				±50	ppm	±20ppm is for -20°C to 70°C only
Operating Temperature Range		-40		+85	°C	
Output Logic 0, VOI	Output Logic 0, V _{OL}		0		V	
Output Logic 1, V _{OH}		0.66	0.7	0.9	V	
Output Load		$R_S = 33\Omega$, $R_P = 50\Omega$, $C_L = 2pF$				Output requires termination
Duty Cycle		45		55	%	Measured 50% V _{CC}
Rise and Fall Time				700	ps	Measured from $V_{OL} = 0.175V$ to $V_{OH} = 0.5252V$
Jitter, RMS	PCIe Gen2, 100 MHz		2.0	3.0	ps	As defined by PCI-SIG for PCIe Gen2
Jitter, RMS	PCIe Gen3, 100 MHz		0.43	1.0	ps	As defined by PCI-SIG for PCIe Gen3
Jitter, Accumulated, RMS (1-σ)				6	ps	20.000 adjacent periods
	< 40MHz		0.4	1	ps	12kHz to 5 MHz frequency band
Jitter, Phase, RMS	40 to 212.5MHz		0.4	1	ps	12kHz to 20 MHz frequency band
	100MHz, 125MHz		0.4	0.6	ps	12kHz to 20 MHz frequency band
Jitter, pk-pk				40	ps	100,000 random periods

Notes:

- Stability includes all combinations of operating temperature, load changes, rated input (supply) voltage changes, initial calibration tolerance (25°C), aging (1 year at 25°C average effective ambient temperature), shock and vibration.
- Phase jitter typical value is depending on output frequencies.
- For specifications other than those listed, please contact sales.

Frequency Select Function

Parameter	Min.	Тур.	Max.	Units	Notes
Input Voltage (pin 1 & pin 2), FS1 & FS0	0.7 V _{CC}			V	
Input Voltage (pin 1 & pin 2), FS1 & FS0			0.3 V _{CC}	V	
Settling Time after FS Change			10	ms	
Start up Time			10	ms	

Absolute Maximum Ratings

Parameter	Min.	Тур.	Max.	Units	Notes
Storage Temperature	-55		+125	°C	

For the latest product information visit: http://www.pericom.com/products/crystals-and-crystal-oscillators/hiflex-xo/?part=NX74SB

For test circuit go to: For test circuit go to: http://www.pericom.com/pdf/sre/tc-hcsl-sb.pdf

For soldering reflow profile and reliability test ratings go to: http://www.pericom.com/pdf/sre/reflow.pdf

For tape and reel information go to: http://www.pericom.com/pdf/sre/tr 7050 xo.pdf



NX74SB