



PAM8902H

30VPP MONO CLASS-D AUDIO AMPLIFIER FOR PIEZO/CERAMIC SPEAKERS

Description

The DIODES[™] PAM8902H is a mono, Class-D audio amplifier with integrated boost converter designed for piezo and ceramic speakers. The PAM8902H is capable of driving a ceramic/piezo speaker with 30VPP (10.6Vrms) from a 3.6V power supply. The PAM8902H's boost converter operates at a fixed frequency of 1.5MHz, and provides a 17.5V supply with a minimum number of external components. The PAM8902H features an integrated audio low pass filter that rejects high frequency noise thus improving audio fidelity. And there are three gain modes of 21dB, 26dB, and 32.5dB for easy using. The PAM8902H also provides thermal, short, under and overvoltage protection.

The PAM8902H is available in a 16-ball 1.95mm x 1.95mm CSP-16L package and 16-pin W-QFN4040-16 (Standard) package.

Features

- Supply Voltage Range from 2.5V to 5.5V
- 30VPP Output Load Voltage from a 2.5V Supply
- Integrated Boost Converter Generates 17.5V Supply
- Programmable Soft-Start
- Small Boost Converter Inductor
- Selectable Gain of 21dB, 26dB, and 32.5dB
- Selectable Boost Output Voltage of 8V, 12V, and 17.5V
- Low Shutdown Current: < 1µA
- Built-in Thermal, OCP, OVP, Short Protection
- Available in Space Saving Packages:
 - 16-Ball 1.95mm x 1.95mm CSP-16L Package
 - 16-Pin W-QFN4040-16 (Standard) Package
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

Applications

- Wireless or cellular handsets
- Portable DVD players
- Personal digital assistants (PDAs)
- Electronic dictionaries
- Digital still cameras

Notes:


1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and

 See https://www.diodes Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.</p>


January 2023 © 2023 Copyright Diodes Incorporated. All Rights Reserved.

Pin Assignments



(NRND)


Top View W-QFN4040-16 (Standard)



: Pin 1 Indicator



Typical Applications Circuit




Pin Descriptions

Pin Name	Bump CSP-16L	Pin Number W-QFN4040-16 (Standard)	Function
PVCC	A1	16	Audio Amplifier Power Supply
VOUT	A2	1	Boost Converter Output
SW	A3	2	Boost Converter Switching Node
PGND1	A4	4	Boost Converter Power Ground
OUT+	B1	15	Positive Differential Audio Output
VSET	B2	3	Boost Converter Output Voltage Setting (8V, 12V, 17.5V)
COMP	B3	5	Boost Converter Compensation
AVDD	B4	6	Power Supply
OUT-	C1	14	Negative Differential Audio Output
GSET	C2	11	Amplifier Gain Setting (21dB, 26dB, 32.5dB)
VCM	C3	7	Common Mode Bypass Cap
AGND	C4	8	Analog Ground
PGND2	D1	13	Class D Power Ground
ENA	D2	12	Whole Chip Enable
INN	D3	10	Negative Differential Audio Input
INP	D4	9	Positive Differential Audio Input



Functional Block Diagram



Absolute Maximum Ratings (Note 4) (@TA = +25°C, unless otherwise specified.)

Parameter	Rating	Unit	
Supply Voltage	6.0		
Input Voltage	-0.3 to V _{DD} +0.3	v	
Storage Temperature	-65 to +150		
Maximum Junction Temperature	+150	°C	
Soldering Temperature	+250, 10s		

Notes: 4. Stresses greater than those listed under Absolute Maximum Ratings can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to Absolute Maximum Ratings for extended periods can affect device reliability. All voltages are with respect to ground.

Recommended Operating Conditions (@TA = +25°C, unless otherwise specified.)

Parameter	Rating	Unit
Supply Voltage Range	2.5 to 5.5	V
Ambient Temperature Range	-40 to +85	ŝ
Junction Temperature Range	-40 to +125	C



Thermal Information

Parameter	Symbol	Package	Maximum	Unit	
Thermal Resistance	0	CSP-16L	90	°C/W	
(Junction to Ambient)	θ」Α	W-QFN4040-16 (Standard)	52	C/W	
Thermal Resistance	0	CSP-16L	72	8CAM	
(Junction to Case)	θις	W-QFN4040-16 (Standard)	30	°C/W	


Electrical Characteristics (@T_A = +25°C, V_{DD} = 3.6V, C_L = 1µF, V_{SET} Float, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit	
Vdd	Input Voltage	—	2.5	_	5.5	V	
		V _{EN} > 1.2V, V _{SET} = High	_	30	48		
lq	Quiescent Current	V _{EN} > 1.2V, V _{SET} = Floating	_	10	18	mA	
		V _{EN} > 1.2V, V _{SET} = GND	_	5	12		
Isd	Shutdown Current	V _{EN} = 0V	_	0.1	1.0	μA	
twu	Wake-up Time	VEN from Low to High	_	40	_	ms	
VEH	Chip Enable	—	1.2	_	—	N/	
VEL	Chip Disable	—	—	_	0.4	V	
Vн	GSET/VSET High	—	V _{DD} -0.5	_	Vdd		
VF	GSET/VSET Floating	—	1	_	Vdd -1	V	
VL	GSET/VSET Low	—	0	_	0.5		
UVLO	Undervoltage Lockout Threshold	VDD from High to Low	_	2.2	_		
UVLOH	Undervoltage Lockout Hysteresis	VDD from Low to High	_	0.2	_	V	
OTP	Thermal Shutdown Threshold	—	_	+150	_	°C	
OTPH	Thermal Shutdown Lockout Hysteresis	—	_	+30	_	°C	
Boost Cor	iverter						
Vo1		V _{SET} = GND, No Load	7.2	8.0	8.8	V	
Vo2	Output Voltage	V _{SET} = NC, No Load	10.8	12.0	13.2	V	
Vo3		V _{SET} = AVDD, No Load	16	17.5	19	V	
CL	Current Limit	Average Input Current	_	1.0	_	А	
RLS	Low Side MOSFET RDS(ON)	I _O = 50mA	_	0.5	_	Ω	
foscв	Boost Switching Frequency	—	1.1	1.5	1.9	MHz	
Class D							
fosco	Class-D Amplifier Switching Frequency	Input AC-GND	225	375	475	kHz	
CMRR	Common Mode Reject Ratio	V _{IN} = ±100mV, V _{DD} = 3.6V	_	60	_	dB	
Vos	Output Offset Voltage	Output Offset Voltage	_	5	50	mV	
_	2	High Side	_	1.5		Ω	
RP	RDS(ON)	Low Side	_	0.6	_	Ω	
A∨1		G _{SET} = AVDD, V _O = 1V _{RMS}	_	32.5	_		
Av2	Closed-Loop Voltage Gain	GSET = AVDD, VO = 1VRMS	_	26	—	dB	
Av3	1	GSET = AVDD, VO = 1VRMS	_	21	_		
PSRR	Power Supply Reject Ratio	200m VPP Supply Ripple @ 217Hz		70	_	dB	
THD+N	Total Harmonious Distortion Plus Noise	Vo = 5V _{RMS}		0.3	_	%	
SNR	Signal to Noise Ratio	Input AC Ground, A-Weighting		90	_	dB	



Typical Operating Characteristics


 $(@T_A = +25^{\circ}C, V_{DD} = 4.2V, Gain = 26dB, C_{IN} = 1\mu F, C_{LOAD} = 1\mu F, unless otherwise specified.)$




PAM8902H Document number: DS36453 Rev. 5 - 2




Typical Operating Characteristics (@TA = +25°C, VDD = 5V, Gain = 18dB, unless otherwise specified.)




8. Output Voltage RMS VS Frequency



10. Output Voltage RMS VS Frequency



12. Output Voltage RMS VS THD+N



PAM8902H Document number: DS36453 Rev. 5 - 2

Output Voltage RMS



Application Information

Select Boost Converter Output Voltage

Customer can use V_{SET} pin to set boost converter output voltage between 8V, 12V and 17.5V. V_{SET} pin configuration table as below:

VSET Pin Configuration	Min	Мах	PVCC Voltage	Audio Amplifier Maximum Output Voltage
Connect to AVDD	AVDD – 0.5V	AVDD	17.5V	11V _{RMS} (V _{PP} = 31.1V)
Floating	1V	AVDD – 1V	12V	8Vrms (Vpp = 22.6V)
Connect to GND	GND	0.5V	8V	5V _{RMS} (V _{PP} = 14.1V)

Input Resistance (Ri)

The input resistors ($R_I = R_{IN} + R_{EX}$) set the gain of the amplifier according to Equation 1 when anti-saturation is inactive.

GSET	Rın	RF
GSET = VDD	36.5kΩ	122.6kΩ
GSET = Floating	59kΩ	100kΩ
G _{SET} = GND	82kΩ	77.4kΩ

$G = 20 \text{ Log } [12.8 \text{ x } R_F/(R_{IN} + R_{EX})] (dB)$

Where R_{IN} is a 77.4k Ω internal resistor, R_{EX} is the external input resistor, R_F is a 122.6k Ω internal resistor. Resistor matching is very important in fully differential amplifiers. The balance of the output on the reference voltage depends on matched ratios of the resistors. CMRR, PSRR, and cancellation of the second harmonic distortion diminish if resistor mismatch occurs. Therefore, it is recommended to use 1% tolerance resistors or better to keep the performance optimized. Matching is more important than overall tolerance. Resistor arrays with 1% matching can be used with a tolerance greater than 1%.

Place the input resistors very close to the PAM8902H to limit noise injection on the high-impedance nodes. For optimal performance the gain should be set to lower. Lower gain allows the PAM8902H to operate at its best, and keeps a high voltage at the input making the inputs less susceptible to noise. In addition to these features, higher value of R_I minimizes pop noise.

Input Capacitors (Ci)

In the typical application, an input capacitor, C_I, is required to allow the amplifier to bias the input signal to the proper DC level for optimum operation. In this case, C_I and the minimum input impedance R_I form is a high-pass filter with the corner frequency determined in the following equation:

$$f_{\rm C} = \frac{1}{2\pi R_{\rm I} C_{\rm I}}$$

It is important to consider the value of C_I as it directly affects the low frequency performance of the circuit. For example, when R_I is 150k Ω and the specification calls for a flat bass response are down to 150Hz. Equation is reconfigured as follows:

$$C_{I} = \frac{1}{2\pi R_{IFC}}$$

When input resistance variation is considered, the C_I is 7nF, so one would likely choose a value of 10nF. A further consideration for this capacitor is the leakage path from the input source through the input network (C_I , $R_I + R_F$) to the load. This leakage current creates a DC offset voltage at the input to the amplifier that reduces useful headroom, especially in high gain applications. For this reason, a low-leakage tantalum or ceramic capacitor is the best choice. When polarized capacitors are used, the positive side of the capacitor should face the amplifier input in most applications as the DC level is held at $V_{DD}/2$, which is likely higher than the source DC level. Please note that it is important to confirm the capacitor polarity in the application.



Application Information (continued)

Decoupling Capacitor

The PAM8902H is a high-performance CMOS audio amplifier that requires adequate power supply decoupling to ensure the output Total Harmonic Distortion (THD) as low as possible.

The optimum decoupling is achieved by using two different types of capacitors that target on different types of noise on the power supply leads. For higher frequency transients, spikes or digital hash on the line, a good low Equivalent Series Resistance (ESR) ceramic capacitor, typically 1µF, is placed as close as possible to the device AVDD pin for the best operation. For filtering lower frequency noise signals, a large ceramic capacitor of 10µF or greater placed near the AVDD supply trace is recommended.

External Schottky Diode

Using external Schottky diode can get the best driving capability and efficiency. Since internal power diode has limited driving capability, only in the following conditions can customer remove the external Schottky diode to reduce the cost.

- 1. V_{SET} = GND or Floating and C_L less than 1µF.
- 2. The signal frequency less than 4kHz.
- 3. Haptic application (50 to 500Hz)

Shutdown Operation

In order to reduce power consumption while not in use, the PAM8902H contains shutdown circuitry amplifier off when a logic low is placed on the ENA pin. By switching the ENA pin connected to GND, the PAM8902H supply current draw will be minimized in idle mode.

Undervoltage Lockout (UVLO)

The PAM8902H incorporates circuitry designed to detect supply voltage. When the supply voltage drops to 2.2V or below, the PAM8902H goes into a state of shutdown, and the device comes out of its shutdown state and restore to normal function only when resetting the power supply or ENA pin.

Short Circuit Protection (SCP)


The PAM8902H has short circuit protection circuitry on the outputs to prevent the device from damage when output-to-output shorted or output-to-GND shorted occurs. When a short circuit occurs, the device goes into a latch state and must be reset by cycling the voltage on the ENA pin to a logic low and then back to the logic high state for normal operation. This will clear the short-circuit flag and allow for normal operation if the short was removed. If the short was not removed, the protection circuitry will again be activated.

Overtemperature Protection (OTP)

Thermal protection on the PAM8902H prevents the device from damage when the internal die temperature exceeds +150°C. There is a +15°C tolerance on this trip point from device to device. Once the die temperature exceeds the set point, the device will enter the shutdown state and the outputs are disabled, in this condition both OUT+ and OUT- will become high impedance. This is not a latched fault. The thermal fault is cleared once the temperature of the die decreased by +30°C. This large hysteresis will prevent motor boating sound well and the device begins normal operation at this point with no external system interaction.




Ordering Information



Part Number	Part Marking	Package	Pack	Status		
Fait Nulliper	Fait Marking	Раскауе	Qty.	Carrier	Status	
PAM8902HZER	BT YW	CSP-16L	3000 Units	Tape and Reel	NRND (<mark>CONTACT US</mark>)	
PAM8902HKER	P8902H XXXYW	W-QFN4040-16 (Standard)	3000 Units	Tape and Reel	Active	

NRND: Not Recommended for New Design.


Marking Information






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.



W-QFN4040-16 (Standard)




	W-QFN4040-16						
((Type Standard)						
Dim	Min	Max	Тур				
Α	0.55	0.80	0.75				
A1	0.00	0.05					
A3	-	-	0.203				
b	0.25	0.35	0.30				
D	3.95	4.05	4.00				
D2	2.45	2.55	2.50				
Е	3.95	4.05	4.00				
E2	2.45	2.55	2.50				
е	(0.65 B	SC				
e1	1	.950 F	REF				
L	0.35	0.45	0.40				
z			0.875				
All	All Dimensions in mm						



Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



W-QFN4040-16 (Type Standard)

Dimensions	Value
Dimensions	(in mm)
С	0.650
G	0.250
G1	0.250
Х	0.400
X1	2.350
X2	2.600
Y	0.600
Y1	2.350
Y2	2.600
Y3	4.300

Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.042 grams (Approximate)



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' products are provided subject Diodes' Standard Terms and Conditions of to Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com