

A Product Line of Diodes Incorporated



Features

- → CMOS Technology for Bus and Analog Applications
- → Low On-Resistance: 0.45Ω
- → Wide V_{DD} Range: 1.65V to 4.2V
- ➔ Rail-to-Rail Signal Range
- → High Off Isolation: -83dB @ 100kHz
- ➔ Crosstalk Rejection Reduces Signal Distortion: -108dB @ 100kHz
- ➔ Break-Before-Make Switching
- ➔ Extended Industrial Temperature Range: -40°C to 85°C
- → ESD protection : 4kV(HBM)
- → Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- → Halogen and Antimony Free. "Green" Device (Note 3)
- ➔ Packaging (Pb-free & Green): -10-pin UQFN (ZM), 1.4mm × 1.8mm

Block Diagram



Pin Configuration (top view)



Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Small Plastic Package, Dual SPDT Analog Switch

Description

PI3A2268 is a dual fast single-pole double throw (SPDT) CMOS switch. It can be used as an analog switch or as a lowdelay bus switch. Specified over a wide operating power supply voltage, 1.65V to 4.2V, the PI3A2268 has an On-Resistance of 0.45Ω at +4.2V.

Break-before-make switching prevents both switches being enabled simultaneously. This eliminates signal disruption during switching.

Applications

- → Cell Phones
- → PDAs
- → MP3 Players
- ➔ Portable Instrumentation
- → Computer Peripherals
- ➔ Speaker Headset Switching
- → Power Routing
- → Relay Replacement
- → Audio and Video Signal Routing
- → PCMCIA Cards
- ➔ Modems

Pin Description

Pin no	Name	Description
1	NO1	Data Port (Normally open)
2	NC2	Data Port (Normally closed)
3	NO2	Data Port (Normally open)
4	GND	Ground
5	COM2	Common Output / Data Port
6	IN2	Logic Control
7	IN1	Logic Control
8	COM1	Common Output / Data Port
9	V _{DD}	Positive Power Supply
10	NC1	Data Port (Normally closed)
	-	

Logic Function Table

Logic Input (IN _X)	Function
0	NC _X Connected to COM _X
1	NO_X Connected to COM_X
Note: $x = 1$ or 2	





Maximum Ratings

Storage Temperature	65°C to +150°C
Ambient Temperature with Power Applied	40°C to +85°C
Supply Voltage V _{DD}	0.5Vto +4.6V
Control Input Voltage V _{INx}	0Vto +4.6V
DC Input Voltage V _{INPUT}	0.5Vto +4.6V
Continuous Current NO_NC_COM	±300mA
Peak Current NO_NC_COM_	
(pulsed at 1ms 50% duty cycle)	±400mA
Peak Current NO_NC_COM_	
(pulsed at 1ms 10% duty cycle)	±500mA
ESD(HBM)	4kV

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Control input must be held HIGH or LOW; it must not float.

Recommended Operating Conditions

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
V _{DD}	Operating Voltage	-	1.65	-	4.2	V
V _{IN}	Control Input Voltage	-	0	-	V _{DD}	V
V _{INPUT}	Switch Input Voltage	-	-0.3	-	4.2	V
T _A	Operating Temperature	-	-40	25	85	°C
t _r , t _f	Input Rise and Fall Time	-	0	-	10	ns/V

DC Electrical Characteristics

+3.0V Supply (V_{DD} = 2.7V to 3.6V, V_{IH} =+1.6V, V_{IL} =+0.4V, T_A = -40°C to 85°C, unless otherwise noted. Typical values are at 3.0V and +25°C.)

Parameter	Symbol	Test Conditions	TEMP	Min.	Тур.	Max.	Units
ANALOG SWITCH							
Analog Signal Range	$V_{ m NO}, V_{ m NC}, V_{ m COM}$	-	-40°C to 85°C	0	-	V_{DD}	v
O. D. L	P	$V_{DD} = 2.7V, I_{COM} = 100mA, V_{NO} \text{ or}$	+25°C	-	0.55	0.9	0
On-Resistance	R _{ON}	$V_{\rm NC} = 1V$, Test Circuit 1	-40°C to 85°C	-	0.55	1	Ω
On-Resistance Match	ΔR_{ON}	$V_{DD} = 2.7V, I_{COM} = 100mA, V_{NO} \text{ or}$	+25°C	-	0.05	0.22	0
Between Channels		V _{NC} =1V, Test Circuit 1	-40°C to 85°C	-	0.05	0.25	52
On-Resistance	р	$V_{DD} = 2.7V, I_{COM} = 100mA, V_{NO} \text{ or}$	+25°C	-	0.1	0.22	0
Flatness	KONF	$V_{NC} = 1V, 2.5V, Test Circuit 1$	-40°C to 85°C	-	0.1	0.26	52
Source Off Leakage Current	$I_{OFF (NO)}$ or $I_{OFF (NC)}$	V_{DD} =3.6V, V_{NO} or V_{NC} = 3.3V/0.3V, V_{COM} = 0.3V/3.3V	-40°C to 85°C	-	-	1	
Channel On Leakage Current	I _{NC(ON)} , I _{NO(ON)} , I _{COM} (ON)	$V_{DD} = 3.6V$, V_{NO} or $V_{NC} = 3V/$ 0.3V, $V_{COM} = 3V/0.3V$, or floating	-40°C to 85°C	-	-	1	μΑ
DIGITAL INPUTS							
Input Logic High	V_{IH}	-	-40°C to 85°C	1.2	-	-	V
Input Logic Low	V _{IL}	-	-40°C to 85°C	-	-	0.5	v
IN Input Leakage Current	I_{IN}	$V_{DD} = 2.7V, V_{IN} = 0 \text{ or } 2.7V$	-40°C to 85°C	-	-	1	μΑ
DYNAMIC CHARAC	TERISTICS						
Turn-On Time	t _{ON}	$V_{IH}=1.5V, V_{IL}=0V,$ See Test Circuit Figure 2.	+25°C	-	15	-	ns
Turn-Off Time	t _{OFF}	$V_{IH}=1.5V, V_{IL}=0V,$ See Test Circuit Figure 2.	+25°C	-	20	-	ns
Break-Before-Make Delay	t _D	$V_{IH}=1.5V, V_{IL}=0V,$ See Test Circuit Figure 3.	+25°C	-	10	-	ns
COM-NC/NO and	O _{ISO}	$V_{BIAS}=1.5V, V_{IN}=0dBm,$ 100kHz	+25 °C	-	-81	-	dB



A Product Line of Diodes Incorporated



NC-NO Isolations		V _{IH} =1.5V, V _{IL} =0V. See Test Circuit Figure 4 &	1MHz	+25°C	-	-61	-	
		Figure 5.	10MHz	+25°C	-	-39	-	
		$V_{BIAS} = 1.5 V,$	100kHz	+25°C	-	-108	-	
Channel-to-Channel Crosstalk	X_{TALKD}	$V_{DD}=0dBm, V_{IH}=1.5V,$ $V_{II}=0V$ See Test Circuit	1MHz	+25°C	-	-110	-	dB
		Figure 6.	10MHz	+25°C	-	-90	-	
3dB Bandwidth	f_{3dB}	$V_{BIAS} = 1.5V, V_{IN}=0dBm,$ $V_{IH}=1.5V, V_{IL}=0V.$ See Test Circuit Figure 7.		+25°C	-	79	-	MHz
Charge Injection Select Input to Common I/O	Q	$V_{IN} = GND, R_S = 0, C_L = 1nF,$ $V_{IH}=1.5V, V_{IL}=0V$ See Test Circuit Figure 8.		+25°C	-	35	-	pC

+4.2V Supply ($V_{DD} = 4.2V$, $T_A = -40^{\circ}$ C to 85°C, unless otherwise noted. Typical values are at 4.2V and +25°C.)

Parameter	Symbol	Test Conditions		TEMP	Min.	Тур.	Max.	Units
ANALOG SWITCH								
Analog Signal Range	V _{NO} , V _{NC} , V _{COM}	-		-40°C to 85°C	0	-	V _{DD}	v
0. 0. 1.	5	$V_{DD} = 4.2V, I_{COM} = 100mA$	A, V_{NO} or	+25°C	-	0.45	0.75	0
On-Resistance	\mathbf{R}_{ON}	$V_{\rm NC} = 1$ V, Test Circuit 1	$V_{\rm NC} = 1V$, Test Circuit 1		-	0.45	0.85	Ω
On-Resistance Match	٨D	$V_{DD} = 4.2V, I_{COM} = 100mA$	A, V _{NO} or	+25°C	-	0.05	0.18	0
Between Channels	ΔK_{ON}	V _{NC} =1V, Test Circuit 1		-40°C to 85°C	-	0.05	0.23	\$2
On-Resistance	R _{ONF}	$V_{DD} = 4.2V, I_{COM} = 100mA$	A, V _{NO} or	+25°C	-	0.1	0.22	0
Flatness		$V_{NC} = 1V, 2.5V, Test Circ$	cuit 1	-40°C to 85°C	-	0.1	0.26	22
Source Off	$I_{OFF(NO)}$ or	V_{DD} = 4.2V, V_{NO} or	V _{NC} =	-40°C to 85°C	_	_	1	
Leakage Current	I _{OFF (NC)}	$3.3V/0.3V, V_{COM} = 0.3V/3$	V	-40 C to 85 C	_	_	1	
Channel On Leakage	I _{NC(ON)} ,	$V_{DD} = 4.2V$, V_{NO} or V_{N}	$_{\rm MC} = 3V/$					μA
Current	$I_{NO(ON)}, I_{COM}$	$0.3V, V_{CO}M = 3V/0.3V, or$	floating	-40°C to 85°C	-	-	1	
DICITAL INPUTS	(ON)		······································					
Input Logic High	V _m	_		-40°C to 85°C	12	_	_	
Input Logic Low	V _{IH}			-40° C to 85 °C	1.2		0.5	V
IN Input Leakage	V IL			-40° C to 85 °C	-	-	0.5	
Current	I_{IN}	$V_{DD} = 4.2V, V_{IN} = 0 \text{ or } 4.2V$		-40 C 10 85 C	-	-	1	μA
DYNAMIC CHARAC	CTERISTICS							
Turn-On Time	t _{ON}	$V_{IH}=3V, \overline{V_{IL}=0V},$ See Test Circuit Figure 2.		+25°C	-	13	-	ns
Turn Off Time	4	$V_{IH}=3V, V_{IL}=0V,$		125°C		12		
Turn-Off Time	LOFF	See Test Circuit Figure 2.		+25 °C	-	12	-	ns
Break-Before-Make	t _D	V _{IH} =3V, V _{IL} =0V, See Test Circuit Figure 3		+25°C	-	8	-	ns
Delay		See Tesi Circuit Figure 5.	40.04 77	0 0				
		$V_{BIAS} = 2.1 V,$	100kHz	+25°C	-	-83	-	
COM-NC/NO and NC-NO Isolations	O _{ISO}	$V_{IN}=0$ dBm, $V_{IH}=3V$, $V_{IL}=0V$. See Test Circuit	1MHz	+25°C	-	-61	-	dB
		Figure 4 & Figure 5.	10MHz	+25°C	-	-39	-	
		$V_{BIAS} = 2.1 V,$	100kHz	+25°C	_	-108	_	
Channel-to-channel Crosstalk	X _{TALK}	V _{IN} =0dBm, V _{IH} =3V, V _{II} =0V See Test Circuit	1MHz	+25°C	-	-110	-	dB
		Figure 6.	10MHz	+25°C	-	-90	-	
3dB Bandwidth	$f_{\rm 3dB}$	$V_{BIAS} = 2.1V, V_{IN}=0dBm,$ $V_{IL}=0V.$ See Test Circuit F	V _{IH} =3V, <i>Figure 7</i> .	+25°C	-	84	-	MHz
		•	~					





Charge Injection		$V_{IN} = GND, R_S = 0, C_L = 1nF,$					
Select Input to	Q	$V_{IH}=3V, V_{IL}=0V$	+25°C	-	50	-	pC
Common I/O		See Test Circuit Figure 8.					
POWER REQUIREN	IENTS						
Power Supply Range	V _{DD}	-	-40°C to 85°C	1.65	-	4.2	V
Power Supply	I _{CC}	$V_{DD}=4.2V, V_{IN}=0V \text{ or } V_{DD}$	-40°C to 85°C	_	_	1	μA
Current							•

Capacitance

Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Units
NC Off Capacitance	C _{NC (OFF)}	f = 1MHz, See Test Circuit Figure 9.	-	20	-	
NO Off Capacitance	C _{NO (OFF)}	f = 1MHz, See Test Circuit Figure 9.	-	20	-	ъF
NC On Capacitance	C _{NC (ON)}	f = 1MHz, See Test Circuit Figure 10.	-	55	-	рг
NO On Capacitance	C _{NO (ON)}	f = 1MHz, See Test Circuit Figure 10.	-	55	-	





Test Circuits and Timing Diagrams



Figure 1. On Resistance

Notes: 1. Unused input (NC or NO) must be grounded.



Figure 2. Switching Times



Figure 3. Break Before Make Interval Timing







Figure 4. COM-NC/NO Isolation



Figure 5. NC-NO Isolation







Figure 6. Channel-to-Channel Crosstalk



Figure 7. Bandwidth



Figure 8. Charge Injection







Figure 9. Channel Off Capacitance



Figure 10. Channel On Capacitance

Part Marking

ZM Package







Packaging Mechanical: 10-UQFN (ZM10)



09-0072

For latest package information:

Please see http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/.

Ordering Information

Part Number	Packaging Code	Description
PI3A2268ZMEX	ZM	10-contact, Ultra-thin Quad Flat No-Lead (UQFN)

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain \leq 900ppm bromine, \leq 900ppm chlorine (\leq 1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. E = Pb-free and Green

5. X suffix = Tape/Reel





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated www.diodes.com