



20V PNP LOW-SATURATION TRANSISTOR IN SOT26

Description

This bipolar junction transistor (BJT) is designed to meet the stringent requirements of automotive applications.

Features

- BVcEo > -20V
- Ic = -2.5A Continuous Collector Current
- I_{CM} = -6A Peak Pulse Current
- $R_{CE(sat)} = 96m\Omega$ for a Low Equivalent On-Resistance
- Low Saturation Voltage (-220mV max @ -1A)
- hFE Characterized Up to -6A for High Current Gain Hold-Up
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The ZXT10P20DE6Q is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Mechanical Data


- Package: SOT26
- Package Material: Molded Plastic, "Green" Molding Compound;
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202. Method 208 (3)
- Weight: 0.015 grams (Approximate)

Applications


- DC-DC converters
- Power-management functions
- Power switches
- Motor controls







Device Symbol



Pin-Out Top View


Ordering Information (Note 4)

Part Number	Packago	Marking	Reel Size (inches)	Tape Width (mm)	Packing		
Part Number	Package	Warking	Reel Size (Iliches)	rape widin (iiiii)	Qty.	Carrier	
ZXT10P20DE6QTA	SOT26	718	7	8	3000	Reel	

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



718 = Product Type Marking Code YM = Date Code Marking Y or \overline{Y} = Year (ex: K = 2023) M or \overline{M} = Month (ex: 6 = June)

Date Code Key

Year	2018	-	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	F	-	K	L	М	N	Р	R	S	T	U	V
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
MOTILLI	oun	1 65	iviai	ΛPi	itiuy	oun	oui	,9				



Absolute Maximum Ratings ($@T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	Vсво	-20	V
Collector-Emitter Voltage	Vceo	-20	V
Emitter-Base Voltage	VEBO	-7	V
Base Current	lв	-500	mA
Continuous Collector Current	lc	-2.5	Α
Peak Pulse Collector Current	Ісм	-6	Α

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Power Dissipation	(Note 5)		1.1 8.8	W mW/°C	
Linear Derating Factor	(Note 6)	PD	1.7 13.6	W mW/°C	
Thermal Decistores, Junction to Ambient	(Note 5)	В	113	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	R _{θJA}	73	C/VV	
Thermal Resistance, Junction to Case	(Note 5)	Rejc	12	°C/W	
Thermal Resistance, Junction to Leads (Note 7)		Røjl	30	°C/W	
Operating and Storage Temperature Range	TJ, TSTG	-55 to +150	°C		

ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge – Human Body Model	ESD HBM	4000	V	3A
Electrostatic Discharge – Machine Model	ESD MM	400	V	С


Notes:

- 5. For a device mounted with collector leads on 25mm x 25mm 2oz copper that is on a single-sided 1.6mm FR-4 PCB; device is measured under still air conditions whilst operating in a steady state.
- 6. Same as Note 5, except the device is measured at $t \le 5$ secs.
- 7. Thermal resistance from junction to solder-point (at the end of the collector leads).

 8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics and Derating Information






Figure 2. Derating Curve




Figure 3. Transient Thermal Impedance




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS						
Collector-Base Breakdown Voltage	ВУсво	-20	-65		٧	Ic = -100μA
Collector-Emitter Breakdown Voltage (Note 9)	BVceo	-20	-53	_	V	Ic = -10mA
Emitter-Base Breakdown Voltage	BVEBO	-7	-8.8	_	V	I _E = -100μA
Collector-Base Cutoff Current	Ісво	_	-1	-100	nA	V _{CB} = -15V
Emitter Cutoff Current	I _{EBO}	_	-1	-100	nA	V _{EB} = -5V
Collector-Emitter Cutoff Current	ICES	1	-1	-100	nA	V _{CES} = -15V
ON CHARACTERISTICS (Note 9)						
		300	475	_		I _C = -10mA, V _{CE} = -2V
DC Current Gain	hFE	300	450	_		I _C = -0.1A, V _{CE} = -2V
DC Current Gain		150	230	_	_	Ic = -2A, VcE = -2V
		15	30	_	_	Ic = -6A, VcE = -2V
		_	-19	-30		Ic = -0.1A, I _B = -10mA
Collector-Emitter Saturation Voltage	V		-170	-220	mV	Ic = -1A, I _B = -20mA
Collector-Emitter Saturation Voltage	V _{CE(sat)}		-190	-250	IIIV	Ic = -1.5A, I _B = -50mA
		_	-240	-350		Ic = -2.5A, I _B = -150mA
Base-Emitter Saturation Voltage	V _{BE(sat)}	_	-0.97	-1.05	V	Ic = -2.5A, I _B = -150mA
Base-Emitter Turn-On Voltage	V _{BE(on)}	_	-0.85	-0.95	V	Ic = -2.5A, VcE = -2V
SMALL SIGNAL CHARACTERISTICS						
Current Gain-Bandwidth Product	f⊤	150	180	_	MHz	VcE = -10V, Ic = -50mA, f = 100MHz
Output Capacitance	C _{obo}	-	21	30	pF	V _{CB} = -10V, f = 1MHz
Turn-On Time	t _(on)	1	40	_	ns	Vcc = -10V, Ic = -1A,
Turn-Off Time	t _(off)		670	_	ns	$I_{B1} = -I_{B2} = -20 \text{mA}$


Note: 9. Measured under pulsed conditions. Pulse width $\leq 300 \mu s$. Duty cycle $\leq 2\%$.





Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)














Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT26




	SOT26						
Dim	Min	Max	Тур				
A1	0.013	0.10	0.05				
A2	1.00	1.30	1.10				
А3	0.70	0.80	0.75				
b	0.35	0.50	0.38				
С	0.10	0.20	0.15				
D	2.90	3.10	3.00				
е	-	-	0.95				
e1	-	-	1.90				
E	2.70	3.00	2.80				
E1	1.50	1.70	1.60				
L	0.35	0.55	0.40				
а	-	-	8°				
a1	-	-	7°				
All	All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT26



Dimensions	Value (in mm)
С	2.40
C1	0.95
G	1.60
Х	0.55
Υ	0.80
V1	3.20



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com