



SBR3U60SLDQ

3.0A SBR DUAL ISOLATED SUPER BARRIER RECTIFIER

Product Summary (@T_A = +25°C)

V _{RRM} (V)	I _O (A)	V _F Max (V)	I _R Max (mA)	
60	3	0.60	0.10	

Description

The SBR3U60SLDQ has two independent 3A, 60V rectifiers in one PowerDI[®]5060-8 (Type D) package.

Applications

Offering low leakage at high temperatures and low forward voltage, this device is ideal for use in the following applications:

- **Bridge Diodes**
- Freewheeling Diodes
- **Blocking Diodes**
- Reverse Protection Diodes

Features and Benefits

- Very Low Forward Voltage Drop
- **Excellent High-Temperature Stability**
- Patented SBR® technology provides a superior avalanche capability than Schottky diodes ensuring more rugged and reliable end applications
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability PPAP Capable (Note 4)


Mechanical Data

- Case: PowerDI5060-8 (Type D)
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208@4
- Polarity: See Diagram
- Weight: 0.097grams (Approximate)



Top View

PowerDI5060-8 (Type D)



Pin Out Configuration **Bottom View**



Device Symbol

Ordering Information (Note 5)

Part Number	Compliance	Case	Packaging
SBR3U60SLDQ-13	Automotive	PowerDI5060-8 (Type D)	2,500/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

 4. Automotive products are AEC-Q10x qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



II= Manufacturers' Marking SBR3U60 = Product Type Marking Code YYWW = Date Code Marking YY = Last Two Digits of Year (ex: 17 = 2017) WW = Week (01-53)



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitance load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _{RM}	60	V
Average Rectified Output Current (Per Diode)	lo	3.0	Α
Non-Repetitive Avalanche Energy $(T_J = +25^{\circ}C, I_{AS} = 2A, L = 50mH)$	E _{AS}	90	mJ
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load (Per Diode)	I _{FSM}	60	А

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Typical Thermal Resistance (Note 6)	$R_{ heta JA}$	105	°C/W
Typical Thermal Resistance (Note 6)	$R_{ heta JC}$	20	°C/W
Typical Thermal Resistance (Note 6)	$R_{ heta JA}$	70	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +175	°C

Note:


- 6. Device mounted on FR-4 PCB, 2oz. Copper, minimum recommended pad layout per http://www.diodes.com/package-outlines.html.
- 7. Device mounted on 2 inch x 2 inch Al board.


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Forward Voltage Drop (Per Diode)	VF	_	0.43	1	V	I _F = 1.5A
		_	0.53	0.60		I _F = 3.0A T _A = +25°C
		_	0.40	_		I _F = 1.5A T _A = +125°C
		_	0.52	_		I _F = 3.0A
Reverse Current (Note 8) (Per Diode)	I _R	_	0.008	0.10	mA	V _R = 60V, T _J = +25°C
		_	2.5	15		$V_R = 60V, T_J = +125^{\circ}C$
Total Capacitance	Ст	_	110		pF	V_R = 4V, f= 1MHz, T_J = +25°C

Note: 8. Short duration pulse test used to minimize self-heating effect.









T_A, DERATED AMBIENT TEMPERATURE (°C) Note 5 18 24 V_R, REVERSE VOLTAGE (V)
Figure 5 Operating Temperature Derating Curve





Figure.2 Typical Reverse Characteristics




=1MHz C_T, JUNCTION CAPACITANCE (pF) V_R, REVERSE VOLTAGE (V) Figure 6 Typical Junction Capacitance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8 (Type D)




PowerDI5060-8 (Type D)				
Dim	Min	Max	Тур	
Α	0.90	1.10	1.00	
A1	0.00	0.05	0.02	
b	0.33	0.51	0.41	
b2	0.200	0.350	0.273	
b3	0.48	0.88	0.68	
С	0.230	0.330	0.277	
D	-	.15 BS0		
D1	4.70	5.10	4.90	
D2	1.45	1.85	1.65	
Е	6	.15 BS0		
E1	5.60	6.00	5.80	
E2	3.28	3.68	3.48	
E2a	3.99	4.39	4.19	
е	1	.27BSC	,	
k	0.51	_	_	
k1	0	.60 BS0		
L	0.51	0.71	0.61	
La	0.51	0.71	0.61	
L1	0.10	0.20	0.175	
М	3.235	4.035	3.635	
M1	1.00	1.40	1.21	
θ	10°	12°	11°	
θ1	6°	8°	7°	
All Dimensions in mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8 (Type D)



Dimensions	Value		
Dillicipions	(in mm)		
С	1.270		
G	0.820		
Х	0.610		
X1	4.420		
X2	5.610		
Υ	1.270		
Y1	0.180		
Y2	0.600		
Y3	1.825		
Y4	3.810		
Y5	6.610		



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com