

25V NPN LOW SATURATION MEDIUM POWER TRANSISTOR IN SOT89

Description

This Bipolar Junction Transistor (BJT) is designed to meet the stringent requirement of Automotive Applications.

Features


- BV_{CEO} > 25V
- I_C = 5.5A High Continuous Current
- I_{CM} = 20A Peak Pulse Current
- Very Low Saturation Voltages
- Extremely Low Equivalent On-Resistance; $R_{CE(SAT)} = 25m\Omega$ at 6.5A
- Excellent h_{FE} Characteristics up to 20A
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data

- Case: SOT89
- Case Material: Molded Plastic. "Green" Molding Compound.
 UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208³
- Weight: 0.05 grams (Approximate)

Applications

- Emergency Lighting Circuits
- Motor Driving (Including DC Fans)
- · Solenoid, Relay and Actuator Drivers
- DC DC Modules
- Backlight Inverters



Ordering Information (Note 5)

Part Number	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
ZXTN2005ZQTA	869	7	12	1,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



869 = Product Type Marking Code YWW = Date Code Marking Y = Last Digit of Year (ex: 8 = 2018) WW = Week Code (01 to 53)



Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	60	V
Collector-Emitter Voltage	V _{CEO}	25	V
Emitter-Base Voltage	V _{EBO}	7	V
Continuous Collector Current	Ic	5.5	Α
Peak Pulse Current	I _{CM}	20	Α

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Power Dissipation	(Note 6)		1.5 12	W mW/°C	
Linear Derating Factor	(Note 7)	- P _D	2.1 16.8		
Thermal Desistance, Junction to Ambient Air	(Note 6)	D	83	°C/W	
Thermal Resistance, Junction to Ambient Air	(Note 7)	R _{θJA}	60		
Operating and Storage Temperature Range	$T_{J_i}T_{STG}$	-55 to +150	°C		

ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С

Notes:


^{6.} For a device mounted with the exposed collector pad on 25mm x 25mm 1oz copper that is on a single-sided 1.6mm FR-4 PCB; device is measured under still air conditions whilst operating in a steady-state.

^{7.} Same as note (6), except the device is mounted on 50mm x 50mm 1oz copper.


^{8.} Refer to JEDEC specification JESD22-A114 and JESD22-A115.




Thermal Characteristics and Derating Information




Safe Operating Area



Derating Curve



Transient Thermal Impedance



Pulse Power Dissipation




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV _{CBO}	60	120	_	V	$I_C = 100\mu A$
Collector-Emitter Breakdown Voltage	BV _{CER}	60	120	_	V	$I_C = 1\mu A, R_B \le 1k\Omega$
Collector-Emitter Breakdown Voltage (Note 9)	BV _{CEO}	25	35	_	V	$I_C = 10mA$
Emitter-Base Breakdown Voltage	BV _{EBO}	7	8.1	_	V	$I_E = 100\mu A$
Collector Cutoff Current	I _{CBO}	_	_	20 0.5	nA μA	V _{CB} = 50V V _{CB} = 50V, T _A = +100°C
Collector Cutoff Current	I _{CER} R ≤ 1kΩ	_	_	20 0.5	nA μA	V _{CB} = 50V V _{CB} = 50V, T _A = +100°C
Emitter Cutoff Current	I _{EBO}	_	_	10	nA	V _{EB} = 5.6V
DC Current Transfer Static Ratio (Note 9)	h _{FE}	300 300 200 40	400 450 275 55	_	_	$I_{C} = 10 \text{mA}, V_{CE} = 1 \text{V}$ $I_{C} = 1 \text{A}, V_{CE} = 1 \text{V}$ $I_{C} = 7 \text{A}, V_{CE} = 1 \text{V}$ $I_{C} = 20 \text{A}, V_{CE} = 1 \text{V}$
Collector-Emitter Saturation Voltage (Note 9)	Vce(sat)	_	25 30 45 105 160	35 45 70 130 200	mV	$I_C = 500$ mA, $I_B = 10$ mA $I_C = 1$ A, $I_B = 10$ 0mA $I_C = 1$ A, $I_B = 10$ mA $I_C = 2$ A, $I_B = 10$ mA $I_C = 6.5$ A, $I_B = 15$ 0mA
Base-Emitter Saturation Voltage (Note 9)	V _{BE(SAT)}	_	950	1050	mV	$I_C = 6.5A$, $I_B = 150mA$
Base-Emitter Turn-on Voltage (Note 9)	V _{BE(ON)}	_	860	960	mV	$I_C = 6.5A, V_{CE} = 1V$
Transitional Frequency	f⊤	_	150	_	MHz	I _C = 100mA, V _{CE} = 10V, f = 50MHz
Output Capacitance	C _{OBO}	_	48	_	pF	V _{CB} = 10V, f = 1MHz
Cuitobing Time	t _{ON}		33		20	V _{CC} = 10V, I _C = 1A,
Switching Time	t _{OFF}		464		ns	$I_{B1} = -I_{B2} = 100 \text{mA}$

Note 9: Measured under pulsed conditions. Pulse width = $300\mu s$. Duty cycle $\leq 2\%$.



Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT89




SOT89					
Dim	Min	Max	Тур		
Α	1.40	1.60	1.50		
В	0.50	0.62	0.56		
B1	0.42	0.54	0.48		
С	0.35	0.43	0.38		
D	4.40	4.60	4.50		
D1	1.62	1.83	1.733		
D2	1.61	1.81	1.71		
Е	2.40	2.60	2.50		
E2	2.05	2.35	2.20		
е	-	-	1.50		
Н	3.95	4.25	4.10		
H1	2.63	2.93	2.78		
L	0.90	1.20	1.05		
L1	0.327	0.527	0.427		
Z	0.20	0.40	0.30		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT89



Dimensions	Value (in mm)		
С	1.500		
G	0.244		
Χ	0.580		
X1	0.760		
X2	1.933		
Υ	1.730		
Y1	3.030		
Y2	1.500		
Y3	0.770		
Y4	4.530		

May 2018



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com