

ZXTR2012FF

100V INPUT, 12V 30mA REGULATOR TRANSISTOR IN SOT23F

Description

The ZXTR2012FF monolithically integrates a transistor, Zener diode and resistor to function as a high-voltage linear regulator. The device regulates with a 12V nominal output at 15mA. It is designed for use in high-voltage applications where standard linear regulators cannot be used. This function is fully integrated into an SOT23F package, minimizing PCB area and reducing number of components when compared with a multi-chip discrete solution.

Applications

Supply voltage regulation in:


- Networking
- · Telecommunications
- Power over Ethernet (PoE)

Features

- Series Linear Regulator Using Emitter-Follower Stage
- Input Voltage = 15V to 100V
- Output Voltage = 12V ± 10%
- Fully Integrated into a SOT23F Package
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Mechanical Data

- Case: SOT23F
- Case material: Molded Plastic. "Green" Molding Compound.
 UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.012 grams (Approximate)




Ordering Information (Note 4)

Product	Package	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
ZXTR2012FF-7	SOT23F	1T4	7	8	3,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen and Antimony free, "Green" and Lead-Free.
- 3. Halogen and Antimony free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds
- 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



1T4 = Product Type Marking Code YW = Date Code Marking

<u>Y</u> = Year : 0~9

W = Week : A~Z : 1~26

a~z:27~52

z represents 52 & 53 week



Absolute Maximum Ratings (Voltage relative to GND, @TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Input Supply Voltage	V _{IN}	-0.3 to 100	V
Continuous Input & Output Current	I _{IN,} I _{OUT}	550	mA
Peak Pulsed Input & Output Current	I _{IM} , I _{OM}	2	Α
Maximum Voltage Applied to Vout	V _{OUT(MAX)}	18	V

Maximum Current at V_{IN} = 48V (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Continuous Output Current	(Note 7)	l _{OUT}	36	mA
Pulsed Output Current	(Note 8)	1	880	m A
Pulsed Output Current	(Note 9)	IOM	180	mA

Thermal Characteristics

Characteristic		Symbol	Value	Unit	
Power Dissipation	(Note 5)	В	1.3	W	
Power dissipation	(Note 6)	P _D	1		
Thermal Pecietanes, Junction to Ambient	(Note 5)	D	95		
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{\theta JA}$	126	°C/W	
Thermal Resistance, Junction to Lead	(Note 10)	$R_{\theta JL}$	59	*C/VV	
Thermal Resistance, Junction to Case (Note 10)		R ₀ JC	38		
Maximum Operating Junction and Storage Temp	T _J , T _{STG}	-65 to +150	°C		

ESD Ratings (Note 11)

Notes:

Characteristics	Symbols	Value	Unit	JEDEC Class
Electrostatic Discharge – Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge – Machine Model	ESD MM	400	V	С

5. For a device mounted with the exposed V_{IN} pad on 25mm x 25mm 1oz copper that is on a single-sided 1.6mm FR-4 PCB; device is measured under still


air conditions whilst operating in steady-state.

6. Same as note 5, except mounted on 15mm x 15mm 1oz copper.

- Same as note 5, except mounted on 15mm x 15mm 1oz copper.
 Same as note 5, whilst operating at V_{IN} = 48V. Refer to Safe Operating Area for other Input Voltages.
- 8. Same as note 5, except measured with a single pulse width = 100μ s and $V_{IN} = 48V$.
- 9. Same as note 5, except measured with a single pulse width = 10ms and V_{IN} = 48V.
- 10. R_{0JL} = Thermal resistance from junction to solder-point (on the exposed V_{IN} pad). R_{0JC} = Thermal resistance from junction to the top of case.
- 11. Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics and Derating Information






Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Output Voltage (Note 12)	V _{OUT}	10.8	12	13.2	V	V _{IN} = 48V, I _{OUT} = 15mA
Line Regulation (Notes 12 & 13)	ΔV_{OUT}	ı	240	750	mV	$V_{IN} = 15V$ to $72V$, $I_{OUT} = 15mA$
Temperature Coefficient	ΔV _{OUT} /ΔΤ	1	8.0	l	mV/°C	$T_J = -40$ °C to +125°C $V_{IN} = 48V$, $I_{OUT} = 15$ mA
Load Regulation (Notes 12 & 14)	ΔV_{OUT}		-450 -600	-600 -750	mV	$I_{OUT} = 0.1 \text{mA}$ to 30mA, $V_{IN} = 48 \text{V}$ $I_{OUT} = 0.1 \text{mA}$ to 100mA, $V_{IN} = 48 \text{V}$
Minimum Value of Input Voltage Required to Maintain Line Regulation	V _{IN(MIN)}	15	_	-	V	_
Quiescent Current	ΙQ	1	240 590	400 900	μA	$V_{IN} = 48V$, $I_{OUT} = 10\mu A$ $V_{IN} = 100V$, $I_{OUT} = 10\mu A$
Power Supply Rejection Ratio	$\Delta V_{\text{IN}} \Delta V_{\text{OUT}}$	1	45	-	dB	$C_{OUT} = 100$ nF, $I_{OUT} = 15$ mA, $V_{OUT} = 12$ V, $V_{IN} = 15$ V to 100V, $f = 100$ Hz

Notes:

- 12. Measured under pulsed conditions. Pulse width ≤ 300µs. Duty cycle ≤ 2%.
- $\Delta V_{OUT} = V_{OUT} (@V_{IN} = 72V) V_{OUT} (@V_{IN} = 15V).$ 13. Line regulation
- $\Delta V_{OUT} = V_{OUT}(@ \ l_{OUT} = 30\text{mA}) V_{OUT}(@ \ l_{OUT} = 0.1\text{mA}).$ $\Delta V_{OUT} = V_{OUT}(@ \ l_{OUT} = 100\text{mA}) V_{OUT}(@ \ l_{OUT} = 0.1\text{mA}).$ 14. Load regulation

Typical Application Circuit




Example of an 12V regulated supply from a nominal 48V for powering a Controller IC.

Pin Functions

Pin Name	Pin Function	Notes
V _{IN}	Input Supply	To maintain output regulation the input voltage can vary from 15V to 100V with respect to the GND pin. It is recommended to connect a 1µF capacitor to GND.
GND	Power Ground	This pin should be tied to the system ground.
		Outputs a regulated 12V. It is recommended to connect a 10μ F capacitor to GND. Minimum of 10μ A must be drawn from V_{OUT} to maintain regulation. The pin can be pulled high to a maximum of 18V with respect to ground.



Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)



Notes: 15. Line regulation $\Delta V_{OUT} = V_{OUT} - V_{OUT}$ (@ $V_{IN} = 15V$, $I_{OUT} = 15mA$, $T_J = +25^{\circ}C$).

^{16.} Load regulation $\Delta V_{OUT} = V_{OUT} - V_{OUT}$ (@ $V_{IN} = 48V$, $I_{OUT} = 0.1$ mA, $T_J = +25$ °C).


^{17.} Temperature Coefficient $\Delta V_{OUT} = V_{OUT} - V_{OUT}$ (@ V_{IN} = 48V, I_{OUT} = 15mA, T_J = +25°C).



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23F




	SOT23F						
Dim	Min	Тур					
Α	0.80	1.00	0.90				
A1	0.00	0.10	0.01				
b	0.35	0.50	0.44				
С	0.10	0.20	0.16				
D	2.80 3.00 2.90						
е	0.95 REF						
e1		1.90 RE	F				
Е	2.30	2.50	2.40				
E1	1.50	1.70	1.65				
k	1.20	-	-				
L	0.30	0.65	0.50				
L1	0.30	0.50	0.40				
R	0.05	0.15	-				
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23F



Dimensions	Value		
וווופוואוטווא	(in mm)		
С	0.95		
Х	0.80		
Y	1.110		
Y1	3.000		

April 2016

© Diodes Incorporated



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com