



### **10A SUPER-FAST RECTIFIER**

## Product Summary (Per Leg, @ T<sub>A</sub> = +25°C)

V <sub>RRM</sub> (V)	I <sub>O</sub> (A)	V <sub>F</sub> (V)	I <sub>R</sub> (μA)
300	5	1.3	10

## **Features and Benefits**

- Super-Fast Switching Capability
- Glass Passivated Die Construction
- Rating to 300V Peak Reverse Voltage
- High Current Capability
- Low Forward Voltage Drop
- Low Reverse Leakage Current
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. <a href="https://www.diodes.com/quality/product-definitions/">https://www.diodes.com/quality/product-definitions/</a>

## **Applications**

- Switched Mode Power Supplies
- High Frequency DC to DC Converters

### **Mechanical Data**


- Package: ITO220AB (Type WX)
- Package Material: Molded Plastic, "Green" Molding Compound.
   UL Flammability Classification Rating 94V-0
- Terminals: Finish Matte Tin Plated Leads Solderable per MIL-STD-202, Method 208
- Polarity: See Diagram
- Weight: 1.558 grams (Approximate)

### ITO220AB (Type WX)



Top View

**Bottom View** 



Package Pin Out Configuration

### Ordering Information (Note 4)


Part Number	Qualification	Packago	Packing		
Part Number	Qualification	Package	Qty.	Carrier	
STPF1030	Commercial	ITO220AB (Type WX)	50 pcs	Tube	

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

# **Marking Information**

#### ITO220AB (Type WX)



STPF1030 = Product Type Marking Code

| | = Manufacturer's Marking

YYWW = Date Code Marking

YY = Last Two Digits of Year (ex: 21 for 2021)

WW = Week Code (01 to 53)

AB = Foundry and Assembly Code



# Maximum Ratings (@ T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage DC Blocking Voltage	$V_{RRM} \ V_{R}$	300	٧
Average Rectified Output Current, @Tc = 90°C (Per Leg) (Total)	lo	5 10	А
Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I <sub>FSM</sub>	80	A

## **Thermal Characteristics**


Characteristic	Symbol	Value	Unit
Typical Thermal Resistance Junction to Case (Note 5, 6)	$R_{ heta JC}$	5	°C/W
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150	°C

# **Electrical Characteristics** (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 7)	V <sub>(BR)R</sub>	300	_	_	V	$I_R = 10\mu A$
		_	_	1.30	٧	I <sub>F</sub> = 5A, T <sub>J</sub> = +25°C I <sub>F</sub> = 5A, T <sub>J</sub> = +125°C
Forward Voltage (Note 8)	V <sub>F</sub>	_	_	1.20		$I_F = 5A, T_J = +125$ °C
Toward Voltage (Note o)		_	_	1.50	\/	I <sub>F</sub> = 10A, T <sub>J</sub> = +25°C I <sub>F</sub> = 10A, T <sub>J</sub> = +125°C
			_	1.40	V	$I_F = 10A, T_J = +125$ °C
Reverse Leakage Current (Note 7)	I <sub>R</sub>	_	_	10	μΑ	$V_R = 300V, T_J = +25^{\circ}C$
Neverse Leakage Current (Note 1)			_	250	μΑ	$V_R = 300V, T_J = +100^{\circ}C$
Typical Total Capacitance	C <sub>T</sub>	_	30	50	pF	V <sub>R</sub> = 4V, f = 1.0MHz
Reverse Recovery Time	t <sub>RR</sub>	_	_	35	ns	$I_F = 0.5A$ , $I_R = 1.0A$ , $I_{RR} = 0.25A$

- 5. Thermal resistance test performed in accordance with JESD-51.
- 6. The unit mounted on 100.64mm x 75.2mm x 26.83 mm Aluminum Plate Heatsink.
- 7. Short duration pulse test used to minimize self-heating effect. 8. 300µs pulse width, 2% duty cycle.









Fig. 1 FORWARD CURRENT DERATING CURVE

Fig. 2 MAXIMUM NON-REPETITIVE SURGE CURRENT






Fig. 3 TYPICAL FORWARD CHARACTERISTICS

Fig. 4 TYPICAL TOTAL CAPACITANCE





Fig. 5 TYPICAL REVERSE CHARACTERISTICS



# **Package Outline Dimensions**

 $\label{prop:package-outlines.html} Please see \ http://www.diodes.com/package-outlines.html \ for \ the \ latest \ version.$ 

## ITO220AB (Type WX)



ITO220AB				
(Type WX)				
Dim	Min	Max		
Α	4.46	4.87		
A1	2.48	2.80		
A2	2.50	2.80		
b	0.50	0.80		
b1	1.15	1.70		
b2	1.50	1.90		
С	0.45	0.70		
D	14.95	15.95		
D1	8.50	8.80		
Е	10.00	10.40		
е	2.40	2.70		
L	13.00	13.70		
L1	3.30	3.90		
Q	2.76	3.36		
Р	3.00	3.30		
All Dimensions in mm				



#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- provided to Diodes' Standard Terms and Conditions of Sale Diodes products are subject (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com